

Tweco® MIG 11 & 14-Series Contact Tips

Specifications

Part No.	Description	Part No.	Description
1444-0025	MIG 11-Series .023" Contact Tip 10 PK	1444-0220	MIG 14-Series .023" Contact Tip 10 PK
1444-0026	MIG 11-Series .030" Contact Tip 10 PK	1444-0221	MIG 14-Series .030" Contact Tip 10 PK
1444-0027	MIG 11-Series .035" Contact Tip 10 PK	1444-0222	MIG 14-Series .035" Contact Tip 10 PK
1444-0029	MIG 11-Series .040" Contact Tip 10 PK	1444-0224	MIG 14-Series .045" Contact Tip 10 PK



FEATURES

- 10 Copper Tips Per Pack

APPLICATIONS

Used with 11 & 14-Series MIG Guns for MIG Welding.

Tweco MIG 11 & 14-Series Nozzles

Specifications

Part No.	Description	Part No.	Description
1444-0050	MIG 11-Series 3/8" Flush Nozzle	1444-0140	MIG 14-Series 1/2" Flush Nozzle
1444-0051	MIG 11-Series 1/2" Flush Nozzle	1444-0141	MIG 14-Series 5/8" Flush Nozzle
1444-0052	MIG 11-Series 5/8" Flush Nozzle	1444-0142	MIG 14-Series 5/8" Flush Arc Nozzle



FEATURES

- Heavy Duty Copper Nozzle

APPLICATIONS

Used with 11 & 14-Series MIG Guns for MIG Welding.

Tweco MIG Velocity™ Contact Tips

Specifications

Part No.	Description
1444-0890	MIG Velocity .023" Contact Tip 10 PK
1444-0891	MIG Velocity .030" Contact Tip 10 PK
1444-0892	MIG Velocity .035" Contact Tip 10 PK
1444-0893	MIG Velocity .045" Contact Tip 10 PK



FEATURES

- 10 Copper Tips Per Pack

APPLICATIONS

Used with Velocity® Series MIG Guns for MIG Welding.

Tweco MIG Velocity Nozzles

Specifications

Part No.	Description	Part No.	Description
1444-0885	MIG Velocity 3/8" Flush Nozzle	1444-0888	MIG Velocity Flux Cored Nozzle
1444-0886	MIG Velocity 1/2" Flush Nozzle	1444-0889	MIG Velocity 3/4" Spot Nozzle
1444-0877	MIG Velocity 1/2" Recess Nozzle	1444-0876	MIG Velocity Adjustable Slip Fit Tip Holder
1444-0887	MIG Velocity 5/8" Flush Nozzle	1444-0879	MIG Velocity Adjustable Slip Fit Nozzle
1444-0878	MIG Velocity 5/8" Recess Nozzle		



FEATURES

- Heavy Duty Copper Nozzle

APPLICATIONS

Used with Velocity Series MIG Guns for MIG Welding.