



**MCR**  
SAFETY

# Klondike Plus

## Safety Glasses

### Plus Series

#### Specification Sheet

#### **PRODUCT DESCRIPTION:**

The Klondike® Plus features safety and style at an affordable price to separate you from the pack. Whether on the slopes or in the workplace, Klondike®'s matte black frame finish, 5-position ratchet adjustable temples, 11 degree base curve lens and TPR nose piece keeps you at the peak of comfort and style all day long. Lens models are available in your choice of multiple options.

#### **FEATURES:**

- Adjustable, 5-position ratchet action spatula temples
- Black matte finish
- Full orbital seal with dual lens design
- Soft, secure TPR nose pad



#### **TECHNICAL DATA FOR: KD310**

|                        |                          |                          |                 |
|------------------------|--------------------------|--------------------------|-----------------|
| <b>Brand</b>           | MCR Safety               | <b>Scratch Resistant</b> | Yes             |
| <b>Series</b>          | Klondike Plus            | <b>Frame Material</b>    | Nylon           |
| <b>Category</b>        | Safety Glasses           | <b>Packaging</b>         | White Inner Box |
| <b>Case Pack</b>       | 144 pair                 | <b>MIL - PRF - 31013</b> | N/A             |
| <b>Case Dimensions</b> | 22.047 x 14.961 x 13.386 | <b>ANSI Z87+</b>         | Yes             |
| <b>Case Weight</b>     | 15.201 oz.               | <b>AS/NZS 1337.1</b>     | N/A             |
| <b>Made In</b>         | Taiwan                   | <b>CE EN166</b>          | Yes             |

| Item No: | Lens Options: | Lens Coating:      | Scratch Resistant: | VLT%: | Frame Color: | Temple Color: | Temple Sleeve: |
|----------|---------------|--------------------|--------------------|-------|--------------|---------------|----------------|
| KD310    | Clear         | Duramass Hard Coat | Yes                | 90    | Black        | Black         | N/A            |
| KD310AF  | Clear         | Duramass Anti-Fog  | Yes                | 90    | Black        | Black         | N/A            |
| KD312    | Gray          | Duramass Hard Coat | Yes                | 13    | Black        | Black         | N/A            |
| KD312AF  | Gray          | Duramass Anti-Fog  | Yes                | 13    | Black        | Black         | N/A            |
| KD313    | Light Blue    | Duramass Hard Coat | Yes                | 68    | Black        | Black         | N/A            |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2016 MCR Safety - All Rights Reserved



**MCR**  
**SAFETY**

# Klondike Plus

## Safety Glasses

### Plus Series

#### Specification Sheet

| <b>Item No:</b> | <b>Lens Options:</b> | <b>Lens Coating:</b> | <b>Scratch Resistant:</b> | <b>VLT%:</b> | <b>Frame Color:</b> | <b>Temple Color:</b> | <b>Temple Sleeve:</b> |
|-----------------|----------------------|----------------------|---------------------------|--------------|---------------------|----------------------|-----------------------|
| KD314           | Amber                | Duramass Hard Coat   | Yes                       | 80           | Black               | Black                | N/A                   |
| KD319           | I/O Clear Mirror     | Duramass Hard Coat   | Yes                       | 36           | Black               | Black                | N/A                   |
| KD319AF         | I/O Clear Mirror     | Duramass Anti-Fog    | Yes                       | 36           | Black               | Black                | N/A                   |
| KDRX            | Clear                | Uncoated             | No                        | N/A          | N/A                 | N/A                  | N/A                   |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2016 MCR Safety - All Rights Reserved