



## G10 Blue Nitrile Gloves

Codes: 57370, 57371, 57372, 57373, 57374

### Product Information

Code	Size	Palm Width*(mm)	Length* (mm)	Quantity
57370	XS	70	242	100 gloves/box; 10 boxes/case
57371	S	80	242	100 gloves/box; 10 boxes/case
57372	M	95	242	100 gloves/box; 10 boxes/case
57373	L	110	242	100 gloves/box; 10 boxes/case
57374	XL	120	242	90 gloves/box; 10 boxes/case

\*As measured by ASTM D 6319;ASTM D 3578; 2.5 AQL<sup>1</sup>



Property	Description
General Description	Blue nitrile, powder free, non-sterile, textured fingertip, ambidextrous gloves, beaded cuff, online chlorinated on donning side, powder free coagulant on the grip side

Physical Property	Unit	Upper Limit	Test Method (1.5 AQL)
Watertightness	NA	Pass	ASTM D 5151
Residual Powder Level	mg/glove	1	ASTM D 6124

Thickness	Nominal	Nominal	Test Method (2.5 AQL)
Middle Finger	6.00 mil	0.15 mm	ASTM D 6319
Palm	3.94 mil	0.10 mm	ASTM D 6319
Cuff	2.36 mil	0.06 mm	ASTM D 6319

Property	Tensile Strength	Ultimate Elongation	Median Force at Break
Before Aging	14 Mpa	500%	N/A
After Aging	14 Mpa	400%	6.0 Newtons
Test Method (2.5 AQL S-2)	ASTM D 412 ASTM D 573 ASTM D 3578	ASTM D 412 ASTM D 573 ASTM D 3578	EN 455-2

<sup>1</sup> AQL levels defined according to ISO 2859-1 (current edition) Sampling Procedures for Inspection by Attributes.

### Workmanship Requirement:

Gloves shall be made in accordance with reasonable industry practice with respect to defects, dirt and contamination. Gloves should be packaged as specified having described size and color in the appropriate quantity as listed. Shipping Case and inner packaging shall be labeled with product name, size, lot/batch and catalog number.

For additional information: 1-800-255-6401 or [kimtech@kcc.com](mailto:kimtech@kcc.com)

Kimberly-Clark warrants that its products (1) comply with K-C's standard specifications as of the delivery date to K-C's authorized distributors/direct purchasers and are warranted for the following periods from end user's date of purchase (verified by valid sales receipt) (a) five years for Balder Technology auto darkening filters; (b) two years for all other auto darkening filters; and (c) one year for powered air purifying respirators; (2) comply with all K-C labeling representations; and (3) are manufactured in compliance with all applicable federal, state, and local laws in effect at the time and place of manufacture of the products. THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. K-C is not liable for any kind of special, incidental, or consequential damages. K-C's liability for breach of contract, tort or other cause of action shall not exceed the product purchase price. Purchasers and users are deemed to have accepted the above warranty and limitation of liability, and cannot change the terms by verbal agreement or by any writing not signed by K-C. To the extent required by applicable law, K-C does not limit its liability for death/injury resulting from K-C's negligence.