



4700 W. 160th St.  
Cleveland, OH 44135  
1-800-321-9532  
1-800-321-9535  
www.oatey.com

TECHNICAL SPECIFICATION

## CENTRO II WASHING MACHINE OUTLET BOX



**TECHNICAL SPECIFICATION:** Oatey's Centro II Washing Machine Box is used for commercial and residential washing machine applications. Oatey's Centro WMOB can be mounted with the valves on the top or bottom. Oatey's WMOB comes with two support brackets and two piece uninstalled valves.



- Takes up less space and will fit almost anywhere
- WMOB made of PVC
- Brackets and Faceplate made of HIPS
- 2 knockout drain caps
- 2" Socket Hubs
- Mountable with valves on top or bottom
- 2 piece valves come uninstalled or installed
- Two support brackets
- Available in a wide variety of tailpiece configurations and packaging options
- Dimensions:
  - WMOB-8"W x 4-3/4"H x 3"D
  - Faceplate- 10"W x 6-3/4"H

PRODUCT NUMBER	DESCRIPTION	CTN. QTY.
<b>No Hammer Assembled</b>		
38100	¼ Turn, Copper, No Hammer, Assembled, Standard Pack	12
38102	¼ Turn, CPVC, No Hammer, Assembled, Standard Pack	12
38104	¼ Turn, ASTM F1807, No Hammer, Assembled, Standard Pack	12
38106	¼ Turn, ASTM F1960, No Hammer, Assembled, Standard Pack	12
38150	¼ Turn, Copper, No Hammer, Assembled, Contractor Pack	12
38153	¼ Turn, CPVC, No Hammer, Assembled, Contractor Pack	12
38151	¼ Turn, ASTM F1807, No Hammer, Assembled, Contractor Pack	12
38152	¼ Turn, ASTM F1960, No Hammer, Assembled, Contractor Pack	12
<b>Hammer Assembled</b>		
38101	¼ Turn, Copper, Hammer, Assembled, Standard Pack	12
38103	¼ Turn, CPVC, Hammer, Assembled, Standard Pack	12
38105	¼ Turn, ASTM F1807, Hammer, Assembled, Standard Pack	12
38107	¼ Turn, ASTM F1960, Hammer, Assembled, Standard Pack	12
38154	¼ Turn, Copper, Hammer, Assembled, Contractor Pack	12
38157	¼ Turn, CPVC, Hammer, Assembled, Contractor Pack	12
38155	¼ Turn, ASTM F1807, Hammer, Assembled, Contractor Pack	12
38156	¼ Turn, ASTM F1960, Hammer, Assembled, Contractor Pack	12



4700 W. 160th St.  
Cleveland, OH 44135  
1-800-321-9532  
1-800-321-9535  
www.oatey.com

TECHNICAL SPECIFICATION

**CENTRO II WASHING MACHINE  
OUTLET BOX**



<b>No Hammer Unassembled</b>		
38108	¼ Turn, Copper, No Hammer, Unassembled, Standard Pack	12
38110	¼ Turn, CPVC, No Hammer, Unassembled, Standard Pack	12
38112	¼ Turn, ASTM F1807, No Hammer, Unassembled, Standard Pack	12
38114	¼ Turn, ASTM F1960, No Hammer, Unassembled, Standard Pack	12
<b>Hammer Unassembled</b>		
38109	¼ Turn, Copper, Hammer, Unassembled, Standard Pack	12
38111	¼ Turn, CPVC, Hammer, Unassembled, Standard Pack	12
38113	¼ Turn, ASTM F1807, Hammer, Unassembled, Standard Pack	12
38115	¼ Turn, ASTM F1960, Hammer, Unassembled, Standard Pack	12
<b>Plain Boxes</b>		
38120	Plain Box, Display Pack	4
38121	Plain Box, Standard Pack	12
<b>Accessories</b>		
38381	Centro II, Plastic Faceplate	12
38382	Brackets 4" Long Plastic	12
38383	Brackets 12" Long Plastic	12
38294	Hot/Cold Temperature Indicator Clips for Supply Valves (12 Red, 12 Blue)	24