# SPEC SHEET #S00039 April 2002

# **300 DEGREE Plumbers Grease** Valve Stem Grease





#### DESCRIPTION

Hercules unique formula petroleum based grease lubricates and prevents corrosion on valve stems, faucets, ballcock linkage, and other places where a water resistant grease is needed. Smoothes and eases hard turning faucets. Use on sump and sewage ejector pump linkage to prevent corrosion and sticking. Assures free movement and extended life. Will not melt like ordinary greases. For use on steam and hot/cold water systems. Withstands -20°F to +300°F. Non-hazardous and non-toxic. Waterproof; will not dissolve into stream, resists wash out even in severe water flow or water wash situations. Safe for use with potable water.

SIZES AND PACKING			
STOCK NO.	SIZE	PACKING	WEIGHT/CASE
40-601	2 oz.	24	4.2 lbs.



### SPEC SHEET #S00039

# **300 DEGREE PlumbersGrease** Valve Stem Grease

## APPROVALS AND LISTINGS

Not Applicable.

#### **SPECIFIC USES**

Use **300 Degree Plumbers Grease** to lubricate valve stems, faucets and ballcocks.

### **SPECIFIC APPLICATIONS\***

**300 Degree Plumbers Grease** can be used as a lubricant on sliding or rotating metal parts in steam and hot/cold water systems.

### PHYSICAL PROPERTIES

Appearance/color/odor: Smooth translucent amber grease. Odorless.

#### WARNINGS OR CAUTIONS

- Read all cautions and directions carefully before using this product.
- KEEP OUT OF REACH OF CHILDREN.
- If Plumbers Grease is dropped on floor wipe up to prevent slippery footing.

#### **DIRECTIONS FOR USE**

Valve Bodies: Unscrew valve bonnet nut. Rotate valve stem counter clockwise to remove from valve body. Clean stem and threads if necessary. Apply a liberal amount of **300 Degree Plumbers Grease** to the stem and stem threads. Reassemble in reverse order. Tighten bonnet nut lightly. Retighten if necessary to prevent seepage when system pressure is restored.

**Ballcock and Float Linkages:** Clean and descale first if necessary. Apply liberally to all rubbing and pivoting surfaces. Apply a thin film to all metal parts in contact with water to prevent corrosion and scale build up. Apply to float linkage threads to prevent corrosion.



### MATERIAL SAFETY INFORMATION

FOR MORE INFORMATION ON THIS PRODUCT, REQUEST MATERIAL SAFETY DATA SHEET- Clear (MSDS) #39

For Delivery by Fax	Call 1-800-942-4636	
Internet	See MSDS section of www.herchem.com	
Mail	Contact Hercules at address below or any Hercules representative	

HMIS Hazard Warning 0-0-0-A

INGREDIENTS

CAS#

NJ-T.S.R. #31348300 5005P, 5003P

This product is not classified as hazardous in accordance with OSHA 29 CFR 1910.1200.

\* For special applications which may not be covered on this or other Hercules literature, please contact Hercules Technical Services Department by phone at 1-800-221-9330 or send a fax to 1-800-333-3456.



# **Hercules Chemical Company, Inc.**

111 South Street, Passaic, NJ 07055-9100 Phone: 800-221-9330 • Fax: 800-333-3456 e-mail: info@herchem.com

http://www.herchem.com

