



SPECIFICATION SHEET

63-336PF

AMBI-DEX® OVERDRIVE DISPOSABLE NITRILE GLOVE, POWDER FREE WITH TEXTURED GRIP - 6 MIL

- Powder-Free for clean comfort and superior tactile sensitivity
- Contains no natural rubber latex proteins
- Ambidextrous for quick and easy donning
- Economical puncture resistance with great comfort, dexterity and tactile sensitivity
- Silicone free
- Complies with FDA food handling requirements, 21 CFR 177.2600

APPLICATIONS

- Industrial
- Sanitation
- Plumbing

TECHNICAL DATA

MATERIAL	Nitrile
COLOR	Blue
SIZES	S - XL
PACKAGING	100 gloves per dispenser box; 10 boxes per case (1,000 gloves)
CASE	15.2" x 10.2" x 10.4" / 38.5cm x 26.0cm x 26.5cm
CASE WEIGHT	22 lbs / 10 kg
COO	Malaysia



ELONGATION INFORMATION


BEFORE AGING		AFTER ACCELERATED AGING	
Tensile Strength (minimum)	Elongation (minimum)	Tensile Strength (minimum)	Elongation (minimum)
(Mpa)	%	(Mpa)	%
14	600	14	500

BARCODES

ITEM	BAG	DISPENSER	CASE
63-336PF/S	---	616314034435	02616314034435
63-336PF/M	---	616314034404	02616314034404
63-336PF/L	---	616314034411	02616314034411
63-336PF/XL	---	616314034428	02616314034428

DIMENSIONS (in/cm)

	S	M	L	XL
A	10 / 25.5	10 / 25.5	10 / 25.5	10 / 25.5
B	3.3 / 8.3	3.7 / 9.5	4.2 / 10.6	4.4 / 11.2
Palm Thickness: 0.15 mm (+/- 0.02 mm)				
Cuff Thickness: 0.09 mm (+/- 0.02 mm)				
Finger Tip Thickness: 0.19 mm (+/- 0.02 mm)				



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.