



Sundström Safety AB  
 Västergatan 4, S-341 50 Lagan  
 1-887-SUNDSTROM



**SR 231 CARTRIDGE (H02-3621)**

THIS CARTRIDGE IS APPROVED ONLY IN THE FOLLOWING CONFIGURATIONS:

RESPIRATOR COMPONENTS

TC-	Protection <sup>1</sup>	Cartridge	Alternate Facepiece						Alternate head harness				Filter	Accessories												Cautions and Limitations <sup>2</sup>		
			SR 200	SR 100 S/M	SR 100 M/L	SR 90-3 S/M	SR 90-3 M/L	U01-1221	T01-1215	U01 - 2001	S-5792	H02-1321		SR 345	SR 64	SR 221	5153-2	R01-0605	SR 322	SR 336	T01-1203	T01-1201	T01-1204	T01-1205	SR 84		ST2-SR	
23C - 1903	CL/HC/SD/FM	X	X	X					X	X			X	X	X	X	X	X									X	ABCHJKLMNO
84A - 2661	CL/HC/SD/FM/P100	X		X	X						X	X	X	X	X	X	X	X									X	ABCHJKLMNOP
23C-2097	CL/HC/SD/FM	X	X					X	X				X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	ABCHJKLMNO
84A-3382	CL/HC/SD/FM/P100	X	X					X	X				X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	ABCHJKLMNOP
23C-2298	SA/CF/CL/HC/SD/FM	X	X					X	X				X	X					X	X								ABCHJKLMNO
84A-4309	SA/CF/CL/HC/SD/FM/P100	X	X					X	X				X	X	X				X	X								ABCHJKLMNOP
23C-2624	CL/HC/SD/FM	X				X	X			X	X		X	X	X	X	X	X									X	ABCHJKLMNO
84A-5392	CL/HC/SD/FM/P100	X				X	X			X	X		X	X	X	X	X	X									X	ABCHJKLMNOP

**1. PROTECTION**

**P100-Particulate Filter** (99.97% filter efficiency level) effective against all particulate aerosols.

- CL - Chlorine
- CF - Continuous Flow
- FM - Formaldehyde
- SA - Supplied-Air
- HC - Hydrogen chloride
- SD - Sulfur dioxide

**2. CAUTIONS AND LIMITATIONS**

- A - Not for use in atmospheres containing less than 19.5 percent oxygen.
- B - Not for use in atmospheres immediately dangerous to life or health.
- C - Do not exceed maximum use concentrations established by regulatory standards.
- H - Follow established cartridge and canister change schedules or observe ESLI to ensure that cartridges and canisters are replaced before breakthrough occurs
- J - Failure to properly use and maintain this product could result in injury or death.
- K - The Occupational Safety and Health Administration regulations require gas-proof goggles to be worn with this respirator when used against formaldehyde.
- L - Follow the manufacturer's User's Instructions for changing cartridges, canister and/or filters.
- M - All approved respirators shall be selected, fitted, used, and maintained in accordance with MSHA, OSHA and other applicable regulations.
- N - Never substitute, modify, add, or omit parts. Use only exact replacement parts in the configuration as specified by the manufacturer.
- O - Refer to User's Instructions, and/or maintenance manuals for information on use and maintenance of these respirators.
- P - NIOSH does not evaluate respirators for use as surgical masks.