

Standard Features:

- Auto Start/Auto Stop: Optical sensor detects paper and starts operation automatically
- LED Control Panel with Load Indicator
- Door Safety Sensor: Motor stops automatically if cabinet door is opened
- Auto Reverse: In case of paper jam, built-in controls switch motor into reverse to clear jam
- Heat-Treated Steel Cutters: Specially ground for longevity and require minimal oiling
- High Quality Geared Motor: Powerful, efficient AC geared-motor with heavy duty steel gears for high performance and minimal noise
- Extra-wide 16" feed opening
- Continuous-Duty Motor for non-stop operation
- All-Metal Cabinet with casters
- Auto Sensor: When the waste bin is full, the motor stops automatically
- Lifetime Guaranteed Heavy-Duty Waste Bin
- Auto Cleaning: If shred capacity is decreased, press reverse button for 5 seconds and motor will run in reverse for 1 minute
- Oil Indicator: After every 4 hours of use, the control panel LED flashes to suggest oiling cutting blades for optimal performance
- Self-Diagnosis System: Records operation time, number of auto-reverse sequences, volume of paper shredded, and can display information for service technicians
- Thermal overload protection
- Safety Circuit Breaker ensures safe operation

Abilities:


- Accepts staples, paper clips and credit cards
- Manual Function: For shredding small paper or films which can't be detected by the sensor

Options:

- EvenFlow™ Automatic Oiling System: Lubricates cutting blades for optimal performance
- Cutting Head Lubricating Oil: #8000-10, six 8-ounce bottles per case
- Shredder Bags: Uses #8000-50, case of 100

Warranty:

- Lifetime Limited Warranty on cutting head
- 1-Year Warranty on all other parts



Control Panel



Commercial-grade components in a sleek, practical design

Formax FD 8600CC & FD 8600SC Office Shredders combine document security with convenience, safety and reliability. Cross-cut and Strip-cut models feature an easy-to-use LED control panel and an extra-wide 16" feed opening which accommodates green-bar computer forms.

Commercial-grade components include heat-treated steel blades, a steel cabinet, lifetime guaranteed waste bin, and a powerful AC geared-motor to ensure years of reliable performance and information security in your office environment.

The optional EvenFlow™ Automatic Oiling System helps to keep the FD 8600 in peak operating condition.

Specifications: FD 8600CC FD 8600SC

Cutting Style:	Cross Cut	Strip Cut
Shred Size:	5/32" x 1-1/5"	1/4"
Sheet Capacity:	26 to 28	29 to 31
Speed:	20 fpm	30 fpm
Feed Opening:	16"	16"
Dimensions:	24" W x 20" D x 35" H	24" W x 20" D x 35" H
Bin Capacity:	26 gal.	26 gal.
Weight:	242 lbs.	242 lbs.
Security Level:	Level 3 (HIPAA Compliant)	Level 2
Power Supply:	110V, 50/60 Hz	110V, 50/60 Hz



Optional EvenFlow™
Automatic Oiling System