

Standard Features:


- Internal AutoOiler: Automatically oils the cutting blades periodically, as needed
- Auto Start/Auto Stop: Optical sensor detects paper and starts operation automatically
- LED Control Panel with Load Indicator
- Door Safety Sensor: Motor stops automatically if cabinet door is opened
- Auto Reverse: In case of paper jam, built-in controls switch motor into reverse to clear jam
- Heat-treated steel cutters are specially ground for longevity
- High Quality Geared Motor: Powerful, efficient AC geared-motor with heavy duty steel gears for high performance and minimal noise
- Extra-wide 16" feed opening
- All-Metal Cabinet with casters
- Auto Sensor: When the waste bin is full, the motor stops automatically
- Lifetime Guaranteed Heavy-Duty Waste Bin
- Auto Cleaning: If shred capacity is decreased, press reverse button for 5 seconds and motor will run in reverse for 1 minute
- Self-Diagnosis System: Records a variety of information for service technicians
- Accepts staples, paper clips and credit cards
- Thermal Overload Protection
- Safety Circuit Breaker ensures safe operation

Options:

- Cutting Head Lubricating Oil: Uses #8000-12, bottles specifically sized for the FD 8650CC, eight 16-ounce bottles per case
- Shredder Bags: Uses #8000-50, case of 100

Warranty:

- Lifetime Limited Warranty on cutting head
- 1-Year Warranty on all other parts



Control Panel



Fully-Automatic AutoOiler for Optimal Performance

The Formax FD 8650CC AutoOiler Office Shredder features an automatic oiler that oils the cutting blades periodically for optimal performance.

The FD 8650CC is an office size shredder with industrial strength, and shreds up to 28 sheets at one time at speeds up to 30 feet per minute. The extra wide feed opening handles documents up to 16" wide and the large waste bin holds up to 53 gallons. These specifications make it an ideal centralized office shredder.

Commercial-grade features include an easy-to-use LED control panel with load indicator, heat-treated steel blades, a steel cabinet, lifetime guaranteed waste bin, and a powerful AC geared-motor ensuring years of reliable performance and information security in your office environment.

Specifications:

Cutting Style:	Cross Cut
Shred Size:	5/32" x 1 19/32"
Sheet Capacity:	26 to 28 sheets
Speed:	30 fpm
Dimensions:	28" W x 24" D x 43" H
Bin Capacity:	53 gal.
Weight:	317 lbs.
Security Level:	Level 3 (HIPAA Compliant)
Power Supply:	110V, 50/60 Hz 20Amp



AutoOiler - Automatically pumps oil onto the cutting blades