

### Standard Features:

- Multimedia Shredder: Two dedicated feed openings accept paper, CDs, DVDs, DV tape, ZIP/floppy disks, staples, paper clips and credit cards
- Auto Start/Auto Stop: Optical sensor detects paper and starts operation automatically
- LED Control Panel with Load Indicator
- Door Safety Sensor: Motor stops automatically if cabinet door is opened
- Auto Reverse: In case of paper jam, built-in controls switch motor into reverse to clear jam
- Heat-Treated Steel Cutters: Specially ground for longevity and require minimal oiling
- High Quality Geared Motor: Powerful, efficient AC geared-motor with heavy duty steel gears for high performance and minimal noise
- Continuous-Duty Motor for non-stop operation
- All-Metal Cabinet with casters
- Auto Sensor: When the waste bin is full, the motor stops automatically
- Lifetime Guaranteed Heavy-Duty Waste Bin
- Auto Cleaning: If shred capacity is decreased, press reverse button for 5 seconds and motor will run in reverse for 1 minute
- Oil Indicator: After every 4 hours of use, the control panel LED flashes to suggest oiling cutting blades for optimal performance
- Self-Diagnosis System: Records operation time, number of auto-reverse sequences, volume of paper shredded, and can display information for service technicians
- Thermal overload protection
- Safety Circuit Breaker ensures safe operation

### Options:

- EvenFlow™ Automatic Oiling System: Lubricates cutting blades for optimal performance
- Cutting Head Lubricating Oil: #8000-10, six 8-ounce bottles per case
- Shredder Bags: Uses #8000-40, case of 100

### Warranty:

- Lifetime Limited Warranty on cutting head
- 1-Year Warranty on all other parts



Control Panel



### Compact design, multimedia power

The Formax FD 8704CC Multimedia Office Shredder offers commercial-grade quality and unmatched features in a compact design ideal for the office environment. With two dedicated feed openings, the FD 8704CC is capable of shredding paper, CDs, DVDs, mini-DV tapes and ZIP/floppy disks.

Standard features include heat-treated steel blades, an easy-to-use LED control panel, lifetime guaranteed waste bin, and a powerful AC geared-motor. The optional EvenFlow™ Automatic Oiling System helps to keep the FD 8704CC in peak operating condition.

### Specifications:

Cutting Style:	Cross Cut
Shred Size:	5/32" x 1-5/8"
Sheet Capacity:	40 - 45 sheets*
Speed:	12 fpm
Feed Opening:	9.4"
Dimensions:	20" W x 20" D x 36" H
Bin Capacity:	28 gal.
Weight:	176 lbs.
Security Level:	Level 3 (HIPAA Compliant)
Power Supply:	110-120V, 50/60 Hz

\*Capacity varies depending on paper and power supply



Optional EvenFlow™  
Automatic Oiling System