




DuraSoak™ Series General Purpose Medium-Duty Pads



What's Inside:

DuraSoak™ General Purpose Absorbents start with excess material from our popular shop towels

Absorbs up to 30.3 gallons of oil per bale*


* per ASTM F726-06

- Made with 60% recycled shop towel fibers
- Meltblown-spunbond coverstock on both sides of the absorbent core creates very durable sorbent pads
- Absorbs both oil and water as well as grease, transmission fluid, hydraulic fluid, diesel fuel, coolants and many other fluids
- Durable coverstock on both sides of the pad provides greater strength than standard meltblown polypropylene pads
- Very stable pricing and does not have the volatile costs that are typically associated with oil based absorbents as they are made with recycled fibers
- Class A fire retardant when pad is dry (lab tested per ASTM E84)
- Ash content is 0.63% per ASTM D240
- 10,580 BTU/lb per ASTM D240
- U.S. Patent No. 8, 118, 117

Caution: Not intended for use with aggressive acids or caustics. Dispose of all sorbent materials in accordance with local, state and federal regulations.

Per Pad Comparison

Over 25% more absorbent than New Pig
MAT203 & over**
35% more absorbent than SPC* MRO100**




One pad of DuraSoak™ 23200 absorbs 0.303* gallons of SAE 30 motor oil vs. 1 pad of New Pig** MAT203 which adsorbs 0.241* gallons of SAE 30 motor oil and 1 pad of SPC*** MRO100 which adsorbs 0.22* gallons of SAE motor oil



DuraSoak™ Pads Outer Case

Absorbents



Durable meltblown spunbond coverstock on top of pads

Absorbent core made with Q-CEL® Technology

Durable meltblown spunbond coverstock on bottom of pads

Made in the U.S.A.

DuraSoak™ General Purpose Medium-Duty Pads

Product Number:	23200
Pad Size:	15" x 19"
Quantity Per Case:	100/box
Color:	Gray
Cases Per Pallet:	24 cases/pallet
TI:	6 cases/layer
HI:	4 layers/pallet
Case Dimensions:	Length: 20"
	Width: 16"
	Height: 23"
Case Weight:	16 lbs
Pallets Per Truck:	30
UPC:	660708232006
ITF-14:	60660708232008

*absorbency results were independently tested by SF Analytical Laboratories using ASTM method F726-06 using SAE 30 motor oil

**New Pig is a registered trademark of New Pig Corporation.

***SPC is a registered trademark of Brady Worldwide, Inc.

To order, contact your **Authorized Sellars® Distributor**

©2014 Sellars Absorbent Materials, Inc. 12.14



DuraSoak Series

General Purpose Absorbents


Sellers General Purpose TOOLBOX® DuraSoak™ pads not only provide more absorbency (see charts on individual product pages) than other popular competitive meltblown sorbents, they're made with recycled fibers (see chart) to create greater price stability. And with our recycled fibers being made from our internal excess wiper material, DuraSoak™ provides amazing product consistency.

4 Grades of Durasoak™




	AMOUNT OF RECYCLED FIBER	ABSORBENCY	DURABILITY
DuraSoak™ General Purpose Heavy-Duty	65%	■■■■■■■	■■■■■■■
DuraSoak™ General Purpose Medium-Duty	60%	■■■■■	■■■■■■■
DuraSoak™ General Purpose Light-Duty	65%	■■■	■■■
DuraSoak™ General Purpose Econo-Duty	75%	■■■	■■

General Purpose Pads



DuraSoak™ Heavy-Duty Absorbent Pads

Product Number:	23100
Pad Size:	15" x 19"
Quantity Per Case:	50/box




DuraSoak™ Medium-Duty Absorbent Pads

Product Number:	23200
Pad Size:	15" x 19"
Quantity Per Case:	100/box



DuraSoak™ Light-Duty Absorbent Pads

Product Number:	23300
Pad Size:	15" x 19"
Quantity Per Case:	100/box



DuraSoak™ Econo-Duty Absorbent Pads

Product Number:	23400
Pad Size:	15" x 19"
Quantity Per Case:	100/box

General Purpose Rolls



DuraSoak™ Heavy-Duty Absorbent Rolls

Product Number:	23150
Roll Size:	28.5" X 75'
Quantity Per Case:	1/box



DuraSoak™ Medium-Duty Absorbent Rolls

Product Number:	23250
Roll Size:	28.5" X 125'
Quantity Per Case:	1/box



DuraSoak™ Light-Duty Absorbent Rolls

Product Number:	23350
Roll Size:	28.5" X 150'
Quantity Per Case:	1/box



DuraSoak™ Econo-Duty Absorbent Rolls

Product Number:	23450
Roll Size:	28.5" X 150'
Quantity Per Case:	1/box

General Purpose Split Rolls



DuraSoak™ Heavy-Duty Absorbent Split Rolls

Product Number:	23160
Roll Size:	14.25" x 75'
Quantity Per Case:	2/box



DuraSoak™ Medium-Duty Absorbent Split Rolls

Product Number:	23260
Roll Size:	14.25" x 125'
Quantity Per Case:	2/box



DuraSoak™ Light-Duty Absorbent Split Rolls

Product Number:	23360
Roll Size:	14.25" x 150'
Quantity Per Case:	2/box



DuraSoak™ Econo-Duty Absorbent Split Rolls

Product Number:	23460
Roll Size:	14.25" x 150'
Quantity Per Case:	2/box