




Three duct tapes that do everything you need.

This trio can handle the full range of duct tape strengths needed to tackle any job. Multilingual, individually wrapped rolls are color-coded by performance level, and hand tearable for ease of use.

Right performance. Right price.



These three can do it all.



3M™ All Purpose Duct Tape DT 8

Holds to smooth metal, glass, plastic, sealed concrete and more.



8 mil thickness
Good adhesion
Good durability



3M™ Heavy Duty Duct Tape DT 11

The go-to tape for holding, seaming, sealing, repairing and packaging. Ideal for sticking to plastic



11 mil thickness
Great adhesion
Great durability



3M™ Super Duty Duct Tape DT 17

Super thick for super tough jobs including repairing, seaming, and protecting metal parts and surfaces.



17 mil thickness
Super adhesion
Super durability

Description	Thickness	3M ID	Packaging	Size	Color	Case Qty
3M™ All Purpose Duct Tape DT8	8 mil	70006775004	Ind. Wrapped	48 mm x 54.8 m	Silver	24
3M™ Heavy Duty Duct Tape DT11	11 mil	70006775012	Ind. Wrapped	48 mm x 54.8 m	Black	24
		70006775020	Ind. Wrapped	48 mm x 54.8 m	Silver	24
3M™ Super Duty Duct Tape DT17	17 mil	70006775038	Ind. Wrapped	48 mm x 32 m	Black	24

Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000

Phone 1-800-362-3550
Fax 1-877-369-2923
Web www.3M.com/tape

3M is a trademark of 3M Company.
© 3M 2016. All rights reserved.
70-0710-0470-2