

# INTERCEPTOR

## WIRELESS SPEAKER MICROPHONE WITH DUAL PTT FOR SMARTPHONE



Use the **INTERCEPTOR** Bluetooth wireless speaker microphone with your (POC) Push-to-Talk Over Cellular Apps. With 2 PTT (push-to-talk) buttons & simultaneous listen feature, you can pair to 2 different Bluetooth enabled devices (radio & smartphone) plus listen to dual audio from 2 Bluetooth devices at the same time.



### FEATURES & BENEFITS:

- ▶ Interceptor can be paired to two Bluetooth Devices simultaneously. Connect with these dual link pairs:
  - 2 two-way radios with BlueWi Bluetooth adapters.
  - 1 Smartphone & one two-way radio with BlueWi Bluetooth adapter/dongle.
  - 2 Bluetooth Smartphones
- ▶ Listen to dual audio from two paired Bluetooth Devices at the same time.
- ▶ POC (Push-to-Talk Over Cellular) Compatible.
- ▶ Newly upgraded firmware allows the Interceptor to pair to radios with built-in Bluetooth without the need of an external Bluetooth adapter dongle.
- ▶ The incoming audio from the two sources are completely blocked, preventing information leakage.
- ▶ Uni-directional microphone, 128-Bit Encryption, 20+ Hour Talk Time.
- ▶ 3.5mm audio jack for field versatility.



**DUAL AUDIO MERGE LISTEN AND SEPARATE TALK FUNCTION**  
Listen to dual audio from 2 paired Bluetooth devices at the same time. Transmit outgoing communication to 2 talk groups by separate PTT control.



MIC TYPE	OMNI-DIRECTION MIC WITH DSP NOISE AND ECHO CANCELLATION	INTERCOM DISTANCE	100 METERS
BLUETOOTH VERSION	V3.0 CLASS 1	CHARGE TIME	APPROX. 4 HOURS
BLUETOOTH PROFILE	HSP, HFP, A2DP, AVRCP, SPP	TALK TIME	APPROX. 20 HOURS
BLUETOOTH ENCRYPTION	128-BIT KEY ENCRYPTION	STANDBY TIME	ABOUT 80 HOURS
FREQUENCY RANGE	2402MHz~2480MHz	OPERATING TEMP	-15° ~50°C
ANTENNA IMPEDANCE	50 Ohm	STORAGE TEMP	-25° ~60°C
RADIO POWER GRADE	BLUETOOTH CLASS 1 (MAX RF POWER MORE THAN 6DBM LESS THAN 20DBM)	BATTERY	LI-POLYMER BATTERY(1500MA/3.7V)
RF RECEIVER SENSITIVITY	-80DBM		