

# AL650



32" x 23.63" x 23.5" (H x W x D)

Freestanding ADA compliant refrigerator-freezer for general purpose use, with dual evaporator cooling, cycle defrost, and white exterior

## Highlights:

32" height for use in ADA compliant settings

Improved temperature performance with our unique dual evaporator cooling

Door racks provide convenient storage options

Over 5 cu.ft. of storage capacity in a perfectly sized 24" footprint

## Product Features:

Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
ADA compliant	32" height for use in settings complying with ADA guidelines for lower counter height
Fully finished white cabinet	Allows the unit to be used freestanding
Zero degree freezer	Stable interior allows you to store sensitive items under reliable freezer conditions
Dual evaporator	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators
Reversible door	User-reversible door swing for added flexibility
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Door storage	Store large bottles right on the door for easy access
Clear crisper	Get the longest life and best taste out of produce by storing in a convenient slide drawer

**AL650 Specifications:**

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with Handle	24.25"
Depth with door at 90°	45.13"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	White
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs.
Shipping Weight	102.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	19.5"
Refrigerator - Interior Width	20.5"
Refrigerator - Interior Depth	17.0"
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	3
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.0"
Freezer - Interior Width	19.0"
Freezer - Interior Depth	11.5"
Adjustable Shelves	Yes
Thermostat Type	Dial
Freon	R134a

Freon Amount	2.6
High Side PSI	285.0
Low Side PSI	70.0
Level Legs	2
Compressor Step Height	7.0"
Compressor Step Width	20.5"
Compressor Step Depth	5.0"

