

## **ENGINEER AND ARCHITECT SPECIFICATION**



# Solaira SMaRT 60 Minute Timer

#### **Push button 1-60 Minute Timer**

User settable 1 - 60 minute time increment Offers energy savings for Infrared Heaters when there is no one in the zone

## Control up to 6.0kW Infrared Heaters

4 and 6 kW Options provide flexible installation Options

## Soft Start Technology

Engineered feature extends emitter life by up to 30%

## Water Resistant Enclosure Design

For Outdoor or Indoor Applications

#### **SOLAIRA SMaRT 40 and 60 Push Button Timer**

SPE-1000 listed

Solaira SMaRT 40 and 60 Push Button Timers are part of a family of water-resistant Solaira SMaRT controllers designed to provide energy saving when used with infrared heaters or other heating and lighting products. These models switch the heaters on for a predetermined time period of between 1 and 60 minutes.

The microcontroller-based unit incorporates zero-voltage switching and a soft-start function to eliminate the heaters initial high inrush current, potentially increasing heater emitter life by as much as 30%. The heaters are switched on for a user-settable time period of between 5 and 60 minutes. Installation of the unit is simple and once our solid state controller is installed it is relatively maintenance-free.

#### SMaRT PUSH BUTTON DESIGN

SMRTTIM40 Maximum 4.0kW, 208-240V - 2 X 1.5 kW.208/240 or 2 X 2.0 kW.208/240 or 1 X 3.0 or 4.0kW. 208/240 SMRTTIM60 Maximum 6.0kW, 208-240V - 4 X 1.5 kW,208/240 or 4 X 2.0 kW,208/240 or 2 X 3.0 kW, 208/24 or 1 X 6.0 kW, 208/240

### **TECHNICAL SPECIFICATION**

Part #	Voltage	Max Heater Watt	Load	User set On-Time
SMRTTIM40	208-230V	4.0kW	16.6 A	1-60Minute
SMRTTIM60	208-230V	6.0kW	25 A	1-60Minute

**Enclosure Dimensions:** 5-1/8" X 5-1/8"X 3" (130x130x75 mm)

**Enclosure Operating Temperature Range:** -4°F (-20°C) to 104°F 40°C

UL94 certified Resin Enclosure, IP65 Water Proof for outdoor/indoor use Enclosure/Protection Rating:

cETL SPE-1000, CE Certification

#### SOLAIRA SMART PUSH BUTTON TIMER 40 and 60 SUBMITTAL

JOB NAME		JOB LOCATION	
ARCHITECT		ENGINEER	
CONTRACTOR		SUBMITTED BY	DATE
ITEM SPEC	QTY	CONTROLS	

Solairatm -Inforesight Consumer Products Inc,

125 Traders Blvd #4, Mississauga, Ontario US DC: Inforesight c/o Benlin 2769 Broadway Blvd, Buffalo, NY 14227 Canada: Phone: 866-321-8373 local 905-568-7655 Fax: 905-568-7521 web: www.solairaheaters.com email: info@solairaheaters.com