



This medium-duty commercial microwave features the durable quality and easy maintenance of a stainless steel interior. The cost-efficient R-21LCF also has a super-rugged grab handle.

Features:

Stainless Steel Interior and Door are designed with a high-grade stainless steel that is featured in every oven in Sharp's commercial line. They're easy to clean and resists pitting, chipping, scratching and erosion, even with a tough schedule of everyday use.

Cool Gray Cabinet and Stainless Door provide a streamlined, style-setting look that suits any situation — from snack bars to offices.

Dependable 6-Minute Light Up Dial Timer is clearly marked in 10, 15 and 30 second increments for easy-to-set, easy-to-read convenience. When the door is opened during cooking, the remaining time is canceled eliminating the oven being on without a food load. Increments are lettered for use with coded foods.

1,000 Watts of Power built for fast, efficient heating.

Heating Time Guide charts proper times needed to heat a variety of popular foods. It's a handy "on-the-spot" reference for timesaving convenience.

Sturdy Grab Handle designed to stand up to the daily demands of the medium-duty user, providing easy access.

End of Heating Signal lets user know when food is ready.

Interior Oven Light lets you view food as it cooks to monitor progress. See-through door and oven light promote maximum visibility.

Ease of Cleaning of the rubber-sealed ceramic shelf makes it easy to keep oven in "ready-for-inspection" order.

Specifications

Model	R-21LCF
Output Wattage (IEC Procedure)	1000 watts
Stainless Steel Interior	Yes
Cool Gray Cabinet & Door	Yes
Power Requirements	1.6 kW, 14.0 A
Receptacle Required	15 Amp., NEMA -15 R
Cord Length (in inches)	63
Warranty*	Sharp commercial microwave ovens have a reputation for unsurpassed quality in the foodservice industry. This Sharp commercial microwave oven is backed by a three-year limited warranty on the magnetron tube and one-year warranty on parts and labor with service provided in the end-user's place of business. See Operation Manual for complete details.
Outside Unit Dimensions (w x h x d, in inches)	20-1/2 x 12-1/8 x 16
Outside Unit Dimensions with Door Open (in inches)	31-1/4
Cavity Dimensions (w x h x d, in inches)	13-7/8 x 8-1/8 x 14-5/8
Net Weight / Shipping Weight (in pounds)	37 / 44
UPC	074000616493

*1 See warranty statement included in the product operation manual available as a PDF download at www.sharppusa.com.

Sharp and all related trademarks are trademarks or registered trademarks of Sharp Corporation and/or its affiliated companies.

All other trademarks are property of their respective owners.

Design and specifications subject to change without notice. See operation manual for complete details.

To Specify a Sharp R-21LCF Medium-Duty Commercial Microwave Oven - Oven shall comply with standards set by the U.S. Department of Health and Human Services, FCC, NSF-4 and UL and shall display such labels. Oven shall be equipped with 6-minute Light Up Dial timer marked in 10, 15 and 30 second increments. Remaining time will be canceled if the door is opened during cooking. Heating Time Guide and instructions shall be visible on oven control panel. Output wattage shall be 1000 watts. Bottom feed distribution system shall provide uniform heating pattern. Oven cavity shall be of stainless steel construction with see-through stainless oven door. Cavity shall be illuminated. Bottom of cavity shall consist of rubber-sealed ceramic shelf. Oven shall have three-year limited warranty on the magnetron tube; one-year parts and labor with service provided in the end-user's place of business.



Built to meet rugged commercial standards.
Complies with DHHS & FCC.

SHARP ELECTRONICS CORPORATION

Sharp Plaza, Mahwah, NJ 07495-1163

For more information call: 201-529-8619 or 1-800-BE-SHARP

www.sharppusa.com