



SPARE PARTS CATALOG



ACE SERIES BREWERS



TS

ACE SERIES

Glass Bowl & Thermal Brewing Systems

TABLE OF CONTENT

Base Assemblies	Pages 3 - 5
Cover Assemblies	Pages 6 - 7
Tank Assemblies	Pages 8 - 13
Micro Switch & Bracket Assemblies	Page 14
Valve & PDS Assemblies	Pages 14 - 15
Miscellaneous Components	Pages 16 - 22

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION		UM
Base Assemblies				
102842-B		<i>Base Assembly, 3 Station Black ACE [LP Model Only]</i>	1	EA.
102795-B		<i>Base Assembly, 1 Station Black ACE [S Model Only]</i>	1	EA.
110385		<i>Base, LDR 8.5" Wide Black [TC, AP, LD, TD, & TS Models Only]</i>	1	EA.
100003		Snap On Bushing, 3/4" Black Plastic	1	EA.
100010		Warming Plate Assembly Black	1	EA.
100008		Porcelain Plate, Black With Studs	1	EA.
100054		#8 Lock Washer, External Tooth SS	1	EA.
100061		8-32 Nut, Hex SS	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	
Base Assemblies - Continued				
100086		Support Plate, Warming Element	1	EA.
100187		Warming Element, 100W 120V Short [Recommended Stocking Part]	1	EA.
100078		Bumper Foot With Screw	1	EA.
100160		Screw, 4-40 x 5/8" SPHMS SS	1	EA.
100254		Decal, Warning "Hot Surface"	1	EA.
100316		T-100 Base [LP Model Only]	1	EA.
102792		Base, Top 1 - Station Blank ACE [S Model Only]	1	EA.
102333		Screw, Combo Head 6-32 x 3/8 SS [LP Model Only]	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	
Base Assemblies - Continued				
102811		Base Top, 3 Station Blank [LP Model Only]	1	EA.
102814		Base Bottom, 3 Station Spot Welded [LP Model Only]	1	EA.
102794		Base Bottom, Blank 1 Station ACE [S Model Only]	1	EA.
102826		Face Plate, Base 3 Station SS [LP Model Only]	1	EA.
102826-B		Face Plate, Base 3 Station Black [LP Model Only]	1	EA.
102825		Face Plate, Base 1 Station SS [S Model Only]	1	EA.
102825-B		Face Plate, Base 1 Station Black [S Model Only]	1	EA.
102845		Plate, Louver 3 Station Base Stove [LP Model Only]	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	
Covers				
102789		<i>Cover Plain, ACE Model</i> <i>[AP, LD, LP, TC, TD, & TS Models Only]</i>	1	EA.
102791-B		<i>Cover Assembly, 2 Station Step Up Black</i> <i>[S Model Only]</i>	1	EA.
100003		Snap On Bushing, 3/4" Black Plastic	1	EA.
100010		Warming Plate Assembly Black	1	EA.
100008		Porcelain Plate, Black With Studs	1	EA.
100054		#8 Lock Washer, External Tooth SS	1	EA.
100061		8-32 Nut, Hex SS	1	EA.
100086		Support Plate, Warming Element	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	UM
Covers - Continued				
100187		Warming Element, 100W 120V Short [Recommended Stocking Part]	1	EA.
100160		Screw, 4-40 x 5/8" SPHMS SS	1	EA.
100254		Decal, Warning "Hot Surface"	1	EA.
102333		Screw, Combo Head 6-32 x 3/8 SS	1	EA.
102790		Cover Only, 2 Station Step Up Blank [S Model Only]	1	EA.
705370		NK Stove 2 Station Cover [S Model Only]	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	UM
Tank Assemblies				
102798		<i>Tank Assembly, ACE 1400W 120V [LP, S, & TC Models Only]</i>	1	EA.
102859		<i>Tank Assembly, ACE 1750W 120V [AP, LD, TD, & TS Models Only]</i>	1	EA.
100030		Gasket, Brass .566ID Tinplated	1	EA.
100043		Thermostat Knob (102299)	1	EA.
100054		#8 Lock Washer, External Tooth SS	1	EA.
100061		8-32 Nut, Hex SS	1	EA.
100135		Bulkhead Fitting, Outlet	1	EA.
100149		Male Elbow, 1/4C x 1/8NPT S&N	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	
Tank Assemblies - Continued				
100166		Sleeve, 3/8" Compression Brass [Inlet & Spray Head Tube]	1	EA.
100170		Nut, 3/8" Compression Brass [Inlet & Spray Head Tube]	1	EA.
100190		Jam Nut, 1/2 - 20 Brass	1	EA.
100209		Capillary Clip, Thermostat	1	EA.
100212		Washer, #6 External Lock SS [Thermostat]	1	EA.
100269		Hi Limit Thermostat Bracket	1	EA.
100409		Gasket Brass, .520 ID Tinplated	1	EA.
100431		Nut, Brass 9/16-24 x 11/16 Hex Tinplated	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	
Tank Assemblies - Continued				
100440		Hose Clamp, LP Brewers	1	EA.
102580		Heating Element, 1400W 120V [LP, TC, & S Models Only] [Recommended Stocking Part]	1	EA.
100071		Heating Element, 1750W 120V [AP, LD, TD, & TS Models Only] [Recommended Stocking Part]	1	EA.
102797		Tank Only, ACE Faucet	1	EA.
102831		Connector Fitting, Female 3/8C x 1/8NPT	1	EA.
102835		Bulkhead Fitting, Faucet Outlet Tinplated	1	EA.
102874		Silicone Tubing 3/8" x 5/8" x 9.00" [152213]	1	EA.
108104		Thermostat Bracket, Main ACE	1	EA.





ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	UM
Tank Assemblies - Continued				
108248		Adaptor Fitting, 1/4NPS x 3/8 Tube	1	EA.
110507		"O" Ring, 1/4" x 3/8" OD x 1/16" Wall Silicone	1	EA.
110595		Silicone Vacuum Breaker	1	EA.
110666		Screw, 6-32 x 1/4 " PPHMS SS [Thermostat]	1	EA.
111105		Nipple, Fitting VIP Silicone	1	EA.
111593		Manual Thermostat Vertical Tab 221F 25A [Recommended Stocking Part]	1	EA.
111635		Hose Clamp, .574 ID	1	EA.
120729		Tank Clip, ACE - FC Brewers	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	
Tank Assemblies - Continued				
152198		Lead Wire, 14GA Violet - Black 4" Teflon 1S - 1S	1	EA.
152701		Tube, SS 3/8 x .028 x 2.0 x 5.53 x 90 Degrees	1	EA.
201112		Brass Insert, 1/4 ID Tube Tinplated	1	EA.
201178		Male Adaptor, Double .250	1	EA.
701942		Silicone Tubing, 1/4 " x 3/8" x 5.25" [152218]	1	EA.
704215		Thermostat, Main I/H KP121524 4.78 [Recommended Stocking Part]	1	EA.
781181		Silicone Gasket, Tank 23"	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	UM
Tank Assemblies - Continued				
104012		<i>Tank Lid Assembly, ACE</i>	1	EA.
500354		Probe 1.537" Passivated	1	EA.
152207		Plug, Tank Cover Silicone Natural	1	EA.
500038		Silicone Grommet, No Slit .060	1	EA.
121848		Lid Only, Punched With Vent Hole	1	EA.
500396		Probe Assembly, 1.537" With Bushing	1	EA.
500350		Grommet, Probe Bushing 5/16"	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION		UM
Micro Switch & Bracket Assemblies				
102862		<i>Micro Switch & Bracket Assembly</i>	1	EA.
100160		Screw, 4-40 x 5/8" SPHMS SS	1	EA.
102807		Micro Switch Bracket Assembly	1	EA.
102841		Micro Switch With Offset [Recommended Stocking Part]	1	EA.
Valve & PDS Assemblies				
108404		<i>Valve & PDS Assembly ACE - IA</i>	1	EA.
108425		Valve Assembly, No Flow Washer [Recommended Stocking Part]	1	EA.
100296		Cap, Flow Control Compression	1	EA.
100442		Male Elbow, 1/4F x 3/8NPT Tinplated	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	
Valve & PDS Assemblies - Continued				
102780		Solenoid Valve, S-45 [Recommended Stocking Part]	1	EA.
790019		Flow Control Gasket, Nylon	1	EA.
110322		PDS Valve Assembly, Low Flow ACE	1	EA.
700904		Tubing, Copper 1/4" X .030 X 1.75"	1	EA.
110305		PDS Valve Assembly Only, Low Flow Flare - Plug [Recommended Stocking Part]	1	EA.
201158		Solenoid Repair Kit [102780] [Recommended Stocking Part]	1	EA.









ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	
Miscellaneous Components				
100003		Snap On Bushing, 3/4" Black Plastic	1	EA.
100022		Power Cord, 14/3 120V 15A	1	EA.
100024		Spray Head, SS 5 Hole [Recommended Stocking Part]	1	EA.
100025		Spray Head Gasket	1	EA.
100054		#8 Lock Washer, External Tooth SS	1	EA.
100061		8-32 Nut, Hex SS	1	EA.
100085		Lighted On - Off Switch, 120V [Recommended Stocking Part]	1	EA.
100153		Tube, Ace Back Compression	1	EA.









ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	
Miscellaneous Components - Continued				
100164		Sleeve, 1/4" Compression	1	EA.
100165		Nut, 1/4" Compression	1	EA.
100254		Decal, Warning "Hot Surface"	1	EA.
100500		Rocker Switch, On - Off Black [Recommended Stocking Part]	1	EA.
100557		Line splice .250 22 - 10 Gauge	1	EA.
101011		Washer, 1/2" External Tooth SS	1	EA.
101035		Grommet, Strain Relief 14/3	1	EA.
102333		Screw, Combo Head 6-32 x 3/8 SS	1	EA.



ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	
Miscellaneous Components - Continued				
102770		Faucet With Red Handle, ACE [Recommended Stocking Part]	1	EA.
102775		Lamp, "Ready" - Green / "Brew" - Amber 120V [Recommended Stocking Part]	1	EA.
102783		Spray Head Tube, ACE	1	EA.
102799		Right Hand Brew Rail - ACE	1	EA.
102800		Left Hand Brew Rail - ACE	1	EA.
102864		Screw, 6-32 x 1/4" SFHMS (U/C)	1	EA.
105043		Washer, 6-32 x 3/8" PPHMS SS	1	EA.
108160		Label, Face Plate Warmer ACE [LP & S Models Only]	1	EA.









ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	UM
Miscellaneous Components - Continued				
108155		Label, Face Plate Thermal [AP, LD, TC, TD, & TS Models Only]	1	EA.
110965		Washer, #6 Internal Tooth	1	EA.
110985		Brew Basket Assembly, BW MOD VAC black [Recommended Stocking Part]	1	EA.
121723		Control Board Assembly, Super ACE [Recommended Stocking Part]	1	EA.
201112		Brass Insert, 1/4 ID Tube Tinplated	1	EA.
201173		Spray Head Nut, 7/16 - 20 SS	1	EA.
201178		Receptacle Adaptor, Double .250	1	EA.
201985		Start Switch, Black [AP, LD, LP, S, TC, & TD Models Only] [Recommended Stocking Part]	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	
Miscellaneous Components - Continued				
511027		Screw, 8-32 x 3/8" SPHMS SS	1	EA.
700904		Tubing, Copper 1/4" X .030 X 1.75"	1	EA.
100275		Screw, 6-32 x 3/16" SS [TS Model Only]	1	EA.
100284		Plastic Tie Wrap, 5 3/4" [TS Model Only]	1	EA.
100571		Screw, Combo Head 8-32 x 3/8" [TS Model Only]	1	EA.
102618		Cover, Solenoid Valve - ACE	1	EA.
102884		Lamp, "Heating" - Red/ "Brew" - Amber [TS Model Only] [Recommended Stocking Part]	1	EA.
104015		Bezel Adaptor, Plastic Black [TS Model Only]	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	
Miscellaneous Components - Continued				
105110		Screw, 6-32 x 3/8" Combo Black Zinc [TS Model Only]	1	EA.
108045		Momentary Switch, Red STDP [TS Model Only] [Recommended Stocking Part]	1	EA.
110359		Screw, #8 x 1/2" PPHZPS Hi - Lo [TS Model Only]	1	EA.
110626		Rocker Switch, Rectangular DP/ST [TS Model Only] [Recommended Stocking Part]	1	EA.
111725		Control Board Assembly, Tele ACE [TS Model Only] [Recommended Stocking Part]	1	EA.
120755		Tank Shelf Assembly, Tele ACE [TS Model Only]	1	EA.
120774		Barrier, Control Board Tele ACE [TS Model Only]	1	EA.
152164		Washer, .218 ID x .562 OD SS [TS Model Only]	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ITEM #	IMAGE	DESCRIPTION	UM	UM
Miscellaneous Components - Continued				
700021		Nut, Knurled Brass 8-32 [TS Model Only]	1	EA.
701799		Terminal, Connect QC .250	1	EA.
781843		Power Cord, 14/3 120V 15A With Shrink [TS Model Only]	1	EA.
726308		Adaptor, Double Tab .250 - Brass [TS Model Only]	1	EA.
500041		Positive Lock Receptacle Insulator [Used On Micro Switch]	1	EA.
500382	NA	Probe Assembly Kit, 1.537" [Consists of: 1 ea. 500350, Probe Assy., & Instruction]	1	EA.
103785		Hex Nut, 4-40 Nylon Insert SS [Used On Micro Switch]	1	EA.

ACE SERIES

Glass Bowl & Thermal Brewing Systems

ACE SERIES

Glass Bowl & Thermal Brewing Systems