

PECO remote sensors are highly accurate and stable. Enclosures are provided for both indoor and outdoor mounting. A remote probe allows the sensor to be placed in duct work or spaces where temperature sensing is desired.

Outdoor Sensor	PECO 70327 outdoor sensor can be used with most any PECO thermostat. This high quality outdoor remote temperature sensor has a weather-resistant cover for reliable performance in every climate. It also provides easy mounting in a small compact design.
Remote Probe	PECO 68671 remote probe sensor can be used with most any PECO thermostat. It is used to sense temperatures in duct work or other locations.
Indoor Sensor	PECO SP155 indoor sensor can be used with most any PECO thermostat. The Indoor sensor can be placed for optimal temperature sensing, allowing the thermostat to be located for convenience, or control of use by the inhabitant.

Sensors

Specifications			
	70327	68671	SP155-017
	Outdoor Sensor	Probe	Indoor Sensor
Operating Temperature Range	-40° to 122° F (-40° to 32° C)	-22° to 220° F (-30° to 105° C)	0° to 120° F (-18° to 49° C)
Dimensions	1" x 2.2" X 1.2"	Tip: 0.25" x 1.20"	2.8" x 4.5" x 1"
	or	6.1 cm x 3.0 cm	or
	2.6 cm x 5.5 cm x 3.1 cm	Lead: 60" (or 152.4 cm)	7.1 cm x 11.4 cm x 2.5 cm
Sensor Value	10KOhm NTC type 2	10KOhm NTC type 2	10KOhm NTC type 2
	@ 25°C / 77°F	@ 25°C / 77°F	@ 25°C / 77°F

Technical Data

Accessory Models		
Model	Part No.	Description
70327	70327	Outdoor remote sensor.
68671	68671	Probe remote sensor.
SP155-017	69308	Indoor sensor.

Other Accessories & Models

Model	Part No.	Description
SC500-001	70452	CO2 sensor Coming Soon
SA200-001	68374	Occupancy sensor: ceiling-mounted.
SB200-001	68375	Occupancy sensor: wall-mounted, time based.
SK200-001	68381	Occupancy sensor; guest room.
70210	70210	Protective locking cover. Key security for T4000 series thermostats.
70481	70481	SD memory card for use in Performance PRO Series T8000, T12000 & School Stat.
70499	70499	USB / SD reader.







Automation & Controls Division of PECO, Inc. Portland, OR 97282

800-874-8547

sales@PECOmanufacturing.com www.PECOmanufacturing.com

DS-AccSen11/11 © PECO, Inc. 2011