

Powerful coil cleaning with the **Condenser Needle**® from SpeedClean®

Powerful coil cleaning from the inside out. Blast dirt, debris and grime from condenser coils without damaging sensitive fins with the Condenser Needle® from SpeedClean®. Designed to clean from the inside of the coil, Condenser Needle comes with everything you need to get started.



Simply attach to a standard water hose and deliver a powerful 90° stream of water and chemical cleaner - up to 3 gallons per minute. It also includes an adjustable chemical injection hose for use with SpeedyFoam™, an acid free, foaming coil cleaning solution that works great. Now that's smart.



Clean from the inside, out

All-access 90° spray tip

Spray up to 3 GPM

- Connects to standard garden hose
- Forces dirt and debris back in the direction it entered - a proven technique for increasing coil cleaning and system efficiency
- 90° spray wand and 3 gallon per minute flow blasts dirt and grime, won't damage fins and virtually eliminates electrical tripping issues
- Fits easily through the top of most condenser units, no more hassling to remove the top of the unit
- Includes heavy duty spray gun with garden hose connector, 3' spray wand and chemical injection tube



SPEEDCLEAN™

Condenser Needle from SpeedClean

Additional cleaning solutions



CoilJet®:

For the most complete coil cleaning solution, consider adding the CoilJet from SpeedClean. This all-in-one portable solution cleans condenser and evaporator coils in hard to reach places without the need for water hoses or electrical outlets. The CoilJet® offers a powerful, battery powered coil cleaner that can be used virtually anywhere.

Part No: CJ-125



SpeedyFoam®:

Safer, more effective and works great. Designed for use with CoilJet and Condenser Needle, SpeedyFoam acid-free coil cleaner delivers superior cleaning power without the harsh effects that other caustic alkaline cleaners have.

Part No: SC-FCC-1



FlowJet™:

High flow, continuous cleaning. The FlowJet from SpeedClean with chemical injection, makes quick work of cleaning debris and grime from microchannel and thick condenser and evaporator coils. Now deliver professional results in a compact, portable solution.

Part No: FLOWJET-60



BucketVac®:

New from SpeedClean, the BucketVac turns any standard 5 gallon bucket into a powerful, portable commercial grade wet/dry vacuum. Easily switch between wet and dry, or add extra capacity for a big job by snapping onto a new bucket.


Part No: BV-5

Visit www.speedclean.com for a complete list of accessories.

Specifications

Part Number:	CN-03
Dimensions (H x W x D):	48" x 3" x 3"
Weight:	5 lbs
Output Pressure:	100 PSI at 3.3 GPM
General Warranty:	1 Year
Patent:	D624,718

Features



Distributed by:



SPEEDCLEAN™

SpeedClean, 404 West Ave, Stamford, CT 06902 • 1-888-700-3540

www.speedclean.com