

Super Concentrated Floor Stripper

Super Concentrated Floor Stripper offers maximum speed and effectiveness when stripping floors. Removes all types of water-based finishes and sealers used on resilient tile, terrazzo, brick, quarry tile, and stone flooring. Powerful penetrating agents cut through and emulsify heavy buildups and remove multiple coats of finish on the first pass. Ideal to use on floors that have been repeatedly high speed buffed and propane burnished. No ammonia odor. No caustic.

DIRECTIONS

Read the entire label and SDS for proper use, handling and storage before using this product.

Test for colorfastness using diluted solution in an inconspicuous area. Wear appropriate PPE. Dilute solution with any temperature of water. Recommended dilution ratio of stripper to water: 1:26 (1 quart bottle in 5.2 gallons of water). For extreme buildups, increase strength of solution.

1. Liberally apply diluted solution to floor. Do not allow floor to dry. Reapply stripping solution as needed to keep floor wet.
2. Allow solution to remain on floor until the finish has become loosened and can be removed from floor.
3. Scrub floor with machine and pick up residue from floor. Do not allow loosened material to dry on floor.
4. Rinse floor prior to recoating. Use of a neutralizing solution in the final rinse will ensure better bonding and performance of future floor coatings.
5. Reapply Super Concentrated Floor Stripper and/or finish in normal manner.

USE WITH GLOBAL FLOOR CARE MACHINES

- 261990 - Global Industrial™ Electric Auto Floor Scrubber 20" Cleaning Path - Corded
- 641244 - Global Industrial™ Auto Floor Scrubber 20" Cleaning Path, Two 115 Amp Batteries
- 641245 - Global Industrial™ Auto Ride-On Floor Scrubber 34" Cleaning Path, Three 170 Amp Batteries
- 641250 - Global Industrial™ Electric Auto Floor Scrubber 18" Cleaning Path - Corded
- 641251 - Global Industrial™ 17" Floor Machine
- 641252 - Global Industrial™ 20" Floor Machine
- 641253 - Global Industrial™ 20" Floor Machine, Dual Speed
- 641263 - Global Industrial™ Auto Floor Scrubber 18" Cleaning Path, Two 115 Amp Batteries
- 641264 - Global Industrial™ Auto Floor Scrubber 20" Cleaning Path, Two 115 Amp Batteries
- 641265 - Global Industrial™ Auto Floor Scrubber 26" Cleaning Path, Two 115 Amp Batteries
- 641310 - Global Industrial™ 20" Floor Burnisher
- 641311 - Global Industrial™ 20" Floor Burnisher W/ Dust Control



GLOBAL FACTS

- Super concentrated - ultra high active ingredients
- Convenient 1 quart packaging
- Powerful - removes multiple layers and buildups of finishes, sealers, and burnished coatings
- Fast and effective; speeds up the stripping process

MARKETS

- Building Service Contractors
- Retail
- Education
- Healthcare
- Hospitality & Lodging

SPECIFICATIONS

Color	Clear
Scent	Solvent
pH	11.0 - 12.5
Viscosity	Water Thin

REORDER

640405 6x1 Quarts/Case

COMPARE TO

Global Catalog	Floor Science Floor Strip (B260547)
Global Catalog	Simoniz Ultra Line Strip (B639147)
Global Catalog	Simoniz Zip Strip (B639253)
Global Catalog	Franklin Offense (B56839/B56840)
Global Catalog	Franklin Once Over (B850388)
Betco	Extreme Ultra
Diversey	Bravo
Spartan	Emulsifier Plus

Global Industrial
2505 Mill Center Parkway, Buford, GA 30518
800-645-1232 • www.globalindustrial.com
Refer to SDS for more information.