



INSTALLATION MANUAL

MODEL 1218 ACCESSORY QUICK CLAMP

- ATTENTION -

Read and understand all instructions and warnings before installing and using this product. Confirm contents of the shipping carton with the "Parts IDENTIFICATION" page before beginning installation. If a part is missing, or if you have any questions, please call WEATHER GUARD® customer service at 1-800-456-7865.

▲ WARNING

This product is only intended for, and only safe for, transporting ladders, lumber, pipe and other similar materials. It is the responsibility of the user to secure these materials to the rack before transporting. Any modifications made to this product, or use of this product for any other purpose than its intended use, could create a hazardous condition that can cause serious personal injury or property damage.

Ladders must be secured per ANSI standard A142.2-1990 paragraph 8.4.4. Ladder damage will occur from road shock and vehicle vibration if the ladder is not properly secured to the ladder rack. Bouncing and side to side motion of a improperly secured ladder will cause wear and weaken the ladder. Using a damaged ladder could lead to a structural collapse and could result in a serious injury or death.

- NOTICE -

Any modification or unintended use of this product shall immediately void all manufacturers warranties. Manufacturer disclaims all liability for injuries to persons or property resulting from any modification to, or unintended use of this product.

Some vehicle manufacturers require a reinforcing kit, available through the vehicle dealership, to be installed on the truck bed prior to mounting any kind of rack or tool box. Contact your dealership to see if your vehicle requires a reinforcing kit before installation.

A CAUTION

Never load your rack to exceed the safe capacity of your vehicle. Heavy loads when carried high can dangerously alter the center of gravity of your vehicle. Consult your vehicle owners manual for specifications on load ratings and recommendations from the vehicle manufacturer regarding installation of aftermarket racks and tool boxes.

Approximate Assembly and Installation Time: 10 min. depending on truck equipment installation experience.

LIMITED WARRANT

This LIMITED WARRANTY is made by Knaack LLC, 420 E. Terra Cotta Ave., Crystal Lake, Illinois to the original retail purchaserof KNAACK® or WEATHER GUARD® Equipmentproducts.

KNAACK LLC WARRANTS TH AT KNAACKOR WEATHER GUARD EQUIPMENT WILL BE FREE FROM DEFECTS IN MATERIAL ANDWORK MANSHIP FOR A PERIOD OF TWO (2) YEARS FROM DATE OF PURCHASE BY THE ORIGINAL RE TAIL PURCHASER.

If, before the expiration of the Warranty period, purchaser discovers that the KNAACK or WEATHER GUARDEquipment fails to fulfill the Warranty, purchaser shall contact Knaack LLC to make arrangements for aninspection of the product. If Knaack LLC determines a defect exists, Knaack LLC shall, at its option and expense, repairor replace any defective part. All Warranty repairs shall be made by an authorized KNAACK Equipment dealer or Knaack LLC approved service company.

This Warranty shall not apply if the KNAACK or WEATHER GUARD Equipment has been subjected to misuse, abnormal service or handling, improper maintenance, or alterations made by anyone other than a KNAACK or WEATHER GUARD Equipment dealer or a Knaack LLC approved service company.

THE WARRANTY PRINTED ABOVE IS THE ONLY WARRANTY APPLICABLE TO THIS PURCHASE. ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY ANDFITNESS FOR A PARTICULAR PURPOSE ARE HERE BY DISCLAIMED.

KNAACK LLC SHALL NOT BE LIABLE FOR ANY INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF ANY BREACH OF THIS WARRANTY. NOR SHALL THE DAMAGES EXCEED THE RETURN AMOUNT OF THE PURCHASE PRICE PAID BY THE ORIGINAL PURCHASER. This Warranty is in lieu of all Warranties express or implied. The terms of this Warranty shall not be modified by any party, their successors or assigns. This Warranty gives you specific legal rights, and you may also have other rights which vary from state to state.

WEATHER GUARD® products are protected by one or more of the following patents or trademarks: U.S. -4509787, 842268, 1661625, 1663369, 2228051, 2434963, U.K. -1400720; NZ-296049; Aus. -761964: Canada-1218968, 282725.

KNAACK LLC

420 E. TERRA COTTA AVENUE, CRYSTALLAKE, ILLINOIS, USA 60014 815-459-6020, info@knaack.com ©2003 Knaack LLC






TOOLS REQUIRED

3/8" Drive Ratchet 3/8" Drive Socket 1/2" Deep Well

PART IDENTIFICATION




Part Y (Qty. 2) Universal Quick Clamp

IMPORTANT!

ONLY OPERATE VEHICLE WITH REAR CROSS MEMBER IN PLACE



DO NOT OPERATE VEHICLE WITH REAR CROSS MEMBER REMOVED



A CAUTION


Quick clamps must be tight before operating vehicle.


INSTALLATION

STEP ONE

Remove the four 5/16 X 3" carriage bolts from both the driver side and passenger side triangle clamps holding the rear cross member in place.

NOTE: Clamps are spring loaded.






A CAUTION

Clamps are spring loaded. Always wear protective eye wear.

STEP TWO

Set quick clamp, Part
Y, to represent picture
below by turning the
back plate 180 degrees
from the front plate.



Insert quick clamp at an angle on triangle bracket. Turn back plate 180 degrees.

