

PRODUCT SPECIFICATIONS

ElasTech 6' Shock Absorbing Lanyard

#8240Y3

Features

- "Y"-leg lanyard for fall arrest and 100% tie off.
- Elasticated leg expands from 4 1/2 - 6' and helps to minimize tripping hazards.
- Internal shock absorber is designed to limit arrest forces to 900 lbs.
- Light-weight design is an end-user favorite.
- Anchorage end rebar hook has a 2-1/4" gate opening and allows a broader range of connections.

Material Specifications

Webbing:	<i>Polyester; Min. 6,000 lbs. tensile strength</i>
Energy Absorber:	<i>Polyester; activation greater than 450 lbs.</i>
Connectors:	<i>Alloy Steel; Min. 5,000 lbs. tensile strength</i>
Connector Gates:	<i>Alloy Steel; Min. 3,600 lbs. front load and side load</i>

Performance Specifications

Tensile Strength:	<i>Min. 5,000 lbs.</i>
Max. Capacity:	<i>310 lbs.</i>
Max. Freefall:	<i>6 feet</i>
Average Arrest Force:	<i>Less than 900 lbs.</i>
Max. Elongation:	<i>48 inches</i>

Relevant Standards

OSHA:	<i>CFR1926.502, CFR1910.66</i>
ANSI:	<i>Z359.13-2009</i>
(Z359.13-2009 supersedes Z359.1-2007 for Shock Absorbing Lanyards)	

Warnings

- Read, understand and follow all labels and instructions prior to use.
- Inspect before each use.
- Remove from service if there is evidence of damage or excessive wear.
- Remove from service if there is any signs of activation.
- Never attach a Shock Absorbing Lanyard to the front or side D-rings.



FallTech 1306 S. Alameda St. Compton, CA 90221 Tele: 323-752-0066 www.falltech.com

WARNING: THIS SPECIFICATION SHEET PROVIDES AN OVERVIEW OF PRODUCTS AVAILABLE FROM FALLTECH. CARE HAS BEEN TAKEN TO ASSURE THE ACCURACY OF THE INFORMATION. IT DOES NOT PROVIDE IMPORTANT PRODUCT WARNINGS AND INSTRUCTIONS. FALLTECH RECOMMENDS ALL USERS OF FALL PROTECTION EQUIPMENT UNDERGO THOROUGH TRAINING, AND THAT ALL WARNINGS AND INSTRUCTIONS PROVIDED WITH THESE PRODUCTS BE THOROUGHLY READ UNDERSTOOD PRIOR TO USE. FAILURE TO READ AND FOLLOW ALL PRODUCT WARNINGS AND INSTRUCTIONS COULD RESULT IN SERIOUS INJURY OR DEATH.