



Zido Phlebotomy Cart Package



Height-Adjustable Phlebotomy Cart — Carry all your phlebotomy supplies on a compact, easy-to-steer cart that takes everything you need right to your patient. Use the built-in storage for gloves, sharps containers, and more.

- ① **Handle** — The 17" (43.18 cm) wide handle makes the cart easy to steer
- ② **Adjustable Height** — Set the worksurface height 30" - 40" (76.2 - 101.6 cm) so it's comfortable for patients and clinicians
- ③ **Storage for Gloves and Sharps** — This cart has a place for everything, including a glove box holder and a metal bin with 3" (7.62 cm)-high sides to hold your sharps
- ④ **Contoured Top** — A 0.25" (0.64 cm)-high lip runs all the way around the 0.75" (1.9 cm)-thick cap worksurface to keep vials and supplies in place
- ⑤ **Locking Drawer** — The 5-3/4" (14.61 cm)- high drawer features a keyed lock. It's big enough to store vials and paperwork for security and privacy
- ⑥ **Large Casters** — The 4" (10.16 cm) diameter twin-wheel casters (2 locking) travel easily over thresholds and directly to the point of care

Part Number	BZD04CG/CG4
Product Includes	Wood lipped worksurface with bracket, 17" (43.18 cm) wide handle, deep drawer, glove box holder, metal bin, 2.5" (6.35 cm) diameter adjustable-height column with holes in 1" (2.54 cm) increments for accessory installation, rubber column cover, heavy metal base, and 4 casters (4" [10.16 cm] size, 2 locking)
Materials and Finishes	Glove box, bin, steel column and cast metal base receive a baked-on powder coated finish that's durable and easy to clean. Worksurface is medium density fiberboard wrapped in Comfort Edge thermoplastic laminate that resists cracking and chipping and stands up to a wide range of chemicals
Column Height Range	<p>40" (101.6 cm) 30" (76.2 cm)</p>
Optimal Load*	16-30 lbs. (7.26 - 13.61 kg)
Weight Capacity*	31 lbs. (14.1 kg) on the worksurface; 118 lbs. (53.06 kg) overall
Base Dims	17" W x 22.25" D (43.18 x 56.52 cm)
Worksurface Dims	0.75" H x 22" W x 17" D (1.9 x 55.88 x 43.18 cm); Lip measures 0.25" H (0.64 cm)
Mobility	Easy to move with 4" (10.16 cm) twin-wheel rubber casters (two locking). Heavy cast metal base provides stability
Product Weight	66 lbs. (29.9 kg)
Shipping	Shipping Weight: 84 lbs (38.2 kg); Ships in 5 boxes
Warranty	Limited lifetime against manufacturing defects on materials and workmanship. 5 years on gas cylinder

* When calculating the load being applied to the cart's column and worksurface, also factor the weight of any accessory options that are being installed. The listed capacity for the Zido Phlebotomy Cart Package factors the additional weight of the handle (4 lbs/1.8 kg), glove-box holder (3 lbs/1.4 kg), deep drawer (15 lbs/6.8 kg) and metal bin (10 lbs/4.5 kg). Without addition of packaged accessories, the Zido Cart's total weight capacity = 150 lbs (68.2 kg)



The 30-year legacy of Anthro Corporation lives on in its world-class factory, flexible award-winning designs, and market-leading personal customer service. When you see Anthro-DNA, it signifies quality manufacturing and technology leadership.

Americas Sales and Corporate Headquarters	EMEA Sales	APAC Sales	Worldwide OEM Sales
St. Paul, MN USA (800) 888-8458 +1-651-681-7600 www.ergotron.com sales@ergotron.com	Amersfoort, The Netherlands +31 33 45 45 600 www.ergotron.com info.eu@ergotron.com	Tokyo, Japan www.ergotron.com apaccustomerservice@ergotron.com	www.ergotron.com info.oem@ergotron.com

