



**MCR**  
SAFETY

# Checklite

## Safety Glasses

### Value Series

### Specification Sheet

#### **PRODUCT DESCRIPTION:**

This light weight option gives you a comfortable feel and each Checklite® exceeds ANSI Z87+, so feel safe while looking good!. The CL010 features a clear uncoated lens and spatula temples. Get the look you want at a reasonable price.

#### **FEATURES:**

- Good for everyday use or a new visitor spec
- Smaller frame sized to fit smaller faces
- Rugged polycarbonate lens filters 99.9% of harmful U.V. rays



#### **TECHNICAL DATA FOR: CL010**

|                              |   |                          |                 |
|------------------------------|---|--------------------------|-----------------|
| <b>Brand Series Category</b> | MCR Safety<br>Checklite<br>Safety Glasses | <b>Packaging</b>         | White Inner Box |
| <b>Case Pack</b>             | 144 pair                                  | <b>MIL - PRF - 31013</b> | Yes             |
| <b>Case Dimensions</b>       | 20.866 x 12.205 x 14.173                  | <b>ANSI Z87+</b>         | Yes             |
| <b>Case Weight</b>           | 12.600 oz.                                | <b>AS/NZS 1337.1</b>     | Yes             |
| <b>Made In</b>               | Mexico,Taiwan                             | <b>CE EN166</b>          | Yes             |

| Item No: | Lens Options: | Lens Coating:      | Scratch Resistant: | VLT%: | Frame Color: | Temple Color: | Temple Sleeve: |
|----------|---------------|--------------------|--------------------|-------|--------------|---------------|----------------|
| CL010    | Clear         | Uncoated           | No                 | 90    | N/A          | Clear         | N/A            |
| CL010D   | Clear         | Uncoated           | No                 | 90    | N/A          | Clear         | N/A            |
| CL012    | Gray          | Uncoated           | No                 | 13    | N/A          | Smoke         | N/A            |
| CL110    | Clear         | Duramass Hard Coat | Yes                | 90    | N/A          | Clear         | N/A            |
| CL110AF  | Clear         | Duramass Anti-Fog  | Yes                | 90    | N/A          | Clear         | N/A            |
| CL110D   | Clear         | Duramass Hard Coat | Yes                | 90    | N/A          | Clear         | N/A            |
| CL112    | Gray          | Duramass Hard Coat | Yes                | 13    | N/A          | Smoke         | N/A            |
| CL112AF  | Gray          | Duramass Anti-Fog  | Yes                | 13    | N/A          | Smoke         | N/A            |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2016 MCR Safety - All Rights Reserved



**MCR**  
**SAFETY**

# Checklite

## Safety Glasses

### Value Series

#### Specification Sheet

| Item No: | Lens Options:    | Lens Coating:      | Scratch Resistant: | VLT%: | Frame Color: | Temple Color: | Temple Sleeve: |
|----------|------------------|--------------------|--------------------|-------|--------------|---------------|----------------|
| CL113    | Light Blue       | Duramass Hard Coat | Yes                | 68    | N/A          | Light Blue    | N/A            |
| CL114    | Amber            | Duramass Hard Coat | Yes                | 80    | N/A          | Amber         | N/A            |
| CL117    | Silver Mirror    | Duramass Hard Coat | Yes                | 13    | N/A          | Smoke         | N/A            |
| CL118    | Blue Mirror      | Duramass Hard Coat | Yes                | 13    | N/A          | Smoke         | N/A            |
| CL119    | I/O Clear Mirror | Duramass Hard Coat | Yes                | 36    | N/A          | Clear         | N/A            |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2016 MCR Safety - All Rights Reserved