



MCR
SAFETY

Yukon

Safety Glasses

Value Series

Specification Sheet

PRODUCT DESCRIPTION:

The Yukon® features a contemporary wrap-around style. It provides increased angular coverage and improved peripheral vision. Molded-in brow guard and vented sideshields give additional protection. Available in both hard-coated for scratch resistance, or uncoated for extra cost savings.

FEATURES:

- Dielectric, no metal parts
- Single lens design with integral side shields for greater orbital seal
- Rugged polycarbonate lens filters 99.9% of harmful U.V. rays
- Spatula temples



TECHNICAL DATA FOR: 9810

Brand	MCR Safety	Scratch Resistant	Yes
Series	Yukon	Packaging	Bulk Packed
Category	Safety Glasses		
Dielectric	Yes		
Case Pack	144 pair	MIL - PRF - 31013	N/A
Case Dimensions	17.323 x 15.748 x 20.079	ANSI Z87+	Yes
Case Weight	19.800 oz.	AS/NZS 1337.1	Yes
Made In	Mexico,Taiwan	CE EN166	N/A

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
9800	Clear	Uncoated	No	90	N/A	Clear	N/A
9800B	Clear	Uncoated	No	90	N/A	Clear	N/A
9800D	Clear	Uncoated	No	90	N/A	Clear	N/A
9800XL	Clear	Uncoated	No	90	N/A	Clear	N/A
9800XLB	Clear	Uncoated	No	90	N/A	Clear	N/A
9800XLD	Clear	Uncoated	No	90	N/A	Clear	N/A
9810	Clear	Duramass Hard Coat	Yes	90	N/A	Clear	N/A
9810B	Clear	Duramass Hard Coat	Yes	90	N/A	Clear	N/A



MCR
SAFETY

Yukon

Safety Glasses

Value Series

Specification Sheet

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
9810XL	Clear	Duramass Hard Coat	Yes	90	N/A	Clear	N/A
9810XLB	Clear	Duramass Hard Coat	Yes	90	N/A	Clear	N/A
9810XLD	Clear	Duramass Hard Coat	Yes	90	N/A	Clear	N/A
98120	Filter 2.0	Duramass Hard Coat	Yes	30	N/A	Green	N/A
98150	Filter 5.0	Duramass Hard Coat	Yes	2	N/A	Green	N/A

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2016 MCR Safety - All Rights Reserved