

# Model 390 & 390HEPA



## 4 Gallon Canister Style Vacuum

Pullman-Holt's 390 is a powerful 4-gallon, dry only vacuum with exceptional stability. Designed for professional cleaning, this canister style vacuum has a superior, low profile design that makes it extremely maneuverable and easy to use.

Pullman-Holt's **390HEPA is a powerful 4-gallon, dry only HEPA vacuum with exceptional stability.** Designed for professional cleaning, this canister style vacuum has a superior, low profile design that makes it extremely maneuverable and easy to use. Unlike similar canister HEPA vacuums, the 390HEPA is equipped with a HEPA filter that is individually tested and certified, a standard feature on all Pullman-Holt HEPA Vacuums.

Unlike most HEPA Vacuums on the market, **the model 390HEPA's filter is designed and manufactured to meet or exceed all applicable EPA and OSHA standards.** The key is an independently certified HEPA Filter, a must when vacuuming in areas where positive control of hazardous particles is essential to general health and safety.



390HEPA

### Features:

A quiet, yet powerful 1.5 HP motor provides the suction of vacuums twice its size.

HEPA filters are individually tested and certified to have a minimum efficiency of 99.99% at .3 microns based on particle count test method, IEST-RP-CC001.

Convenient onboard tools and power cord storage.

Low profile design prevents tipping while providing greater mobility.

Durable stainless steel tank is attractive yet rugged.

Conveniently located foot activated on/off switch.

ETL certification - meets UL and CSA standards.

Convenient electrical outlet on base for connecting power head.




### Specifications

Style:	Dry
Horsepower:	1.5
Waterlift:	97"
CFM:	100
Recovery:	.5 bu.
Shipping Weight:	26 lbs.
Net Weight:	18 lbs.
Product Code:	B160535 (HEPA) and B100312
Motor Type:	2-stage, air-thru
Amps:	11.8
Noise Level:	65 decibels
Construction:	SS tank, injection molded base & lid
Cord:	25 ft.
Warranty:	1 year
Filters:	HEPA Filter (B160534) Disposable paper filter bag, 4 gallon (B600900) Motor Intake Filter (B160538)

### Make the Comparison

Model	Pullman Holt 390ASB	Euroclean GD930
<b>Performance</b>		
Amps	11.8	10.4
Waterlift	97	96
HP	1.5	1.3
<b>Motor</b>		
Replaceable	Yes	Yes
Serviceable	Yes	Yes
<b>Construction</b>		
Stainless Steel Tank	Yes	No
Steel Lid Clamps	Yes	No
Onboard Tool Caddy	Yes	No
Powerhead Receptacle	Yes	Yes
<b>Collection Bag</b>		
Paper (four gallon)	Yes	Yes
Reusable cloth bag available	Yes	No
<b>Attachments</b>		
Wand		
Steel	Yes	Yes
Telescopic	Yes	Yes
Floor/Rug Tool		
EZY Glide Wheels	Yes	No
Onboard Storage	Yes	No
Hose		
Crushproof	Yes	Yes
Ergo Slide Control	Yes	No

### Pullman-Holt HEPA Filter System



Individually Tested & Certified HEPA Filter  
(based on IEST-RP-CC007 particle count test method)