

SmartRack Standard Sliding Shelf (50 lb/23 kg capacity; 28.3 in/719 mm depth)

MODEL NUMBER: SRSHELF4PSL





Highlights

- Sliding Shelf mountable rack accessory
- Designed for 4 post rack mounting
- 28.3 in. / 72cm shelf depth, supports up to 50 lbs.
- Extendable shelf accommodates tower units, monitors, and other equipment
- Cold rolled steel with black finish
- Required mounting hardware included

Package Includes

- Shelf
- Mounting hardware

Description

Tripp Lite's SmartRack SRSHELF4PSL is a standard sliding shelf for installation in rack cabinets. The SRSHELF4PSL has a 28.3 in. / 72cm depth (29.5 in. / 74.9cm including handle) and can support up to 50lbs. This fully extendable shelf can accommodate tower units, monitors and other equipment. It is designed for 4 post rack mounting and the required mounting hardware is included. Expandable mounting rails supports installation in racks with front to rear rail distances between 28 in. / 71cm minimum and 46 in. / 117cm maximum.

Features

- Standard sliding shelf for installation in rack cabinets
- 28.3 in. / 72cm depth (29.5 in. / 74.9cm including handle)
- Supports up to 50 lb
- Fully extendable shelf can accommodate tower units, monitors and other equipment
- Designed for 4 post rack mounting and the required mounting hardware is included
- Expandable mounting rails supports installation in racks with front to rear rail distances between 28 in. / 71cm minimum and 46 in. / 117cm maximum

Specifications

OVERVIEW	
Accessories Type	Rack Shelves
PHYSICAL	
Maximum Device Depth (in.)	45.8
Maximum Device Depth (cm)	116.33
Minimum Device Depth (in.)	28.3
Minimum Device Depth (cm)	71.88



Shipping Dimensions (hwd / in.)	3.25 x 20 x 31
Shipping Dimensions (hwd / cm)	8.26 x 50.8 x 78.74
Shipping Weight (lbs.)	20.7
Shipping Weight (kg)	9.32
Unit Dimensions (hwd / in.)	1.75 x 18.98 x 30.11
Unit Dimensions (hwd / cm)	4.45 x 48.21 x 76.48
Unit Weight (lbs.)	18.6
Unit Weight (kg)	8.44
Color	Black
Maximum Device Depth (mm)	1163
Minimum Device Depth (mm)	719
WARRANTY	
Product Warranty Period (Worldwide	5-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies