American Standard

占 BARRIER FREE

LUCERNE[™] WALL-HUNG LAVATORY VITREOUS CHINA

LUCERNE™ WALL-HUNG LAVATORY

- Wall-hung sink
- Vitreous china
- Front overflow
- D-shaped bowl
- Self-draining deck area with contoured back and side splash shields
- Faucet ledge

Faucet holes on 203mm (8") centers (Illus.):

- □ 0356.028 For exposed bracket support Shown with 4801.862 Amarilis Heritage faucet with Triune Cross handles (not included)
- O356.015 For wall hanger (included) or concealed arms support
- 0356.037 For wall hanger (included) or concealed arms support
 Extra right-hand hole
- □ 0356.073 For wall hanger (included) or concealed arms support
- Extra left-hand hole

Faucet holes on 102mm (4") centers:

- **0355.027** For exposed bracket support
- □ 0355.012 For wall hanger (included) or concealed arms support
- 0355.034 For wall hanger (included) or concealed arms support
 Extra right-hand hole
- O355.041 For wall hung sink thru bolt support on backsplash for wall anchors
- O355.056 For wall hanger (included) or concealed arms support
 - Extra left-hand hole

Single center faucet hole (Illus.):

- O356.041 For exposed bracket support Shown with 1340.000 metering faucet (not included)
- O356.421 For wall hanger (included) or concealed arms support
- O356.137 For wall hanger (included) or concealed arms support
- Extra right-hand hole
 0356.115 For wall hanger (included) or concealed arms support
 - Extra left-hand hole

Nominal Dimensions:

521 x 464mm (20-1/2" x 18-1/4")

Bowl sizes:

381mm (15") wide 254mm (10") front to back 165mm (6-1/2") deep

Compliance Certifications -Meets or Exceeds the Following Specifications: • ASME A112.19.2 for Vitreous China Fixtures



0356.028



0356.041

SEE REVERSE FOR ROUGHING-IN DIMENSIONS

To Be Specified:

- □ Color: □ White □ Bone □ Silver □ Black □ Linen
- Faucet*:
- □ Faucet Finish:
- Supplies:
- □ 1-1/4" Trap:
- Nipple:
- □ Bracket Support (by others):
- □ Concealed Arms Support (by others):

* See faucet section for additional models available



MEETS THE AMERICANS WITH DISABILITIES ACT GUIDE-LINES AND ANSI A117.1 ACCESSIBLE AND USABLE BUILDINGS AND FACILITIES - CHECK LOCAL CODES. Top of front rim mounted 864mm (34") from finished floor.


American Standard

OR CONCEALED ARMS

0356.015 8" CTRS FOR WALL HANGER



0356.037 8" CTRS FOR WALL HANGER OR CONCEALED ARMS EXTRA RIGHT HAND HOLE



NOTES:

* DIMENSIONS SHOWN FOR LOCATION OF SUPPLIES AND "P" TRAP ARE SUGGESTED. PROVIDE SUITABLE REINFORCEMENT FOR ALL WALL SUPPORTS. FITTINGS NOT INCLUDED AND MUST BE ORDERED SEPARATELY. CONCEALED ARM SUPPORT AS REQUIRED TO BE FURNISHED BY OTHERS.

IMPORTANT: Dimensions of fixtures are nominal and may vary within the range of tolerances established by ANSI Standard A112.19.2. These measurements are subject to change or cancellation. No responsibility is assumed for use of superseded or voided pages.

LAVATORY DESIGNED TO MEET ADA HANDICAPPED GUIDELINES WITH MOUNTING HEIGHT SET AT 864MM (34") ABOVE FINISHED FLOOR.


American Standard


0356.073 8" CTRS FOR WALL HANGER OR

BARRIER FREE

LUCERNE[™] WALL-HUNG LAVATORY VITREOUS CHINA

0355.012 4" CTRS FOR WALL HANGER OR CONCEALED ARMS





NOTES:

* DIMENSIONS SHOWN FOR LOCATION OF SUPPLIES AND "P" TRAP ARE SUGGESTED. PROVIDE SUITABLE REINFORCEMENT FOR ALL WALL SUPPORTS. FITTINGS NOT INCLUDED AND MUST BE ORDERED SEPARATELY. CONCEALED ARM SUPPORT AS REQUIRED TO BE FURNISHED BY OTHERS.

IMPORTANT: Dimensions of fixtures are nominal and may vary within the range of tolerances established by ANSI Standard A112.19.2. These measurements are subject to change or cancellation. No responsibility is assumed for use of superseded or voided pages.

LAVATORY DESIGNED TO MEET ADA HANDICAPPED GUIDELINES WITH MOUNTING HEIGHT SET AT 864MM (34") ABOVE FINISHED FLOOR.

American Standard

Style That Works Better **BARRIER FREE**


CONCEALED ARMS EXTRA RIGHT HAND HOLE

0355.034

LUCERNE[™] WALL-HUNG LAVATORY VITREOUS CHINA

4" CTRS FOR WALL HANGER OR

0355.041 WALL HUNG SINK THRU BOLT SUPPORT ON BACKSPLASH FOR WALL ANCHORS



NOTES:

* DIMENSIONS SHOWN FOR LOCATION OF SUPPLIES AND "P" TRAP ARE SUGGESTED. PROVIDE SUITABLE REINFORCEMENT FOR ALL WALL SUPPORTS. FITTINGS NOT INCLUDED AND MUST BE ORDERED SEPARATELY. CONCEALED ARM SUPPORT AS REQUIRED TO BE FURNISHED BY OTHERS.


IMPORTANT: Dimensions of fixtures are nominal and may vary within the range of tolerances established by ANSI Standard A112.19.2. These measurements are subject to change or cancellation. No responsibility is assumed for use of superseded or voided pages.

LAVATORY DESIGNED TO MEET ADA HANDICAPPED GUIDELINES WITH MOUNTING HEIGHT SET AT 864MM (34") ABOVE FINISHED FLOOR. Ġ

American Standard


& BARRIER FREE

0355.056 4" CTRS FOR WALL HANGER OR CONCEALED ARMS EXTRA LEFT HAND HOLE



LUCERNE[™] WALL-HUNG LAVATORY VITREOUS CHINA

0356.421 SINGLE CENTER HOLE FOR WALL HANGER OR CONCEALED ARMS



NOTES:

* DIMENSIONS SHOWN FOR LOCATION OF SUPPLIES AND "P" TRAP ARE SUGGESTED. PROVIDE SUITABLE REINFORCEMENT FOR ALL WALL SUPPORTS. FITTINGS NOT INCLUDED AND MUST BE ORDERED SEPARATELY. CONCEALED ARM SUPPORT AS REQUIRED TO BE FURNISHED BY OTHERS.

IMPORTANT: Dimensions of fixtures are nominal and may vary within the range of tolerances established by ANSI Standard A112.19.2. These measurements are subject to change or cancellation. No responsibility is assumed for use of superseded or voided pages.

LAVATORY DESIGNED TO MEET ADA HANDICAPPED GUIDELINES WITH MOUNTING HEIGHT


American Standard

BARRIER FREE

0356.137 SINGLE CENTER HOLE FOR WALL HANGER OR CONCEALED ARMS WITH EXTRA RIGHT HAND HOLE

LUCERNE[™] WALL-HUNG LAVATORY VITREOUS CHINA

0356.115 SINGLE CENTER HOLE FOR WALL HANGER OR CONCEALED ARMS WITH EXTRA LEFT HAND HOLE



NOTES:

* DIMENSIONS SHOWN FOR LOCATION OF SUPPLIES AND "P" TRAP ARE SUGGESTED. PROVIDE SUITABLE REINFORCEMENT FOR ALL WALL SUPPORTS. FITTINGS NOT INCLUDED AND MUST BE ORDERED SEPARATELY. CONCEALED ARM SUPPORT AS REQUIRED TO BE FURNISHED BY OTHERS.

IMPORTANT: Dimensions of fixtures are nominal and may vary within the range of tolerances established by ANSI Standard A112.19.2. These measurements are subject to change or cancellation. No responsibility is assumed for use of superseded or voided pages.

LAVATORY DESIGNED TO MEET ADA HANDICAPPED GUIDELINES WITH MOUNTING HEIGHT SET AT 864MM (34") ABOVE FINISHED FLOOR.