


WORLDWIDE FRACTIONAL HP MOTORS

Permanent Magnet DC Motors

TENV / TEFC Enclosure ■ C-Face ■ Removable Base
90, 180, 12 and 24 Volt



DIMENSIONS

12 Volt and 24 Volt

ALL DIMENSIONS IN INCHES

Model	E	E2	2F1	2F2	2F3	H	BA	C	D	L	O	S	ES	R	N-W	U	BC	AH	AK	AJ	BF
WPMDC13-18-12V-56CB	2.44	---	3	---	---	0.34	2.75	10.06	3.5	7.63	4.94	0.188	1.41	0.517	1.88	0.625	0.12	2.06	4.5	5.875	3/8-16
WPMDC13-18-24V-56CB	2.44	---	3	---	---	0.34	2.75	10.06	3.5	7.63	4.94	0.188	1.41	0.517	1.88	0.625	0.12	2.06	4.5	5.875	3/8-16
WPMDC12-18-12V-56CB	2.44	---	3	---	---	0.34	2.75	10.94	3.5	7.63	4.94	0.188	1.41	0.517	1.88	0.625	0.12	2.06	4.5	5.875	3/8-16
WPMDC12-18-24V-56CB	2.44	---	3	---	---	0.34	2.75	10.94	3.5	7.63	4.94	0.188	1.41	0.517	1.88	0.625	0.12	2.06	4.5	5.875	3/8-16
WPMDC34-18-12V-56CB	2.44	---	3	---	---	0.34	2.75	13.51	3.5	7.63	5.57	0.188	1.41	0.517	1.88	0.625	0.12	2.06	4.5	5.875	3/8-16
WPMDC34-18-24V-56CB	2.44	---	3	---	---	0.34	2.75	13.51	3.5	7.63	5.57	0.188	1.41	0.517	1.88	0.625	0.12	2.06	4.5	5.875	3/8-16
WPMDC1-36-24V-56CB	2.44	---	3	---	---	0.34	2.75	14.3	3.5	7.63	5.57	0.188	1.41	0.517	1.88	0.625	0.12	2.06	4.5	5.875	3/8-16
WPMDC1-18-12V-56CB	2.44	---	3	---	---	0.34	2.75	14.3	3.5	7.63	5.57	0.188	1.41	0.517	1.88	0.625	0.12	2.06	4.5	5.875	3/8-16
WPMDC1-18-24V-56CB	2.44	---	3	---	---	0.34	2.75	14.3	3.5	7.63	5.57	0.188	1.41	0.517	1.88	0.625	0.12	2.06	4.5	5.875	3/8-16
WPMDC1.5-18-24V-56CB	2.44	---	3	---	---	0.34	2.75	16.45	3.5	7.63	5.57	0.188	1.41	0.517	1.88	0.625	0.12	2.06	4.5	5.875	3/8-16

Dimensions shown in this catalog are for general use only.
For an exact drawing on a specific rating, please contact our sales office.

