

Aria Install Instructions

Because of the wide variation of mounting surface construction, specific mounting hardware is not included. For the most secure mounting Ghent recommends using #8 x 1-1/4" pan head type self-tapping screws fastened directly into wall studs. When wall studs can not be used, we recommend using wall anchors appropriate for the construction materials and product weight (not included).

STEP 1: Determine the desired height from the floor to the bottom of the board. Scribe a level line on the wall at that distance. See *illustration 1*.

STEP 2: Position bottom edge of the Steel Support Bar along the scribed line. Using appropriate fasteners for the wall construction the board is being mounted to, securely fasten the Steel Support Bar to the wall. See *illustration 1*.

STEP 3: Using the table below, measure up from the interior face of the Steel Support Bar to the corresponding height(s). Scribe a level line at this height(s). See *illustration 1*.

STEP 4: Pre-drill a minimum of 4 holes into the wall mounted cleat(s). We recommend spacing the holes to align with as many studs as possible.

STEP 5: Align the bottom of the cleat(s) to the scribed line(s). Using the appropriate fasteners, mount the cleat(s) to the wall. See *illustration 1*.

STEP 6: Lift the glass higher than the wall mounted cleat(s) and press firmly to the wall. Gently lower the board until the board mounted cleat(s) are resting securely inside the wall mounted cleat(s). See *illustration 2*.

STEP 7: When your board is positioned at the desired location carefully remove the adhesive coverings from the Steel Support Bar. Apply firm pressure at the bottom of the board to ensure secure adhesion. See *illustration 1*.

STEP 8: Markers can be stored below the board by placing the attached magnet against the Steel Support Bar.

STEP 9: Make sure to thoroughly clean the writing surface before use.

ATTENTION

- Ghent recommends two person install teams to mount our Aria glassboards.
- Ghent recommends the use of suction cups to aid in lifting the board when mounting glassboards larger than 3'x4'. Please call for details or visit our website.
- Ghent recommends visiting our website for videos on installing complete coverage glass walls.

PART NUMBER	CLEAT 1	CLEAT 2
ARIASX23XX	18-15/16"	-
ARIASX32XX	30-15/16"	-
ARIASX34XX	30-15/16"	-
ARIASX43XX	42-15/16"	-
ARIASX44XX	42-15/16"	-
ARIASX45XX	42-15/16"	-
ARIASX46XX	42-15/16"	-
ARIASX48XX	42-15/16"	-
ARIASX54XX	20-15/16"	54-15/16"
ARIASX64XX	32-15/16"	66-15/16"
ARIASX84XX	56-15/16"	90-15/16"

Note: Illustrations show mounting of an ARIASN84BE.

Illustration 1




Illustration 2

