



\$239
CN653295

37" H POST
CONVERTS IN
MINUTES TO A
BENCH SCALE

**SAME DAY
IN STOCK
SHIPMENT**

**Online
Video
& Photos**



**EXTENDED
SERVICE PLAN**

INDUSTRIAL BENCH/FLOOR SCALE

This digital shipping scale is ideal for multiple uses and environments. Can be used for weighing, counting or checkweighing. 10" H and removable 37" H posts allow display height adjustment for bench and floor scale use. Hand screw knob on post allows quick post removal. Stainless steel platform measures 16 1/2" W x 20 1/2" L. Plastic display measures 9 3/4" W x 6" H and includes LCD screen displaying six 1" H digits for easy-to-read viewing. Hand screw leveling feet allows quick and easy deck height adjustments up to 7" H. Includes leveling indicator for proper weighing. Operating functions include auto-zero, tare, accumulate and counting. Features auto shutoff with sleep mode function. 660 lb./300 kg. capacity, 0.25 lb./0.10 kg. accuracy. 115V, AC with built-in rechargeable battery, 6' L power cord. 1 year Limited Warranty.



**660 lb.
capacity**

**POST HEIGHT
ADJUSTS FOR
TABLE TOP
OR FLOOR
APPLICATIONS**



EASY TO READ 1" H NUMBERS

**500 lb.
capacity**

COMPACT SHIPPING FLOOR SCALE



Accurate within 0.2% of full capacity. **Stainless steel platform.** ABS indicator with standard NCI interfaces for use with software including UPS™ Worldship Online and FedEx®. 5-digit LCD display with tare, unit conversion and hold/print features. Requires 4 AAA batteries for a 20 hour battery life or AC adapter. **Includes a removable rubber slip-resistant mat** and indicator for wall mounting bracket. Includes 10' L RS-232 cable. 500 lb./250 kg. capacity, 0.2 lb./0.1 kg. accuracy. Complies with FCC regulations, UL listed. 1 Year Limited Warranty.

**EXTENDED
SERVICE PLAN**

**48 HOUR
SHIPMENT**

W" x D"	Model	Price
22 x 22	CN613168	\$379.00
22 x 36	CN613169	439.95
22 x 42	CN613170	509.95

BENCH SCALE / CHECKWEIGHER



Ideal for weighing, checkweighing and basic parts counting. NTEP Approved at 3000 divisions, 6000 divisions for 300 lb. capacity. Legal for Trade accuracy, plus user configurable up to 7,500 divisions. Simple to operate. Rugged, design with folding display column for portability. **Stainless steel construction** wipes down easily. Easy to read 1.2" H LCD display has 7 function keys and numeric keypad, plus adjustable angle mounting bracket. Operates either with an AC adapter (included) or 120+ hours with 6-C batteries (not included). Ten preset targets with push-button setting for either weight or piece count. Checkweighing features under/accept/over indicators with both a bar graph and audible alarm. Weighs in lb., kg or oz. Full capacity Tare with Net/Gross weight. Large 13.5" x 17.4" x 4" platform, 12.5" display height. Low battery indicator. 1 year Limited Warranty.

Up to 300 lb. capacity

Model	Capacity		Accuracy		Price
	lbs.	kg.	lbs.	kg.	
CN652569	30	15	0.01	0.005	\$529.00
CN652596	60	30	0.02	0.01	529.00
CN652597	150	60	0.05	0.02	529.00
CN652598	300	150	0.05	0.02	599.00

DIGITAL SHIPPING/RECEIVING SCALE

400 lb. capacity



UL

**ONLY
\$79**

**EXTENDED
SERVICE PLAN**

**SAME DAY
IN STOCK
SHIPMENT**

Simple to operate. Rugged low profile steel platform 12 1/4" x 11 3/4". Large, easy to read 1" LCD digital display comes with a 6' coiled cord; includes bracket for wall or surface mounting. Features large keys for tare/hold, units, on and off. Powers off after 2 minutes of non-use. Includes an RS232 serial port. Operates with either an AC adapter (included) or 6-AA batteries (not included). 1 Year Limited Warranty.

Model	Capacity		Accuracy		Price
	Lbs.	Kg	Lbs.	Kg.	
CN300625	400	181	0.5	0.2	\$79.00

BENCH DIAL SCALE

110 lb. capacity

Reliable for everyday use this scale includes a 9" dial, twin spring mechanism (for accuracy) and a shatterproof lens. Chrome plated steel 12" x 12" platform and enamel-finished body. Scale is graduated in both Lbs. and Kgs. Accuracy is 4oz./100g. 1 Year Limited Warranty.

Model CN652638 Price \$59.95



**SAME DAY
IN STOCK
SHIPMENT**



BENCH SCALE

**With Memory Lock
250 lb. capacity**

22 gauge steel construction. Four, 1" H digits back light LCD display. Freezes weight on display only when 3 lbs. or more is placed on scale. Tare function for net weight of product. Scrolls between lbs. and kilos. Auto shut off. Weak battery indicator. Scale measures 11" L x 12 1/2" W x 2 1/2" H. 250 lb./110 kg. capacity, 0.5 lb./0.2 kg. accuracy. 9V AC adapter or use 9V battery not included. 1 Year Limited Warranty.

**EXTENDED
SERVICE PLAN**

**SAME DAY
IN STOCK
SHIPMENT**

Model CN506846 1-2 \$72.95 ea. 3+ \$66.95 ea.

LABEL PRINTING SCALE

Ideal for any butcher shop, market or grocery. Made of corrosion resistant stainless steel. Features user-friendly keyboard, customizable printing formats, bar code UPC or EAN programming, AC adapter, 300 programmable (PLU) memories and designates up to 20 users. Security key prevents unauthorized usage. Programmed through the scale directly or with included software using a computer. Ethernet capable for use with unlimited scales in a functional network. Large, easy-to-read 2-sided LCD display. Easy-to-change print cartridge. Platform measures 15" x 12".

Model	Capacity		Accuracy		Price
	lbs.	kg.	lbs.	kg.	
CN240874	40	20	0.01	0.005	\$699.00

