

# Stepladders

## Fiberglass Stepladders

### 6200 Series


300 lb. Load Capacity  
Type IA Duty Rating



Next generation ladder top holds an arsenal of tools. Lock-In Accessory System secures tools from falling.



Double Riveted slip-resistant Traction-Tred® steps.



### EDGE 360®

Bracing system protects from every angle. Features Integrated Rail Shields, Energy Diffusing Geometry and Oversized Foot Pads

Global Item No.	Model	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
942808	6204	4'	19-7/8"	29"	3.0	16.0
942810	6206	6'	23-3/8"	41-1/4"	5.3	22.0
942812	6208	8'	26-7/8"	53-5/8"	8.1	30.0
942814	6210	10'	30-3/8"	66-7/8"	12.5	39.0
942816	6212	12'	33-7/8"	78-1/4"	15.0	48.0



#1 IN LADDERS™

[www.wernerco.com](http://www.wernerco.com)