


# PALLET POSITIONER *Ergonomic Solutions to Help Reduce Employee Fatigue*


Rotating ring minimizes worker movement, increasing productivity while helping reduce injuries due to bending and reaching. Heavy duty welded steel construction. **Carousel** is ideal for applications that require easy load rotation only. Designed to be used on a floor or table. 40" O.D., 36 1/2" I.D., 2 1/8" H. **Pallet Stand** offers height adjustment benefits. Positive locking mechanism helps ensure worker safety. Choice of 20", 31" and 35" height settings. **Pallet Stand/Carousel** combines the benefits of height adjustment and rotation. Heavy duty 40" x 45" platform and 40" O.D. carousel welded to stand. 22" lowered height with 33" and 37" raised height positions.

**EZ Loader Self Leveling - Positioner** is a true ergonomic tool. As the load changes, the positioner **adjusts automatically**, keeping top of the load at convenient working height. Proven Firestone Airstroke Actuator pneumatic support system. Totally **self-contained** and does not require constant air source (requires initial air pressure of 60 psi). **Forkliftable**. Built-in air gauge and pressure relief valve. 49" L x 24 5/8" W base and 43" O.D. carousel. 10 1/2" lowered height and 30 1/2" raised height.



AS LOW AS  
**\$309**

**Bishamon**  
**Portable**  
SELF LEVELING POSITIONER  
FD123007



Model	Description	Cap. Lbs.	Price
FD330012	Carousel Only	2000	<b>\$309.00</b>
FD330013	Carousel Only	4000	<b>349.95</b>
FD330014	Carousel Only	6000	<b>409.95</b>
FD330015	Pallet Stand Only	5000	<b>499.95</b>
FD330016	Pallet Stand/Carousel	4000	<b>819.00</b>
FD123007	Self-Leveling Positioner	250/4000†	<b>2339.00</b>

†min./max. capacity

Online Video & Photos

## **Presto** PALLET POSITIONER *Automatic Load Leveler with Carousel*


Build or breakdown pallet loads with a minimum of bending or reaching. **Self-Leveling Positioner automatically maintains pallet at a consistently comfortable work height.** As layers of product are added or removed, a combination of a permanently mounted spring and reinforced rubber airbag assures work remains at an ergonomic height, increasing productivity. Limited lifetime warranty airbag is completely protected to prevent accidental puncture. **Fully self-contained and does not require a constant air source.** Simply charge the unit via single air connection (requires initial air pressure of 7 to 62 psi) and integral fork pockets allow easy movement by forklift. Complete with air pressure gauge and relief valve. **400 lbs. minimum/4500 lbs. maximum capacity.** Large 48" L x 36" W base has wide footprint for stability and does not require unit to be lagged to the floor. 43 5/8" OD carousel, with 9 1/2" lowered height and 30 1/2" raised height. 2 Year Limited Warranty.

AS LOW AS  
**\$1999**



ONE SIMPLE AIR CONNECTION; REQUIRES NO ADDITIONAL POWER

Model	Description	Price
FD241482	Self-Leveling Positioner	<b>\$1999.00</b>
<b>OPTIONAL ACCESSORIES</b>		
FD241483	Solid Carousel Top - 12 gauge Steel Cover accommodates small or odd-sized pallets	<b>139.95</b>
FD241484	Portability Package - 2 frame mounted fixed Wheels and Wheeled Dolly Handle. (Unloaded movement only)	<b>549.00</b>



## PALLET TURNTABLE

**4000 lb. capacity**

AS LOW AS  
**\$949**



PALLET TRUCK ACCESSIBLE


Increase productivity and reduce muscle strain from stretching and reaching over and around loads. Precision anti-friction ball bearings allow for 360° pallet rotation by a single person. Low profile 7/8" overall height allows pallet truck access for efficient load transfer without a pit. Includes lock to prevent unwanted rotation. Strong steel construction has chip resistant finish. Use throughout the plant, as unit does not require lagging to the floor.

Model	Overall dia."	Usable dia."	Wt. Lbs.	Price
FD242077	48	39	205	<b>\$949.00</b>
FD242078	54	45	225	<b>999.00</b>
FD242079	60	51	247	<b>1053.00</b>

## **Presto** FLOOR LEVEL LIFT & TILT TABLES

Position work at a comfortable level to help improve productivity and worker safety. Adjustable height helps eliminate bending and stretching. Constructed of heavy gauge steel for strength. Floor level platform ramp allows you to use a pallet truck or hand truck to quickly load and unload equipment. 1 HP 115V, single phase motor. Toe guard/safety edge helps protect workers from injury. **Lift Table** raises and lowers contents to provide individual workers with a personalized working height to insure correct posture. Raised height is 33 3/8". Especially suitable for use with pallets. **Tilt Table** tilts contents from 0° to 45° to help eliminate undue stress on workers. Allows you to angle containers so parts are within sight and reach. Available with either a push button Hand Control with 8' coil cord or a Foot Control. Specify suffix: (H) for Hand or (F) for Foot.

**6000 lb. capacity**



LIFT TABLE					TILT TABLE				
Model	Overall W" x L"	Lift Seconds	Price	Cap. Lbs.	Lowered Height"	Model	Overall W" x L"	Lift Seconds	Price
<b>44"W x 48"L PLATFORM</b>									
FD176820	61 1/4 x 59	40	<b>\$4449.00</b>	2000	3/8	FD176826	55 x 60 1/2	30	<b>\$3929.00</b>
FD176821	61 1/4 x 59	44	<b>4469.00</b>	4000	3/8	FD176827	55 x 60 1/2	32	<b>4039.00</b>
FD176822	61 1/4 x 59	54	<b>5399.00</b>	6000	1/2	FD176828	55 x 60 1/2	36	<b>5089.00</b>
<b>50"W x 48"L PLATFORM</b>									
FD176823	67 1/4 x 59	44	<b>4549.00</b>	2000	3/8	FD176829	63 x 60 1/2	32	<b>4039.00</b>
FD176824	67 1/4 x 59	46	<b>4589.00</b>	4000	3/8	FD176830	63 x 60 1/2	34	<b>4199.00</b>
FD176825	67 1/4 x 59	56	<b>5529.00</b>	6000	1/2	FD176831	63 x 60 1/2	38	<b>5309.00</b>