

GLOBAL PLASTIC SHELF BIN

- Water and grease proof polypropylene, impervious to most chemicals
- Convenient handle — label area
- "V" notch catches the underside of shelf to prevent spillage
- Transport small parts. Nest when not in use
- Reinforced sides permit full capacity loading
- **Add color suffix when ordering: Blue (BL) or Yellow (YL)**

AS LOW AS
85¢

Over
30 Million
In Use

DIVIDABLE FOR
SUPERIOR
PARTS
CONTROL

LITTLE BIN

fits snugly inside shelf bin to create completely separate compartments. Simplifies parts storage and removal. Use separately or with any size bin. Yellow.



Model	W" x D" x H"	Price/pkg of 50
FD652857	3 1/4 x 2 x 3	\$13.50
FD652881	4 x 2 x 4	22.00
FD146112	5 x 3 x 3	25.00

Model	W" x D" x H"	Case Qty.	Price Each Bin				Clear Divider Model	50/pkg. Price
			1 Case	2-6 Cases	7-12 Cases	13+ Cases		
FD146101	4 x 12 x 4	36	\$1.02	\$0.98	\$0.92	\$0.85	FD146102	\$11.20
FD146103	6 x 12 x 4	30	1.49	1.45	1.41	1.38	FD146104	11.60
FD146109	8 x 12 x 4	20	1.79	1.76	1.72	1.68	FD146106	12.35
FD146105	4 x 18 x 4	20	1.54	1.49	1.45	1.42	FD146102	11.20
FD146107	6 x 18 x 4	20	2.11	2.06	1.93	1.89	FD146104	11.60
FD146113	8 x 18 x 4	20	2.74	2.57	2.41	2.25	FD146106	12.35


SAME DAY
IN STOCK
SHIPMENT

GLOBAL PICK RACK Complete with Bins

Heavy duty steel shelf-rack combined with removable plastic bins offer you an efficient, low cost, space-saving storage system. The perfect way to store and display parts for quick access, better visibility, easy inventory control. Rugged, one-piece 12"L x 4"H plastic bin with handy label holder, won't rust, chip or crack. Mobile double-sided rack on dolly with 2 swivel and 2 rigid 3" wheel casters. Rolls easily from stockroom to production area. Long-lasting gray baked enamel finish. **Add color suffix when ordering: Blue (BL) or Yellow (YL).**

AS LOW AS
\$59

- A. BENCH RACK 33" x 12" x 21"H, 3 SHELVES**
- | Description | Model | Price |
|-------------|----------|---------|
| 12 Bins-8"W | FD601356 | \$59.00 |
| 24 Bins-4"W | FD601354 | 69.95 |
- B. FLOOR RACK 33" x 12" x 61"H, 8 SHELVES**
- | Description | Model | Price |
|-------------|----------|----------|
| 32 Bins-8"W | FD601352 | \$145.95 |
| 64 Bins-4"W | FD601350 | 155.95 |
- C. MOBILE RACK 36" x 26" x 65"H, 16 SHELVES**
- | Description | Model | Price |
|--------------|----------|----------|
| 64 Bins-8"W | FD601360 | \$348.95 |
| 128 Bins-4"W | FD601358 | 358.95 |



A FD601354BL



B FD601352YL

C FD601360YL

SAME DAY
IN STOCK
SHIPMENT

STACKABLE WIRE BIN STORAGE

Interlocking modular bins organize, store and transport material in warehouse, production and assembly areas. Position bins side by side or back to back. Stacked up to 7 high. Open mesh permits quick inventory control. Industrial grade rust and corrosion-resistant welded .283 diameter wire frame, with .105 diameter cross wire construction for ultimate strength and rigidity. Maintenance free triple plated chrome finish. Optional dividers create a variety of compartment sizes. Assembles easily.

AS LOW AS
\$189

5 LEVEL PRECONFIGURED STORAGE UNIT						
Bin Qty.	D" x H" Ht.	36" WIDE		48" WIDE		
		Model	Price	Model	Price	
1	20 x 12					
1	20 x 9	54	FD339011	\$189.00	FD339023	\$255.95
3	14 x 9					
2	20 x 12	57	FD339012	199.95	FD339024	258.95
3	14 x 9					
2	20 x 12	57	FD339015	219.95	FD339027	259.95
3	20 x 9					
5	20 x 9	66	FD339016	225.95	FD339028	295.95



ONE WIRE BIN WITH TWO OPTIONAL DIVIDERS

Easy Access Modular Storage

DOLLY BASE

Turn your storage system into a mobile unit. Smooth rolling 5" x 1 1/4" polyurethane wheel swivel casters. For 20" deep bins.

W" x D" x H"	INDIVIDUAL BINS AND DIVIDERS		DIVIDER	
	Model	Price Each	Model	Price Each
36 x 14 x 9	FD832102	\$41.95	FD832138	\$4.90
48 x 14 x 9	FD832118	55.95	FD832138	4.90
36 x 20 x 9	FD832108	48.95	FD832144	6.20
48 x 20 x 9	FD832124	65.95	FD832144	6.20
36 x 20 x 12	FD832114	55.95	FD832150	7.90
48 x 20 x 12	FD832130	65.95	FD832150	7.90

Model	W" x D"	Price
FD832132	36 x 20	\$79.95
FD832134	48 x 20	89.95



100 lb. bin capacity

FD339024
WITH BIN DIVIDERS AND DOLLY BASE