

AUTOMATIC SCRUBBERS

Electric Scrubbers - Model FD261122

- Rotationally molded polyethylene housing
- 18" Cleaning Path/Deck
- 8 gal. solution/ 11 gal. recovery tanks
- 28"W cast aluminum squeegee assembly
- 1 HP, 2-stage motor that offers 65" water lift
- 250 RPM, 66 lbs. of pad pressure
- Coverage rate of 18,000 sq. ft. per hour
- 82'L power cord

ONLY
\$1299

FD261122

SAME DAY
IN STOCK
SHIPMENT



ACCESSORIES

Model	Description	Price
PAD* Case of 5, price per case		
FD261169	17" Floor Pad	\$16.00

*Specify color suffix for pad type:

Green Scrubbing (GN), Red Buffing (RD)

REPLACEMENT PARTS

Model	Description	Price
FD261127	18" Pad Driver	\$72.00
FD261180	18" Front Squeegee Blade	19.95
FD261181	18" Rear Squeegee Blade	26.95

Auto Battery Scrubbers

- 20" Scrubbers provides 21,000 sq. ft. per hour coverage
- Two 12V batteries. **FD261123** is 105 amp and **FD261124** is 130 amp with 3 1/2 hr. run time per charge. **FD261125** is 215 amp with 5 hr. run time
- 26" Scrubber offers variable speed control with 3-stage motor. Provides 26,000 sq. ft. per hour coverage. Includes two 215 amp batteries for 4 1/2 hr. run time per charge
- Includes on-board charger and set of replacement squeegee blades

SAME DAY
IN STOCK
SHIPMENT



FD261123

Online
Video
& Photos

ACCESSORIES

Model	Description	Price
PAD* Case of 5, price per case		
FD261163†	13" Floor Pad	\$11.00
FD261170	20" Floor Pad	20.75

(†Model FD261126 Requires 2)

* Specify color suffix for pad type: Green Scrubbing (GN), Red Buffing (RD)

REPLACEMENT PARTS

Model	Description	Price
FD261128	13" Pad Driver (Req. 2)	\$48.00
FD261129	20" Pad Driver	79.00
FD261182	20" Front Squeegee Blade	19.95
FD261183	20" Rear Squeegee Blade	26.95
FD261184	26" Front Squeegee Blade	27.95
FD261185	26" Rear Squeegee Blade	36.95

Model	Cleaning Path/Deck"	Pad Pressure Lbs.	Squeegee Width"	Water Lift"	Tank Cap. Gal. Solution/Recovery	Price
FD261123	20	50	28	55	13/15	\$2899.00
FD261124	20	50	28	55	13/15	3099.00
FD261125	20	Up to 200	28	55	16/16	4099.00
FD261126	26	Up to 150	32	67	17/17	4999.00

Mastercraft MINI ELECTRIC SCRUBBER

- Cleans up to 6,000 square feet per hour
- 850 watt vacuum motor; 200 watt brush motor
- 200 rpm brush speed with 22 lbs brush pressure
- 13.5" scrub path; 15.5" vacuum path
- 3.5 gallon solution, 4 gallon recovery tank capacity
- Removable rotational molded tanks with drain port
- Independent controls for brush and vacuum
- Two quick release brushes wash and scrub most hard floor surfaces
- Two quick release squeegees with vacuum shoes quickly dry the cleaning path
- Molded plastic handle adjusts to operator height and folds for transport or storage
- 25' L power cord

ONLY
\$1399

FD239714

IDEAL FOR
SMALLER
AREAS



FLOOR MACHINES

- All metal construction
- Low speed for use on wet hard floors and carpets
- Heavy duty 1.5HP motor
- Triple planetary, all steel gear box
- Safety lock-out switch with easy thumb control throttle
- Pad driver included
- 50'L safety yellow power cord
- **FD261117 & FD261118** have dual capacitor motor
- **FD261119** has DC rectified motor

AS LOW AS
\$499

SAME DAY
IN STOCK
SHIPMENT

Model	Cleaning Path/Deck"	Speed	Price
FD261117	17	175 rpm	\$499.00
FD261118	20	175 rpm	589.00
FD261119	20	185-330 rpm	849.00

ACCESSORIES

Model	Description	Price
PAD* Case of 5, price per case		
FD261164	17" Floor Pad	\$16.00
FD261165	20" Floor Pad	20.75

Solution Tank

FD261130	2.5 Gallon	\$72.00
----------	------------	---------

*Specify color suffix for pad type: Black Stripping (BK), Green Scrubbing (GN), Red Buffing (RD), White Polishing (WH).

Shown with
Floor Pad

FD261118



FLOOR BURNISHERS

- High speed operation for use on dry floors only
- Heavy duty 1.5HP DC rectified motor
- Handle mounted circuit breaker
- Safety lock-out switch with easy thumb control
- 50'L safety yellow power cord
- Tilt and roll mobility with rear wheels
- **FD261121** features folding handle and passive dust control with cloth collector bag

AS LOW AS
\$739

Online
Video
& Photos

SAME DAY
IN STOCK
SHIPMENT

Model	Speed	Price
FD261120	1500 rpm	\$739.00
FD261121	2000 rpm	869.00

BURNISHER PAD - Case of 5, price/case

FD261166	High Freq., Soft To Med. Finish	\$21.25
FD261167	Low Freq., Med. To Hard Finish	21.25
FD261168	Low Freq., Hard Finish	21.25

FD261121

FD261120



VIPER CARPET EXTRACTORS

- Rotationally molded polyethylene tanks
- 3-stage tangential discharge motor
- 118" water lift
- 10 gallon solution and 7 gallon recovery tank
- Includes 50'L safety yellow power cord
- **Box Carpet Extractor** includes 15'L vacuum and solution hoses and 12" stainless steel wand. Offers 1,300 sq. ft. per hr. coverage rate
- **Self Contained Extractor** features a cylindrical brush with 1/8HP brush motor. Offers 16" cleaning path with 2,000 sq. ft. per hr. coverage rate

AS LOW AS
\$1195

Model	Description	Price
FD443134	Box Extractor	\$1195.00
FD443135	Self-Contained Extractor	1315.00

Online
Video
& Photos

FD443135

