

DRUM PALLETIZER

800 lb. capacity

Moves and transports drums easily to or from pallets with a maximum height of 8". Dual ratchet stops hold the weight of the drum, and provide several positions where the handle stays until operator takes hold. Operator holds no weight and does not need to balance drum truck. Two 6" polyolefin load wheels and two 4" swivel casters provide smooth movement. Designed for rimmed 55-gallon steel drums.



ONLY
\$399
FD955061

SAME DAY
IN STOCK
SHIPMENT

DRUM TRANSPORTER

Up to 1500 lb. capacity

Ideal for lifting and transporting 30 & 55 gallon steel, plastic or fiber drums with top lip. Outriggers pivot for access to drums on pallets. Lifts drum 12" above the floor. Four 8" x 2" phenolic casters. Rear casters include foot operated wheel brakes. **Manual Drum Transporter** features a manual mechanical ratchet lift mechanism. **Hydraulic Drum Transporters** use a foot pump to activate heavy duty hydraulic jack. Push handle folds down for easy access to ratchet and foot pump. Heavy duty welded steel with a yellow powder coat finish.



FD795503



AS LOW AS
\$769

Model	Description	Capacity	Jaw Service Range	Price
FD237753	Manual Hand Ratchet	880 lbs.	27" - 47"	\$769.00
FD795503	Standard Hydraulic	1500 lbs.	27" - 47"	852.00
FD795504	High profile Hydraulic	880 lbs.	27" - 74"	933.00



DRUM LIFT CARRIER

Lifts and Rotates Drums Easily

Raise, tilt and drain drums easily with controlled pouring. Self contained; simple one man operation. **Manual Lift** pump jack handle to lift drum to dispensing height. **Powered Lift** reduces operator fatigue (12V battery and charger included). 60" high models have hand crank tilt control; others have remote chain. All handle fully-loaded drums up to 800 lbs.; half-full drums up to 500 lbs. tilting capacity. 4 Polyolefin casters roll smoothly, 2-8" rigid on front and 2-4" swivel on rear.

Disp. H"	O.A. W"	MANUAL		POWERED	
		Model	Price	Model	Price
60	44	FD190270	\$1579.00	FD190278	\$2299.00
72	44	FD190272	1659.00	FD190280	2379.00
96	50	FD190276*	1809.00	FD190284*	2529.00

* 96"H Models handle 750 lb. full drums; 375 lb. half-full drum tilting capacity



SCREW TYPE FLOOR LOCK

MOBILE DRUM CARRIER

Raise, transport, rotate, agitate, tilt, and drain fully loaded drums. Self-supporting, transports drum upright to avoid spills. Automatic handle-locks prevent unintentional lowering. Tilt locks used to keep upright or horizontal to dispense. Unlock for manual tipping to any angle or end-over-end tumbling to agitate. Two 8" polyurethane load bearing wheels and 4" swivel caster for optimal maneuverability.

Model	Drum Type	Drum Dia."	Price
FD952800✓	55 Gal. Steel	22 1/2	\$299.00
FD955060	55 Gal. Poly.	22 1/2-24	519.00

AS LOW AS
\$299



SAME DAY
IN STOCK
SHIPMENT
SAVE OVER 25%

800 lb. capacity

PORTABLE HYDRAULIC DRUM JACK

Use with 55-gallon steel drums. Includes two 3" rigid and two 6" swivel casters for portability. Push-handle operated manual hydraulic pump raises and lowers drum. 800 lb. capacity, 5" drum lift height.



SAME DAY
IN STOCK
SHIPMENT



Model	Price
FD300683	\$329.00

STACKABLE DRUM RACK



AS LOW AS
\$84

Stacks 4 High

Supports and stacks 55 gallon drums securely. Steel racks have 4-way forklift access. Welded and bolted steel construction provides maximum protection, accessibility and versatility. Quick and easy to assemble.

Model	Style	W"	Rack Cap.	Price Each		
				1-2	3+	
FD952964	2-Drum	45 1/2	1600 lb.	\$89.95	\$84.00	
FD952966	3-Drum	71 1/2	2400 lb.	129.95	119.00	

DRUM PALLET RACK

Up To 20,000 lb. Capacity

Store up to (16) 30 or 55 gallon drums. Structural 3" all-welded frame uprights with 1" x 1" x 3/16" bracing. 3" channel beams have 5000 lb. capacity per pair, adjust on 2" centers. Adjustable 12" wide drum cradles rest securely on beams. Gray enamel finish. 105"W x 36"D.

STARTER: 2 end frames, 3 or 4 pair of beams and 12 or 16 drum cradles.
ADD-ON: Same as starter less one end frame.



Drum Style	Drum Cap. Ht."	STARTER UNIT Price Each			ADD-ON UNIT Price Each		
		Model	1-2	3+	Model	1-2	3+
3 Tier	12 84	FD793200	\$727.00	\$677.00	FD793202	\$620.00	\$577.00
4 Tier	16 120	FD793204	962.00	895.00	FD793206	823.00	766.00