



# SAFETY DATA SHEET

Issuing Date 13-Sep-2013

Revision Date 28-Oct-2016

Revision Number 1

## 1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND THE COMPANY/UNDERTAKING

### GHS product identifier

**Product Name** SCRUBS® In-A-Bucket

### Other means of identification

**Product Code(s)** 42201, 42210, 42225, 42230, 42256, 42260, 42272, 42280

**Synonyms** None

### Recommended use of the chemical and restrictions on use

**Recommended Use** Heavy Duty Hand Cleaner

**Uses advised against** None reasonably foreseeable

### Supplier's details

**Supplier Address**  
ITW PRO BRANDS  
805 E. Old 56 Highway  
Olathe, KS 66061  
TEL: 1-800-443-9536

### Emergency telephone number

**Emergency Telephone Number** 800-535-5053 Infotrac

## 2. HAZARDS IDENTIFICATION

### Classification

This chemical is not considered hazardous according to the OSHA Hazard Communication Standard 2012 (29 CFR 1910.1200).

Not classified

### GHS Label elements, including precautionary statements

#### Emergency Overview

**Signal Word** None

The product contains no substances which at their given concentration are considered to be hazardous to health

<b>Appearance</b> Colorless-blue/white.	<b>Physical State</b> Liquid.	<b>Odor</b> Citrus.
---	-------------------------------	---------------------

**Precautionary Statements****Prevention**

- None

**General Advice**

- None

**Storage**

- None

**Disposal**

- None

**Hazard Not Otherwise Classified (HNOC)**

Not applicable.

**Other information**

Toxic to aquatic life. Harmful to aquatic life with long lasting effects.

0% of the mixture consists of ingredient(s) of unknown toxicity.

**3. COMPOSITION/INFORMATION ON INGREDIENTS**

Chemical Name	CAS-No	Weight %	Trade secret
Orange Terpenes	5989-27-5	1-5	*
Alcohols, C12-15, ethoxylated	68131-39-5	1-5	*
Isoparaffinic Hydrocarbon	64742-47-8	1-5	*
Dimethyl adipate	627-93-0	1-5	*
Diethylhexyl sodium sulfosuccinate	577-11-7	1-5	*

*\*The exact percentage (concentration) of composition has been withheld as a trade secret.*

**4. FIRST AID MEASURES****Description of necessary first-aid measures**

<b>Eye Contact</b>	Rinse thoroughly with plenty of water, also under the eyelids. Get medical attention if symptoms occur.
<b>Skin Contact</b>	None normally required. Material is designed for skin cleansing. In the case of skin irritation or allergic reactions see a physician.
<b>Inhalation</b>	Move to fresh air. Get medical attention if symptoms occur.
<b>Ingestion</b>	Not an expected route of exposure. If large quantities of this material are swallowed, call a physician immediately.

**Most important symptoms/effects, acute and delayed**

**Most Important Symptoms/Effects** No information available.

**Indication of immediate medical attention and special treatment needed, if necessary**

**Notes to Physician** Treat symptomatically.

**5. FIRE-FIGHTING MEASURES**

**Suitable Extinguishing Media**

Dry chemical. Carbon dioxide (CO<sub>2</sub>). Foam. Water spray or fog.

**Unsuitable Extinguishing Media** None

**Specific Hazards Arising from the Chemical**

None in particular

**Hazardous Combustion Products** Carbon dioxide (CO<sub>2</sub>). Carbon monoxide. Hydrocarbons. Hydrogen sulfide. Sulfur dioxide. Soot.

**Explosion Data**

**Sensitivity to Mechanical Impact**

None.

**Sensitivity to Static Discharge**

None.

**Protective Equipment and Precautions for Firefighters**

Use water spray to cool surrounding containers.

## 6. ACCIDENTAL RELEASE MEASURES

**Personal precautions, protective equipment and emergency procedures**

**Personal Precautions** Use personal protective equipment. Avoid contact with eyes.

**Environmental Precautions**

**Environmental Precautions** Prevent entry into waterways, sewers, basements or confined areas. Avoid release to the environment. See Section 12 for additional Ecological Information.

**Methods and materials for containment and cleaning up**

**Methods for Containment** Prevent further leakage or spillage if safe to do so.

**Methods for Cleaning Up**

Small spillage: Wipe up with absorbent material (e.g. cloth, fleece). Large spillage: Use a non-combustible material like vermiculite, sand or earth to soak up the product and place into a container for later disposal.

## 7. HANDLING AND STORAGE

**Precautions for safe handling**

**Handling** Avoid contact with eyes. Do not smoke. Handle in accordance with good industrial hygiene and safety practice.

**Conditions for safe storage, including any incompatibilities**

**Storage** Keep container closed when not in use. Keep container tightly closed in a dry and well-ventilated place. Keep away from heat and sources of ignition. Do not contaminate food or feed stuffs. Keep out of the reach of children.

**Incompatible Products** Strong oxidizing agents. Strong acids.

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

**Control parameters**

**Exposure Guidelines** This product does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

**Appropriate engineering controls**

**Engineering Measures** Eyewash stations.

**Individual protection measures, such as personal protective equipment**

<b>Eye/Face Protection</b>	None required under normal usage. Risk of contact, wear: Goggles.
<b>Skin and Body Protection</b>	None required under normal usage. Repeated or prolonged contact: Wear protective gloves/clothing.
<b>Respiratory Protection</b>	None required under normal usage. If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn.
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.

**9. PHYSICAL AND CHEMICAL PROPERTIES****Information on basic physical and chemical properties**

<b>Physical State</b>	Liquid.	<b>Appearance</b>	Colorless-blue/white.
<b>Odor</b>	Citrus.	<b>Odor Threshold</b>	No information available.

<u>Property</u>	<u>Values</u>	<u>Remarks/ - Method</u>
<b>pH</b>	6	None known
<b>Melting Point/Range</b>	No data available	None known
<b>Boiling Point/Boiling Range</b>	212 °F	None known
<b>Flash Point</b>	No data available	None known
<b>Evaporation rate</b>	No data available	None known
<b>Flammability (solid, gas)</b>	No data available	None known
<b>Flammability Limits in Air</b>		
upper flammability limit	No data available	
lower flammability limit	No data available	
<b>Vapor Pressure</b>	No data available	None known
<b>Vapor Density</b>	>1	None known
<b>Specific Gravity</b>	0.995	None known
<b>Water Solubility</b>	Miscible with water	None known
<b>Solubility in other solvents</b>	No data available	None known
<b>Partition coefficient: n-octanol/water</b>	No data available	None known
<b>Autoignition Temperature</b>	No data available	None known
<b>Decomposition Temperature</b>	No data available	None known
<b>Viscosity</b>	No data available	None known
<b>Flammable Properties</b>	Not flammable	
<b>Explosive Properties</b>	No data available	
<b>Oxidizing Properties</b>	No data available	

**Other information**

<b>VOC Content (%)</b>	0%
------------------------	----

**10. STABILITY AND REACTIVITY****Reactivity**

Not reactive under normal conditions.

**Chemical stability**

Stable under recommended storage conditions.

**Possibility of hazardous reactions**

None under normal processing.

**Hazardous Polymerization**

Hazardous polymerization does not occur.

**Conditions to avoid**

Incompatible products.

**Incompatible materials**

Strong oxidizing agents. Strong acids.

**Hazardous decomposition products**Carbon dioxide (CO<sub>2</sub>). Carbon monoxide (CO). Hydrocarbons. Hydrogen sulfide. Sulfur dioxide. Soot.**11. TOXICOLOGICAL INFORMATION****Information on likely routes of exposure****Product Information**

<b>Inhalation</b>	Not an expected route of exposure.
<b>Eye Contact</b>	Non-irritating. (rabbit)
<b>Skin Contact</b>	May cause mild skin irritation.
<b>Ingestion</b>	Not an expected route of exposure.

Chemical Name	LD50 Oral	LD50 Dermal	LC50 Inhalation
Orange Terpenes	= 4400 mg/kg ( Rat )	> 5 g/kg ( Rabbit )	-
Dimethyl adipate	= 1920 mg/kg ( Rat )	-	-
Diethylhexyl sodium sulfosuccinate	= 1900 mg/kg ( Rat )	= 10000 mg/kg ( Rabbit )	-

**Symptoms related to the physical, chemical and toxicological characteristics****Symptoms** No information available.**Delayed and immediate effects and also chronic effects from short and long term exposure****Sensitization** The results of testing on guinea pigs showed this material to be non-sensitizing. OECD Test Guideline 406**Mutagenic Effects** No information available.**Carcinogenicity** The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
Orange Terpenes		Group 3		X

**IARC: (International Agency for Research on Cancer)**

Group 3 - Not Classifiable as to its Carcinogenicity to Humans

**OSHA: (Occupational Safety & Health Administration)**

X - Present

**Reproductive Toxicity  
STOT - single exposure**

This product does not contain any known or suspected reproductive hazards. None of the ingredients are known to cause specific target organ effects from a single exposure.

**STOT - repeated exposure**

None of the ingredients are known to cause specific target organ effects through prolonged or repeated exposure.

**Aspiration Hazard**

Not applicable.

**Numerical measures of toxicity - Product****Unknown acute toxicity** 0% of the mixture consists of ingredient(s) of unknown toxicity.*The following values are calculated based on chapter 3.1 of the GHS document:***LD50 Oral** 35696 mg/kg; Acute toxicity estimate**LD50 Dermal** 113740 mg/kg; Acute toxicity estimate

## 12. ECOLOGICAL INFORMATION

### Ecotoxicity

Harmful to aquatic life with long lasting effects.

Chemical Name	Toxicity to Algae	Toxicity to Fish	Toxicity to Microorganisms	Daphnia Magna (Water Flea)
Orange Terpenes 5989-27-5		LC50 96 h: 0.619 - 0.796 mg/L flow-through (Pimephales promelas) LC50 96 h: = 35 mg/L (Oncorhynchus mykiss)		
Isoparaffinic Hydrocarbon 64742-47-8		LC50 96 h: = 2.2 mg/L static (Lepomis macrochirus) LC50 96 h: = 2.4 mg/L static (Oncorhynchus mykiss) LC50 96 h: = 45 mg/L flow-through (Pimephales promelas)		LC50 96 h: = 4720 mg/L (Daphnia magna)
Diethylhexyl sodium sulfosuccinate 577-11-7		LC50 96 h: 20 - 40 mg/L semi-static (Oncorhynchus mykiss) LC50 96 h: < 24 mg/L static (Oncorhynchus mykiss) LC50 96 h: = 37 mg/L static (Lepomis macrochirus)		EC50 48 h: = 36 mg/L (Daphnia magna)

**Persistence and Degradability** No information available.

**Bioaccumulation** No information available.

### Other Adverse Effects

No information available.

## 13. DISPOSAL CONSIDERATIONS

**Waste Disposal Methods** This material, as supplied, is not a hazardous waste according to Federal regulations (40 CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local regulations for additional requirements.

**Contaminated Packaging** Do not re-use empty containers.

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical Name	California Hazardous Waste
Orange Terpenes	Toxic

## 14. TRANSPORT INFORMATION

**DOT** Not regulated

**TDG** Not regulated

**MEX** Not regulated

**ICAO** Not regulated

**IATA** Not regulated

**IMDG/IMO** Not regulated

**RID** Not regulated

**ADR** Not regulated

**ADN** Not regulated

## 15. REGULATORY INFORMATION

### International Inventories

**TSCA** Not determined

**DSL** All components are listed either on the DSL or NDSL.

### Legend

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

### U.S. Federal Regulations

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.

### SARA 311/312 Hazard Categories

<b>Acute Health Hazard</b>	No
<b>Chronic Health Hazard</b>	No
<b>Fire Hazard</b>	No
<b>Sudden Release of Pressure Hazard</b>	No
<b>Reactive Hazard</b>	No

### Clean Water Act

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

### CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

### U.S. State Regulations

#### California Proposition 65

This product does not contain any Proposition 65 chemicals.

### U.S. State Right-to-Know Regulations

"X" designates that the ingredients are listed on the state right to know list.

Chemical Name	New Jersey	Massachusetts	Pennsylvania	Illinois	Rhode Island
Orange Terpenes	X			X	

### U.S. EPA Label Information

**EPA Pesticide Registration Number** Not applicable

## 16. OTHER INFORMATION

**NFPA** Health Hazard 1 Flammability 0 Instability 0 Physical and Chemical Hazards -

**HMIS** Health Hazard 1 Flammability 0 Physical Hazard 0 Personal Protection X

**Prepared By** Product Stewardship  
23 British American Blvd.  
Latham, NY 12110  
1-800-572-6501

**Issuing Date** 13-Sep-2013

---

Revision Date	28-Oct-2016
Revision Note	Change to composition.

**General Disclaimer**

The information provided on this SDS is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guide for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered as a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other material or in any process, unless specified in the text.

**End of Safety Data Sheet**