

FOLDING BULK CONTAINERS

Save Time, Money and Space!

These 100% polyethylene shipping containers resist rust, odors and moisture. Structurally reinforced at all stress points for added strength and stability. Smooth interior surface cleans easily. FDA approved for food processing applications. 4-way forklift access. 3:1 return ratio reduces shipping costs. Positive **interlocking corners for secure stacking**. 2 hinged drop doors for easy access to contents. Spring latches automatically lock sidewalls for set-up and quick folding.



O.D. L" x W" x H"	Inside H"	Folding H"	Volume Cu. Ft.	Cap. Lbs.	CONTAINER		STACKING LID	
					Model	Price	Model	Price
32 x 30 x 34	26 1/2	15	13.3	1800	FD155208	\$189.00	FD155214	\$59.00
48 x 45 x 25	19	13	19.0	1500	FD155215	259.95	FD155212	59.00
48 x 40 x 34	27	15	25.3	1600	FD155217	329.95	FD155209	59.00
48 x 45 x 34	28 1/2	12 3/4	28.5	2000	FD442211	235.95	FD155212	59.00
48 x 40 x 39	32	15	30.2	1600	FD155218	354.95	FD155209	59.00

AS LOW AS
\$189

SAME DAY
IN STOCK
SHIPMENT

STEEL FOLDING BULK CONTAINER DOLLIES

Mobilize the bulk containers easily. Rugged steel dolly with 5" phenolic casters, 2 swivel, 2 rigid.

Model	Container Footprint L" x W"	Price
FD442742	32 x 30	\$205.95
FD239675	48 x 40	229.95
FD239676	48 x 45	239.95



ORBIS® FOLDING BULK CONTAINERS


Folds when empty to reduce costs on return freight and storage. Structurally reinforced foam molded high density black polyethylene resists rust, odors and moisture. Allows **positive stacking to reduce floor space**. 2 drop down doors for access to contents. Large, spring-loaded ergonomic latches make collapsing containers and opening/closing access doors easy. Convenient four-way forklift access.



O.D. L" x W" x H"	Cap. Lbs.	CONTAINER	Price	LID	Price
32 x 30 x 25	2000	FD268644	\$214.95	FD268650	\$54.95
32 x 30 x 34	2000	FD268645	245.95	FD268650	54.95
48 x 45 x 25	1500	FD268646	285.95	FD268652	68.95
48 x 45 x 34	1500	FD268647	299.95	FD268652	68.95
48 x 40 x 34	2000	FD268648	335.95	FD268651	58.95
48 x 40 x 39	2000	FD268649	355.95	FD268651	58.95

BUCKHORN™ FOLDING BULK CONTAINERS

Polyethylene structural foam resist oils, chemicals and moisture and provides a smooth, easy-to-clean interior. 2 hopper gates are included on the longest sides for **easy access, even when stacked**. **Style A** has spring loaded latches for quick and easy set-up or knock-down. **Style B** with interlocking side panels add durability, strength and fast set-up. Equipped with steel corner guards for protection from forklifts. Models **FD238255** and **FD238256** have steel runners on bottom for added strength and durability. Black Lids sold separately.



STEEL
CORNER GUARD

AS LOW AS
\$319

Style	Color	O.D. L" x W" x H"	Folding H"	Fork Entry	Cap. Lbs.	CONTAINER		LID	
						Price	Price	Price	Price
A	Blue	32 x 30 x 25	12 1/2	2	1200	FD238252	\$319.00	FD238257	\$72.95
A	Black	32 x 30 x 30	15	2	1200	FD238253	349.95	FD238257	72.95
B	Black	32 x 30 x 34	15 1/2	4	1800	FD238254	373.95	FD238257	72.95
B	Black	48 x 40 x 34	12	4	2500	FD238255	473.95	FD238258	79.95
B	Black	48 x 45 x 34	12	4	2500	FD238256	494.95	FD238259	88.95

SUPER VALUE! EASY ASSEMBLY BULK CONTAINERS

Made from structurally reinforced high density blue polypropylene. Hold up to 600 lbs. Included feet allow containers to stack up to 4 high for 2000 lb. total capacity. Stacking feet allow 4-way fork entry. Easy-to-assemble with included hardware. Ships flat for reduced shipping costs. Measures 39 1/4"L x 31 1/2"W x 29"H overall. Available with mesh or solid sides. **Hinged Lid and Caster Kit** sold separately. Caster Kit with swivel casters (2 with brakes) withstands 2000 lb. loads.



AS LOW AS
\$124



Online
Video
& Photos

STACKING
FEET

Stacks
4 High



FD603087
WITH OPTIONAL
CASTERS

Model	Description	Price	FD239452 SHOWN WITH OPTIONAL LID
FD603087	Mesh sides container	\$124.00	
FD239452	Solid sides container	134.95	
FD239453	Solid hinged lid	62.95	
FD603088	Castors (4 swivel, 2 locking)	31.95	

SAME DAY
IN STOCK
SHIPMENT

1-800-645-1232

globalindustrial.com