

1300 Series

VINYL PREMIUM TRIPLE-BRACE



products meet or exceed applicable ANSI/BIFMA standards



MODEL 1304 SHOWN



480lb. weight capacity!

SPECS:

- Features 18-gauge 7/8" round tubular frame
- Three U-shaped double riveted cross braces
- Powder-coated frame
- Double hinges for added stability and durability
- Color coordinated V-tip plugs for added stability
- Color coordinated polypropylene glides
- Features our unique full size double contoured back and waterfall seat
- Vinyl and foam are Cal-117 rated
- .80MM Vinyl over 1 1/4", 0.9lb. density foam seat and 1.2lb. density back
- Fully upholstered seat and back attached with 6 rivets

DIMENSIONS:

OVERALL: 29 1/2"H X 18 3/4"W X 20 3/4"D

FOLDED: 38"H X 18 3/4"W X 2 1/2"D


SEAT: 17 3/4"H X 16"W X 16"D

BACK: 8 3/4"H X 18 3/4"W

CAL-117 RATED

VINYL / FRAME COMBINATIONS

	#1301 FRENCH BEIGE VINYL / BEIGE FRAME
	#1302 WARM GREY VINYL / GREY FRAME
	#1304 DARK MIDNIGHT BLUE VINYL / CHAR-BLUE FRAME



USE WITH:

Model #84
Double-Tier Hanging
Chair Truck

CAPACITY: HOLDS UP TO 84 FOLDING
CHAIRS (1300 SERIES)

Model #DY35/#DY50
Folding Chair Dolly

CAPACITY: DY35 HOLDS UP TO 35
FOLDING CHAIRS (1300 SERIES)
DY50 HOLDS UP TO 50
FOLDING CHAIRS (1300 SERIES)

FOR
VERTICAL
FOLDING
STORAGE



AVAILABLE ACCESSORIES



#PGC1
GANGING DEVICE



GLIDES



#MGC1
GANGING DEVICE



V-TIPS

**National
Public
Seating**

