

FEATURES & SPECIFICATIONS

INTENDED USE — Built on the compact, low-profile Z strip channel, this LED strip offers long maintenance-free life, several color temperatures, lumen outputs and lengths. Ideal for new construction and retrofit applications in T5 and T8 lengths. Ideal for uplight and downlight in commercial, retail, manufacturing, warehouse, cove and display applications. **Certain airborne contaminants can diminish integrity of acrylic.** <u>Click here for Acrylic Environmental Compatibility table for suitable uses</u>.

CONSTRUCTION — Compact-design channel and cover are formed from code-gauge cold-rolled steel. Easy to install row aligner included for continuous row mounting.

Finish: Paint options include high-gloss, baked white enamel (WH), galvanized (GALV), matte black (MB) and smoke gray (SKGY). Five-stage iron phosphate pre-treatment ensures superior paint adhesion and rust resistance.

OPTICS — Standard diffuse snap on/snap off lens eliminates pixels, improves uniformity and minimizes glare. L/LENS option available.

ELECTRICAL — Utilizes high-output LEDs integrated on a two-layer circuit board, ensuring coolrunning operation. Optional internal pluggable wiring harness for reduced labor cost in row mounting applications. (See PLR_ ordering information on page 3.) Electronic LED driver is rated for 75 input watts maximum (see Operational Data on page two for actual wattage consumption), **multi-volt input and 0-10V dimming standard**. This fixture is designed to withstand a maximum line surge of 1.5kV at 0.75kA combination wave for indoor locations, for applications requiring higher level of protection additional surge protection must be provided.

LEDs provide nominal 80 CRI at 3000 K, 3500 K,4000 K, or 5000 K.

Lumen output up to 2,000 lumens per foot. In $86^{\circ}F$ ($30^{\circ}C$) ambient environments. Luminaire should be installed in applications where ambient temperatures do not exceed $86^{\circ}F$ ($30^{\circ}C$).

INSTALLATION — Tool-less channel cover for easy installation.

Fixture may be surface mounted (with or without ZSPRG hanger), pendant or stem mounted with appropriate mounting options. Three-point aligner locks in place for easy continuous row mounting.

LISTINGS — CSA certified to US and Canadian safety standards. For use in damp locations between $-4^{\circ}F$ ($-20^{\circ}C$) and $86^{\circ}F$ ($30^{\circ}C$).

DesignLights Consortium® (DLC) qualified product. Not all versions of this product may be DLC qualified. Please check the DLC Qualified Products List at <u>www.designlights.org</u> to confirm which versions are qualified.

WARRANTY — 5-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Note: Actual performance may differ as a result of end-user environment and application.

All values are design or typical values, measured under laboratory conditions at 25 °C.

Specifications subject to change without notice.



ORDERING INFORMATION Lead times will vary depending on options selected. Consult with your sales representative. Example: ZL1N L48 3000LM FST MVOLT 40K 80CRI WH

Catalog

Number

Series		Length		Nominal lumens ¹		Diffuser		Voltage		Color temperature		Color rendering index		Options		Paint finish	
ZL1N	LED striplight	L24 L46 L48	24" 46" 48"	1500LM 2500LM 3500LM 3000LM 5000LM 7000LM	1,500 lumens ² 2,500 lumens ² 3,500 lumens ² 3,000 lumens ² 5,000 lumens 7,000 lumens	FST L/LENS SBL	Snap on frosted, diffuse No diffuser Straight blade louver	MVOLT 120 208 240 277 347	120-277V 120V 208V 240V 277V 347V ³	30K 35K 40K 50K	3000 K 3500 K 4000 K 5000 K	80CRI 90CRI	80 CRI 90 CRI	PLR PLR1LVG E7W	Plug-in wiring⁴ Plug-in wiring- low voltage⁵ Emer-	WH GALV MB SKGY	White Galvanized Matte black Smoke gray
TZL1N	LED striplight	L92 L96	92" 96"	6000LM 10000LM 14000LM	6,000 lumens ² 10,000 lumens 14,000 lumens			480	480V ³						gency battery pack ^{3,6}		


Accessories: Order as separate catalog number.										
HC36	Hanger chain, 36"	LSXR	Sensor Switch [®] LSXR occupancy sensor ²							
ZACVH	Aircraft cable 10' (one pair)	ZSPRG	For 15/16" T-grid only							
ZLANGBKT	Luma-tilt™ angle bracket for shelf or ledge mounting only	WGZ24	24" wireguard, white							
NPP16D	nLight® switching/dimming module	WGZ48	48" wireguard, white ⁷							

Notes

- 1 See Operational Data on page 2 for actual lumens.
- 2 Not available with 0-10V dimming option.
- 3 Not available with L24, 24" fixture. 347V and 480V utilize a step-down transformer.
- 4 See ordering information on page
- 5 Must use ZSPRG for surface mounting when ordering this option.
- 6 Must specify voltage. 120, 208, 240 or 277V.
- 7 Order 2 for tandem double length fixtures (TZL1N).

	OPERATIONAL DATA												
	Nominal Iumen package	Length (inches)	Delivered lumens 3000 K CCT @ 77°F (25°C) ambient temperature	Delivered lumens 3500 K CCT @ 77°F (25°C) ambient temperature	Delivered lumens 4000 K CCT @ 77°F (25°C) ambient temperature	Delivered lumens 5000 K CCT @ 77°F (25°C) ambient temperature	Wattage @120V	Comparable light source					
	1,500LM	24	1,693	1,725	1,781	1,797	16W	1-lamp 17W T8					
	2,500LM	24	3,059	3,118	3,220	3,247	22W	1-lamp 17W T8					
	3,500LM	24	3,722	3,793	3,917	3,951	36W	1-lamp 32W T8, 1-lamp 54W T5H0, 50W HID					
-	3,000LM	46 or 48	3,505	3,572	3,688	3,720	30W	1-lamp 32W T8, 1-lamp 54W T5H0, 50W HID					
Lensed	5,000LM	46 or 48	4,912	5,006	5,169	5,213	38W	2-lamp 32W T8, 1-lamp 54W T5H0, 70W HID					
-	7,000LM	46 or 48	6,916	7,049	7,278	7,341	62W	3-lamp 32W T8, 2-lamp 54W T5H0, 100W HID					
	6,000LM	92 or 96	7,010	7,144	7,377	7,440	59W	3-lamp 32W T8, 2-lamp 54W T5H0, 100W HID					
	10,000LM	92 or 96	9,823	10,012	10,338	10,427	76W	4-lamp 32W T8, 2-lamp 54W T5H0, 100W HID					
	14,000LM	92 or 96	13,832	14,098	14,556	14,682	123W	4-lamp 32W T8, 3-lamp 54W T5H0, 150W HID					
	1,500LM	24	1,854	1,890	1,951	1,968	16W	1-lamp 17W T8					
	2,500LM	24	3,351	3,415	3,527	3,557	22W	1-lamp 17W T8					
	3,500LM	24	4,076	4,155	4,290	4,327	36W	1-lamp 32W T8, 1-lamp 54W T5H0, 50W HID					
pa	3,000LM	46 or 48	3,921	3,996	4,126	4,162	30W	1-lamp 32W T8, 1-lamp 54W T5H0, 50W HID					
Unlensed	5,000LM	46 or 48	5,495	5,600	5,783	5,832	38W	2-lamp 32W T8, 1-lamp 54W T5H0, 70W HID					
5	7,000LM	46 or 48	7,737	7,886	8,142	8,213	62W	3-lamp 32W T8, 2-lamp 54W T5H0, 100W HID					
	6,000LM	92 or 96	7,842	7,993	8,253	8,324	59W	3-lamp 32W T8, 2-lamp 54W T5H0, 100W HID					
	10,000LM	92 or 96	10,990	11,201	11,565	11,665	76W	4-lamp 32W T8, 2-lamp 54W T5H0, 100W HID					
	14,000LM	92 or 96	15,475	15,772	16,285	16,425	123W	4-lamp 32W T8, 3-lamp 54W T5H0, 150W HID					

DIMENSIONS



PHOTOMETRICS

Please see <u>www.lithonia.com</u>.

PRODUCT INFORMATION

Advanced plug-in system with three-circuit capability. Available on industrial and strip products and a variety of architectural products mounted in continuous rows. 1, 2, 3 and 4-lamp fixtures. PLR22 (2-circuit) and PLR33 (3-circuit) crossover harness switches hot circuit serving next fixture in row. Reduces fixture types on job for alternating circuit applications (see example below.)

Easy one-step installation, saves up to 35% on labor costs. Expanded switching flexibility helps save energy.

Rows can be 50% longer with two-circuit systems. Polarized, lock-together nylon connectors prevent miswiring in the field. #12 THHN conductor, rated 600V, 90°C. White neutral wire included. Grounding accomplished by fixture in-row connectors.

CSA certified systems available with up to 2 circuits. G ground required.

Note: Specifications subject to change without notice.

ORDERING INFORMATION Lead times will vary depending on options selected. Consult with your sales representative.



Wiring

Advanced 3-Circuit Plug-In

Series	Number	of hot wires	Branch circuits					iming	Ground		
PLR PLR22 PLR33	(blank) 1 2 3	Not required for 22 or 33 Black Black and red Black, red and blue	<u>Circuits to</u> (blank) A	o which ballast is connected Not required for 22 or 33 Black wire	B C	Red wire Blue wire	LV	Low-voltage dimming	(blank) G	No ground in PLR Ground. Maximum 2 circuits	

Typical Applications

- Multiple-circuit and single-circuit for longer continuous rows
- Multiple-circuit with alternating fixtures on separate circuits, 2-circuit (PLR 22) and 3-circuit (PLR 33)
- Multiple circuit with night-lights located along row as desired

	TYPICAL APPLICATIONS												
PLR 3 C	PLR 3 C	PLR 3 C	PLR 3 C	PLR 2 B	PLR 2 B	PLR 2 B	PLR 2 B	PLR 1	PLR 1	PLR 1			
(All PLR22)													
Circuit A	Circuit B	Circuit A	Circuit B	Circuit A	Circuit B	Circuit A	Circuit B	Circuit A	Circuit B	Circuit A			
(All PLR33)													
Circuit A	Circuit B	Circuit C	Circuit A	Circuit B	Circuit C	Circuit A	Circuit B	Circuit C	Circuit A	Circuit B			
PLR 3 A	PLR 3 A	PLR 3 A	PLR 3 C	PLR 3 B	PLR 3 B	PLR 3 B	PLR 3 C	PLR 3 A	PLR 3 A	PLR 3 A			

PRODUCT INFORMATION

A standard occupancy time delay is also present to ensure lights turn off (once minimum on timer has also elapsed) if no occupancy is detected.

This timer is factory set at 10 minutes to promote energy savings, but is adjustable between 30 seconds and 30 minutes. These adjustments may be done through the unit's push-button.

FEATURES

- Four interchangeable lenses high mount 360°, low mount 360°, high mount aisleway, and small motion 360°.
- Integrated mounting bracket drops lens down 3" from chase nipple no bracket accessory required.
- 100% digital PIR detection provides excellent RF immunity

Note: Specifications subject to change without notice.

ORDERING INFORMATION



LSXR

Passive Infrared Indoor Occupancy Sensor

Single Relay

sensorswitch

Example: LSXR 10 ADC HVOLT 30M

LSXR													
Series Lens option								Dimming/photocell					
Occupancy Sensor 6 10 50				No lens610High and low mount 360°High mount, 360°650High mount 360° and aislewayLow mount, 360°3PKHigh and low mount 360° and aislewayHigh mount aisleway4PKAll lensesSmall motion, 360°500500						(blank) None HL High/low occupancy operation P Switching photocell (on/off) ADC Dimming and switching photocell ANL Dimming and switching photocell with high/low occupancy operation			
Voltage	1	Max dim level		Min dim level				Lead length Temp hur			idity	ime delay	
(blank) HVOLT	120-277 VAC (MVOLT) 347-480 VAC	(blank) 9H 8H 7H	10 VDC 9 VDC 8 VDC 7 VDC	(blank) 1V 2V 3V 4V 5V 6V	Minimum dim 1 VDC 2 VDC 3 VDC 4 VDC 5 VDC 6 VDC	iming leve	el of ballast	(blank) 42L	14" 42"	(blank) LT	None Low temperature	(blank) 5M 15M 20M 30M	10 minutes (with minimum 15 minutes on time) 5 minutes (LED only) 15 minutes 20 minutes 30 minutes

Lead times will vary depending on options selected. Consult with your sales representative.

For additional information see www.lithonia.com

OPTIONS AND ACCESSORIE

The Z Series fixture offers numerous options for almost every electrical and optical component, including a long list of field-installable accessories.



HANGER CHAIN

36" chain with Y hanger.


Order as: HC36



Z SPRING HANGER

Snap 'n' lock design requires no fasteners and can be used on T-grid ceiling or universal mounting systems.

Order as: ZSPRG



ZACVH HANGER 10' Aircraft cable with Y hanger.


Order as: ZACVH



ANGLE MOUNTING BRACKET

Luma-tilt[™] angle bracket ships as a pair

Order as: ZLANGBKT



WIRE GUARD

Order as: WGZ24 WGZ48



ZL1N