



Safety Data Sheet according to Regulation (EC) No1907/2006

Page 1 of 7

SDS No. : 407823
V003.2

TECHNOMELT PUR 3450 ME known as Purmelt ME 3450

Revision: 31.01.2014
printing date: 21.05.2015

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

TECHNOMELT PUR 3450 ME known as Purmelt ME 3450

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Poly urethan hotmelt

1.3. Details of the supplier of the safety data sheet

Henkel AG & Co. KGaA

Henkelstr. 67

40589 Düsseldorf

Germany

Phone: +49 (211) 797 0

Fax-no.: +49 (211) 798 4008

ua-productsafety.de@henkel.com

1.4. Emergency telephone number

The Henkel information service also provides an around-the-clock telephone service on phone no.+49-(0)211-797-3350 for exceptional cases.

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

Classification (DPD):

No classification required.

2.2. Label elements

Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

Supplemental information

EUH204 Contains isocyanates. May produce an allergic reaction.

Label elements (DPD):

The product is not subject to classification according to the calculation methods of the "General Classification Guideline for Preparations of the EC" as issued in the last version.

Additional labeling:

Contains isocyanates. See information supplied by the manufacturer.

2.3. Other hazards

Contains isocyanate monomer below the concentration limit for consideration.

SECTION 3: Composition/information on ingredients

General chemical description:

1-Component PU adhesive

Base substances of preparation:

Polyurethane prepolymer with isocyanate groups

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Contains no dangerous substances exceeding the limits of the EU-Regulation

Declaration of ingredients according to DPD (EC) No 1999/45:

Contains no dangerous substances exceeding the limits of the EU-Regulation

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air, consult doctor if complaint persists.

Skin contact:

Molten product. After skin contact cool down immediately with cold water. Do not remove adherent product. Seek medical advice.

Eye contact:

After contact with the hot melt: cool with water, seek medical attention.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

All common extinguishing agents are suitable.

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In case of fire toxic gases can be released.

5.3. Advice for firefighters

- Wear protective equipment.
- Wear self-contained breathing apparatus.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

- Wear protective equipment.
- Avoid contact with skin and eyes.

6.2. Environmental precautions

- Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

- Allow to solidify.
- Remove mechanically.
- Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

- See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Hygiene measures:

- Do not eat, drink or smoke while working.
- Wash hands before work breaks and after finishing work.

7.2. Conditions for safe storage, including any incompatibilities

- Ensure good ventilation/extraction.
- Store in a cool place in closed original container.
- Store in a cool, frost-free place.

7.3. Specific end use(s)

- Poly urethan hotmelt

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**

Valid for
Germany

Ingredient	ppm	mg/m ³	Type	Category	Remarks
4,4'-Methylenediphenyl diisocyanate 101-68-8			Short Term Exposure Classification:	Category I: substances for which the localized effect has an assigned OEL or for substances with a sensitizing effect in respiratory passages.	TRGS 900
4,4'-Methylenediphenyl diisocyanate 101-68-8		0,05	AGW:	=2= If the AGW and BGW values are complied with, there should be no risk of reproductive damage (see Number 2.7).	TRGS 900
4,4'-Methylenediphenyl diisocyanate 101-68-8			STEL factor:	1 Substance listed with both Peak factor and STEL factor. The Peak factor is supplied with the AGW values.	TRGS 900

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

In case of dust formation, we recommend wearing of appropriate respiratory protection equipment with particle filter P.
This recommendation should be matched to local conditions.

Hand protection:

Wear refractive gloves while working with the hot melt.

Eye protection:

Protective goggles

Skin protection:

Protective clothing that covers arms and legs.

Advices to personal protection equipment:

Use only personal protection that's CE-labelled according to the regulation no. 819 of 19 August 1994.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	solid material solid beige
Odor	characteristic
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	No flash point up to 200 °C
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density	No data available / Not applicable
Bulk density	No data available / Not applicable
Viscosity	5.000 - 8.500 mPa.s
(Brookfield; 130 °C (266 °F); speed of rotation: 10 min-1; Spindle No: 27)	
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative) (20 °C (68 °F); Solvent: Water)	Insoluble
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

Reaction with water, alcohols, amines.

Reacts with water: Pressure built up in closed vessel (CO₂).

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Humidity

10.5. Incompatible materials

See section reactivity

10.6. Hazardous decomposition products

At higher temperatures isocyanate may be released.

Carbon dioxide is generated under contact with moisture, leading to pressure in the cans. Danger of cans bursting!

SECTION 11: Toxicological information

11.1. Information on toxicological effects

General toxicological information:

To the best of our knowledge no harmful effects are to be expected if the product is handled and used properly.

Persons suffering from allergic reactions to isocyanates should avoid contact with the product.

SECTION 12: Ecological information

General ecological information:

Do not empty into drains, soil or bodies of water.

12.1. Toxicity

No data available.

12.2. Persistence and degradability

No data available.

12.3. Bioaccumulative potential / 12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

No data available.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

In consultation with the responsible local authority, must be subjected to special treatment.

Waste code

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

08 04 10 Waste adhesives and sealants other than those mentioned in 08 04 09.

SECTION 14: Transport information**14.1. UN number**

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.4. Packaging group

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content 0 %
(VOCV 814.018 VOC regulation
CH)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

National regulations/information (Germany):

WGK: 1, slightly water-endangering product. (German VwVwS of July 27, 2005)
Classification in conformity with the calculation method

Storage class according to TRGS 510: 11

SECTION 16: Other information

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.