

COMMERCIAL FAN-FORCED WALL HEATERS

FRA SERIES



APPLICATIONS:

Attics
Basements
Entryways
Large Rooms
Offices
Remodels

CONTEMPORARY DESIGN

- Commercial grade steel grille designed to provide comfort through optimized airflow

UNIFORM DISTRIBUTION OF WARMTH

- Built-in fan delay switch energizes fan motor only after elements are heated, which prevents discharge of unheated air
- Fan only operation for summer use
- Integral double pole thermostat allows for easy adjustment of room temperature to maintain desired comfort level

SAFETY STANDARDS COMPLIANT


- Safety Listed by Intertek (ETL) for use in the USA and Canada complying with ANSI/UL2021 and C22.2, NO. 56 Safety Standards
- Manual reset thermal overheat protector disconnects power in the event of overheating due to accidental blockage

DURABILITY AND EASY MAINTENANCE

- All units have a permanently lubricated totally enclosed fan motor, which creates long life and low maintenance, and gently distributes warmth throughout the area
- Built-in power disconnect switch for added safety during maintenance

Catalog Number	Voltage	Phase	Watts	Amps
FRA1512F	120	1	1500	12.5
FRA1812F	120	1	1800	15.0
FRA4024F	240	1	4000/2000	16.7/8.3
	208		3000/1500	14.5/7.2
FRA4027F	277	1	4000/ 2000	14.5/ 7.2
	240		3000/1500	12.5/6.3
FRA3027F	277	1	3000/1500	10.8/5.4
FRA4020F	208	1	4000/2000	19.2/9.6
FRA40203F	208	3	4000	11.1
FRA40243F	240	3	4000	9.7
FRA4824F	240/208	1	4800/3600	20.0/17.3
FRA4827F	277/240	1	4800/3600	17.3/15.0
FRA4820F	208	1	4800	23.1
FRA48203F	208	3	4800	13.4
FRA48243F	240	3	4800	11.6
FRA3203F	347	1	2000	5.8
FRA3206F	600	1	2000	3.3
FRA3153F	347	1	1500	4.3
FRA3156F	600	1	1500	2.5
FRA3303F	347	1	3000	8.6
FRA3306F	600	1	3000	5
FRA3403F	347	1	4000	11.5
FRA3406F	600	1	4000	6.7
FRA3503F	347	1	4800	13.8
FRA3506F	600	1	4800	8
Accessories				
FRASM	Surface mounting frame			
FRAS1	1" Semi-recessed frame			
FRAS2	2" Semi-recessed frame			
FRAFCTP	Tamper-proof front cover			

DIMENSIONS



MOUNTING LIMITATIONS

Do not install heater closer than 8" from floor or adjacent wall surface, behind towel rack or door, upside down or side up, in floor, ceiling or closet.

