



Safety Data Sheet

Big D Deodorant Concentrate, Cherry

SECTION 1. IDENTIFICATION

Product Identifier	Big D Deodorant Concentrate, Cherry
Other Means of Identification	121300, 321300, 421300, 521300, & C0421303
Other Identification	Deodorant Concentrate, Cherry
Product Family	Liquid Deodorants
Recommended Use	Deodorant.
Restrictions on Use	None known.
Manufacturer	Big D Industries, Inc., 5620 SW 29th St, Oklahoma City, OK, 73179, 405 682 2541, BigDInd.com
Supplier	Big D Industries, Inc., 5620 SW 29th St, Oklahoma City, OK, 73179, 405 682 2541, BigDInd.com
Emergency Phone No.	Big D Industries, 800 535 5053, 24hr (Infotrac)
SDS No.	0408

SECTION 2. HAZARDS IDENTIFICATION

GHS Classification

Serious eye damage/eye irritation - Category 1

GHS Label Elements



Signal Word:
Danger

Hazard Statement(s):
Causes serious eye damage.

Precautionary Statement(s):
Prevention:
Wear eye protection/face protection.

Response:
IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
Immediately call a POISON CENTRE/doctor.

Product Identifier:	Big D Deodorant Concentrate, Cherry
SDS No.:	0408
Date of Preparation:	March 27, 2015

Storage:
Store in accordance with local, regional, national and international regulations.

Disposal:
Dispose of contents/container in accordance with local, regional, national and international regulations.

Other Hazards

None known.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Mixture:

Chemical Name	CAS No.	%	Other Identifiers
Other components below reportable Levels	No CAS	92.76	
Poly(oxy-1,2-ethanediyl), alpha-octyl- omega-hydroxy-	27252-75-1	3.50	
2-Propanol	67-63-0	1.81	
Benzaldehyde	100-52-7	0.92	
Dipropylene glycol monomethyl ether	34590-94-8	0.48	
Ethyl acetate	141-78-6	0.23	
Benzyl acetate	140-11-4	0.15	
n-Amyl acetate	628-63-7	0.15	

SECTION 4. FIRST-AID MEASURES

First-aid Measures

Inhalation

Move to fresh air.

Skin Contact

Wash gently and thoroughly with lukewarm, gently flowing water and mild soap for 5 minutes.

Eye Contact

Immediately rinse the contaminated eye(s) with lukewarm, gently flowing water for 15-20 minutes, while holding the eyelid(s) open.

Ingestion

Call a Poison Centre or doctor if you feel unwell or are concerned. Rinse mouth with water.

Most Important Symptoms and Effects, Acute and Delayed

If on skin:

May cause mild irritation.

Immediate Medical Attention and Special Treatment

Special Instructions

Not applicable.

Medical Conditions Aggravated by Exposure

None known.

SECTION 5. FIRE-FIGHTING MEASURES

Extinguishing Media

Suitable Extinguishing Media

Not combustible. Use extinguishing agent suitable for surrounding fire.

Product Identifier: Big D Deodorant Concentrate, Cherry

SDS No.: 0408

Date of Preparation: March 27, 2015

Unsuitable Extinguishing Media

None known.

Specific Hazards Arising from the Chemical

Does not burn.

This product presents no unusual hazards in a fire situation.

Not known to generate any hazardous decomposition products in a fire.

Special Protective Equipment and Precautions for Fire-fighters

No special precautions are necessary.

Chemical protective clothing (e.g. chemical splash suit) and positive pressure SCBA may be necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal Precautions, Protective Equipment, and Emergency Procedures

No special precautions are necessary.

Environmental Precautions

It is good practice to prevent releases into the environment.

Methods and Materials for Containment and Cleaning Up

Contain and soak up spill with absorbent that does not react with spilled product.

SECTION 7. HANDLING AND STORAGE

Precautions for Safe Handling

No special handling precautions are necessary.

Conditions for Safe Storage

No special requirements for storage area.

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters

Chemical Name	ACGIH TLV®		OSHA PEL		AIHA WEEL	
	TWA	STEL	TWA	Ceiling	8-hr TWA	TWA
2-Propanol	200 ppm	400 ppm	980 mg/m3			
Dipropylene glycol monomethyl ether	100 ppm	150 ppm	600 mg/m3			
Ethyl acetate	400 ppm		1400 mg/m3			
Benzyl acetate	10 ppm					
n-Amyl acetate	50 ppm	100 ppm	525 mg/m3			

ACGIH® = American Conference of Governmental Industrial Hygienists. TWA = Time-Weighted Average. STEL = Short-term Exposure Limit.

Appropriate Engineering Controls

The hazard potential of this product is relatively low. General ventilation is usually adequate.

Individual Protection Measures

Eye/Face Protection

Not required but it is good practice to wear safety glasses or chemical safety goggles.

Skin Protection

Not required, if used as directed.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Basic Physical and Chemical Properties

Product Identifier: Big D Deodorant Concentrate, Cherry

SDS No.: 0408

Date of Preparation: March 27, 2015

Appearance	liquid. Particle Size: Not applicable
Odour	Fragrant (Fragrance)
Odour Threshold	Not available
pH	Not available
Melting Point/Freezing Point	Not available (melting); Not available (freezing)
Initial Boiling Point/Range	> 212 °F (100 °C)
Flash Point	> 200 °F (93 °C) (closed cup)
Evaporation Rate	Not available
Flammability (solid, gas)	Not applicable
Upper/Lower Flammability or Explosive Limit	Not available (upper); Not available (lower)
Vapour Pressure	Not available
Vapour Density (air = 1)	Not available
Relative Density (water = 1)	~ 1 at 68 °F (20 °C)
Solubility	Soluble in all proportions in water; Not available (in other liquids)
Partition Coefficient, n-Octanol/Water (Log Kow)	Not available
Auto-ignition Temperature	Not available
Decomposition Temperature	Not available
Viscosity	Not available (kinematic)
Other Information	
Physical State	Liquid
Molecular Formula	Not applicable
Molecular Weight	Not applicable
Bulk Density	Not available
Surface Tension	Not available
Critical Temperature	Not available
Electrical Conductivity	Not available
Vapour Pressure at 50 deg C	Not available
Saturated Vapour Concentration	Not available

SECTION 10. STABILITY AND REACTIVITY

Reactivity

None known.

Chemical Stability

Normally stable.

Possibility of Hazardous Reactions

None known.

Conditions to Avoid

None known.

Incompatible Materials

None known.

Hazardous Decomposition Products

None known.

SECTION 11. TOXICOLOGICAL INFORMATION

Likely Routes of Exposure

Skin contact; eye contact; ingestion; inhalation.

Acute Toxicity

Chemical Name	LC50	LD50 (oral)	LD50 (dermal)
2-Propanol	72.6 mg/L (rat) (vapour)	4396 mg/kg (rat)	12870 mg/kg (rabbit)
Dipropylene glycol monomethyl ether		5135 mg/kg	9500 mg/kg
Benzaldehyde		> 1300 mg/kg (rat)	> 2000 mg/kg (guinea pig)
Ethyl acetate	16000 mg/L (rat)	5600 mg/m3 (rat) (2-hour exposure)	
Benzyl acetate		830 mg/kg (mouse)	> 5000 mg/kg (rabbit)

Skin Corrosion/Irritation

No information was located.

Serious Eye Damage/Irritation

No information was located.

STOT (Specific Target Organ Toxicity) - Single Exposure

Inhalation

No information was located.

Skin Absorption

No information was located.

Ingestion

No information was located.

Aspiration Hazard

No information was located.

STOT (Specific Target Organ Toxicity) - Repeated Exposure

No information was located.

Respiratory and/or Skin Sensitization

No information was located.

Carcinogenicity

Chemical Name	IARC	ACGIH®	NTP	OSHA
2-Propanol		A4		

ACGIH®: A4 – Not classifiable as a human carcinogen.

Reproductive Toxicity

Development of Offspring

No information was located.

Sexual Function and Fertility

No information was located.

Effects on or via Lactation

No information was located.

Germ Cell Mutagenicity

No information was located.

Interactive Effects

No information was located.

Product Identifier: Big D Deodorant Concentrate, Cherry

SDS No.: 0408

Date of Preparation: March 27, 2015

SECTION 12. ECOLOGICAL INFORMATION

Environmental information was not located.

Toxicity

Acute Aquatic Toxicity

Chemical Name	LC50 Fish	EC50 Crustacea	ErC50 Aquatic Plants	ErC50 Algae
2-Propanol	9640 mg/L (Pimephales promelas (fathead minnow); 96-hour)	13299 mg/L (Daphnia magna (water flea); 48-hour)		> 1000 mg/L (96-hour)
Poly(oxy-1,2-ethanediyl), alpha-octyl- omega -hydroxy-		> 100 mg/L (Daphnia magna (water flea); 48-hour)		
Benzaldehyde	0.8-1.44 mg/L (Lepomis macrochirus (bluegill); 96-hour)			
Ethyl acetate	200.32-225.42 mg/L (48-hour)			
n-Amyl acetate	65 mg/L (96-hour)			

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal Methods

This product is a non-hazardous waste.

SECTION 14. TRANSPORT INFORMATION

Not regulated under Canadian TDG Regulations. Not regulated under US DOT Regulations.

Special Precautions for User Not applicable

Transport in Bulk According to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

SECTION 15. REGULATORY INFORMATION

Safety, Health and Environmental Regulations

Canada

WHMIS Classification



Class D2B

D2B - Toxic (Eye irritant)

This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations and the SDS contains all of the information required by the Controlled Products Regulations.

Domestic Substances List (DSL) / Non-Domestic Substances List (NDSL)

All ingredients are listed on the DSL or are not required to be listed.

Product Identifier: Big D Deodorant Concentrate, Cherry

SDS No.: 0408

Date of Preparation: March 27, 2015

CEPA - National Pollutant Release Inventory (NPRI)

Part 1A. (Polyethylene glycol octylphenyl ether, liquids)

Part 1A. (2-Propanol)

Part 5. (2-Propanol)

USA

Toxic Substances Control Act (TSCA) Section 8(b)

All ingredients are listed on the TSCA Inventory.

Additional USA Regulatory Lists

Massachusetts Right To Know. (2-Propanol). (Dipropylene glycol monomethyl ether). (Benzyl acetate). (Benzaldehyde). (Ethyl acetate). (n-Amyl acetate)

New Jersey Right To Know. (Dipropylene glycol monomethyl ether). (Poly(oxy-1,2-ethanediyl), alpha-octyl- omega -hydroxy-). (Benzaldehyde). (2-Propanol). (n-Amyl acetate). (Ethyl acetate). (Benzyl acetate)

Pennsylvania Right To Know. (2-Propanol). (Poly(oxy-1,2-ethanediyl), alpha-octyl- omega -hydroxy-). (Dipropylene glycol monomethyl ether). (Benzyl acetate). (Benzaldehyde). (Ethyl acetate). (n-Amyl acetate)

Rhode Island Right To Know. (2-Propanol). (Benzyl acetate). (n-Amyl acetate). (Ethyl acetate)

California Proposition 65: Ethylene Oxide (CAS 75-21-8) Formaldehyde (CAS 50-00-0) 1,4-Dioxane (CAS 123-91-1) Acetaldehyde (CAS 75-07-0)

California Proposition 65 - Developmental Toxin: 1,4-Dioxane (CAS 123-91-1).

SECTION 16. OTHER INFORMATION

NFPA Rating	Health - 1	Flammability - 0	Instability - 0
SDS Prepared By	Wayne Hegstrom		
Phone No.	405 682 2541		
Date of Preparation	March 27, 2015		
Revision Indicators	Not applicable.		

Product Identifier: Big D Deodorant Concentrate, Cherry

SDS No.: 0408

Page 07 of 07

Date of Preparation: March 27, 2015