



9" Reversible Twin Window Fan with Full Function Remote

Window Fan



Long Distance Full Function Remote Control



EASY READ SWITCH PANELS


- Soft Touch Push Buttons
- LED Indicators
- Easy Clean Surface



Product Features

- 3 Speed Push Button Control
- 3 Fan Functions: COOL - Brings Fresh Air In EXHAUST - Removes Stale Air From Room CIRCULATE - Operates Fans in Opposing Directions, Creating Air Circulation
- Accordion Expanders
- Turbo Fan Blades Designed for Maximum Air Movement
- Reversible – Intake/Exhaust/Circulation
- Universal – Fits Most Windows
- Portable – Carry Handle & Removable Legs
- Approved for Sale in the US and Canada

#CZ310R (123706) pack 1



Product Specifications

Wind Speed	9.8 F/S
Airflow Rate (High, Med, Low)	918/ 865/ 812 CFM
Box Dimensions	L- 25.25" x W- 4.75" x H- 13.75"
EA Weight	7.72 lbs.
EA Cube	.95'
Pallet Quantity	84
40' H/C Container Qty.	2261
UPC-A Barcode	075877132765



Tel: 800-523-1268 • 609-860-9990 • Fax: 609-860-9991
324A Half Acre Rd., Cranbury, NJ 08512
www.comfortzoneforyou.com