



Safety Data Sheet

Big D Non-Para Block, Mint Fresh

SECTION 1. IDENTIFICATION

Product Identifier	Big D Non-Para Block, Mint Fresh
Other Means of Identification	068800 & B0468805
Other Identification	Non-Para Block, Mint Fresh
Product Family	Restroom Deodorants
Recommended Use	Urinal Blocks.
Restrictions on Use	None known.
Manufacturer	Big D Industries, Inc., 5620 SW 29th St, Oklahoma City, OK, 73179, 405 682 2541, BigDInd.com
Supplier	Big D Industries, Inc., 5620 SW 29th St, Oklahoma City, OK, 73179, 405 682 2541, BigDInd.com
Emergency Phone No.	Big D Industries, 800 535 5053, 24hr (Infotrac)
SDS No.	0481

SECTION 2. HAZARDS IDENTIFICATION

GHS Classification

Acute toxicity (Oral) - Category 4; Skin corrosion/irritation - Category 2; Serious eye damage/eye irritation - Category 1; Skin sensitization - Category 1; Carcinogenicity - Category 2; Toxic to reproduction - Category 2

GHS Label Elements



Signal Word:
Danger

Hazard Statement(s):

H302	Harmful if swallowed.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.
H351	Suspected of causing cancer.
H361	Suspected of damaging fertility or the unborn child if swallowed.

Prevention:

P201	Obtain special instructions before use.
P202	Do not handle until all safety precautions have been read and understood.
P261	Avoid breathing dust, fume, gas, mist, vapours or spray.
P264	Wash hands and skin thoroughly after handling.
P270	Do not eat, drink or smoke when using this product.

Product Identifier:	Big D Non-Para Block, Mint Fresh
SDS No.:	0481
Date of Preparation:	April 21, 2015

P272 Contaminated work clothing must not be allowed out of the workplace.
P280 Wear protective gloves/protective clothing/eye protection/face protection.

Response:

P301 + P312 IF SWALLOWED: Call a POISON CENTRE/doctor if you feel unwell.
P302 + P352 IF ON SKIN: Wash with plenty of water.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308 + P313 IF exposed or concerned: Get medical advice/attention.
P310 Immediately call a POISON CENTRE/doctor.
P321 Specific treatment (see on this label).
P330 Rinse mouth.
P333 + P313 If skin irritation or rash occurs: Get medical advice/attention.
P362 + P364 Take off contaminated clothing and wash it before reuse.

Storage:

P405 Store locked up.

Disposal:

P501 Dispose of contents/container in accordance with local, regional, national and international regulations.

Other Hazards

None known.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Mixture:

Chemical Name	CAS No.	%	Other Identifiers
Alcohols, C16-18, ethoxylated, solids	68439-49-6	51.28	
Sodium sulfate	7757-82-6	31.11	
Fatty acids, tallow, sodium salts	8052-48-0	12.44	
Precipitated silica	112926-00-8	1.55	
Dipropylene glycol (mixed isomers)	25265-71-8	1.55	
p-Mentha-6,8-dien-2-one, (R)-(-)-	6485-40-1	0.66	
Other components below reportable Levels	No CAS	0.51	
Cinnamaldehyde, alpha-hexyl-	101-86-0	0.15	
Terpineol, acetate	8007-35-0	0.12	
Live Bacterial Cultures	No CAS	<0.10	

SECTION 4. FIRST-AID MEASURES

First-aid Measures

Skin Contact

Rinse with lukewarm, gently flowing water for 5 minutes.

Eye Contact

Immediately rinse the contaminated eye(s) with lukewarm, gently flowing water for 15-20 minutes, while holding the eyelid(s) open.

Ingestion

Call a Poison Centre or doctor if you feel unwell or are concerned.

Product Identifier: Big D Non-Para Block, Mint Fresh

SDS No.: 0481

Date of Preparation: April 21, 2015

Most Important Symptoms and Effects, Acute and Delayed

If on skin:

May cause mild irritation.

If in eyes:

May cause mild irritation.

If swallowed:

Symptoms may include nausea, vomiting, stomach cramps and diarrhea.

Immediate Medical Attention and Special Treatment

Special Instructions

Not applicable.

Medical Conditions Aggravated by Exposure

None known.

SECTION 5. FIRE-FIGHTING MEASURES

Extinguishing Media

Suitable Extinguishing Media

Not combustible. Use extinguishing agent suitable for surrounding fire.

Unsuitable Extinguishing Media

None known.

Specific Hazards Arising from the Chemical

Does not burn.

This product presents no unusual hazards in a fire situation.

Very toxic carbon monoxide, carbon dioxide.

Special Protective Equipment and Precautions for Fire-fighters

No special precautions are necessary.

See Skin Protection in Section 8 (Exposure Controls/Personal Protection) for advice on suitable chemical protective materials.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal Precautions, Protective Equipment, and Emergency Procedures

No special precautions are necessary.

Environmental Precautions

It is good practice to prevent releases into the environment.

Methods and Materials for Containment and Cleaning Up

No special clean-up methods are necessary.

SECTION 7. HANDLING AND STORAGE

Precautions for Safe Handling

No special handling precautions are necessary.

No special precautions are necessary.

Conditions for Safe Storage

Store in an area that is: temperature-controlled, dry.

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Product Identifier: Big D Non-Para Block, Mint Fresh

SDS No.: 0481

Date of Preparation: April 21, 2015

Page 03 of 07

Control Parameters

Chemical Name	ACGIH TLV®		OSHA PEL		AIHA WEEL	
	TWA	STEL	TWA	Ceiling	8-hr TWA	TWA
Precipitated silica	3 mg/m3		5 mg/m3			

ACGIH® = American Conference of Governmental Industrial Hygienists. TWA = Time-Weighted Average. OSHA = US Occupational Safety and Health Administration.

Appropriate Engineering Controls

The hazard potential of this product is relatively low. General ventilation is usually adequate.

Individual Protection Measures

Eye/Face Protection

Not required but it is good practice to wear safety glasses or chemical safety goggles.

Skin Protection

Not required, if used as directed.

Respiratory Protection

Not normally required if product is used as directed.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Basic Physical and Chemical Properties

Appearance	Blue. Particle Size: Not available
Odour	Fragrant (Fragrance)
Odour Threshold	Not available
pH	Not available
Melting Point/Freezing Point	Not available (melting); Not available (freezing)
Initial Boiling Point/Range	Not available
Flash Point	Not applicable
Evaporation Rate	Not applicable
Flammability (solid, gas)	Not available
Upper/Lower Flammability or Explosive Limit	Not applicable (upper); Not applicable (lower)
Vapour Pressure	Not available
Vapour Density (air = 1)	Not available
Relative Density (water = 1)	> 1 at 20 °C
Solubility	Not available in water; Not available (in other liquids)
Partition Coefficient, n-Octanol/Water (Log Kow)	Not available
Auto-ignition Temperature	Not available
Decomposition Temperature	Not available
Viscosity	Not applicable (kinematic)
Other Information	
Physical State	Solid
Molecular Formula	Not applicable
Molecular Weight	Not applicable
Bulk Density	Not available
Surface Tension	Not applicable
Critical Temperature	Not available
Electrical Conductivity	Not available

Product Identifier: Big D Non-Para Block, Mint Fresh

SDS No.: 0481

Date of Preparation: April 21, 2015

Vapour Pressure at 50 deg C Not available

Saturated Vapour Concentration Not available

SECTION 10. STABILITY AND REACTIVITY

Reactivity

None known.

Chemical Stability

Normally stable.

Possibility of Hazardous Reactions

None known.

Conditions to Avoid

None known.

Incompatible Materials

None known.

Hazardous Decomposition Products

None known.

SECTION 11. TOXICOLOGICAL INFORMATION

Likely Routes of Exposure

Skin contact; eye contact; ingestion.

Acute Toxicity

Chemical Name	LC50	LD50 (oral)	LD50 (dermal)
Sodium sulfate		5989 mg/kg (mouse)	
Precipitated silica		> 10000 mg/kg (rat)	> 5000 mg/kg (rabbit)

Skin Corrosion/Irritation

There is limited evidence of mild irritation.

Serious Eye Damage/Irritation

There is limited evidence of mild irritation.

STOT (Specific Target Organ Toxicity) - Single Exposure

Inhalation

No information was located.

Skin Absorption

No information was located.

Ingestion

No information was located.

Symptoms may include nausea, vomiting, stomach cramps and diarrhea.

Aspiration Hazard

No information was located.

STOT (Specific Target Organ Toxicity) - Repeated Exposure

No information was located.

Respiratory and/or Skin Sensitization

No information was located.

Carcinogenicity

Product Identifier: Big D Non-Para Block, Mint Fresh

SDS No.: 0481

Date of Preparation: April 21, 2015

Page 05 of 07

Not specifically listed.
No information was located.

Reproductive Toxicity

Development of Offspring

No information was located.

Sexual Function and Fertility

No information was located.

Effects on or via Lactation

No information was located.

Germ Cell Mutagenicity

No information was located.

Interactive Effects

No information was located.

SECTION 12. ECOLOGICAL INFORMATION

Environmental information was not located.

Persistence and Degradability

No information was located.

Bioaccumulative Potential

No information was located.

Mobility in Soil

No information was located.

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal Methods

Contact local environmental authorities for approved disposal or recycling methods in your jurisdiction.

SECTION 14. TRANSPORT INFORMATION

Not regulated under Canadian TDG Regulations. Not regulated under US DOT Regulations.

Special Precautions for User Not applicable

Transport in Bulk According to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

SECTION 15. REGULATORY INFORMATION

Safety, Health and Environmental Regulations

Canada

WHMIS Classification



Class D2B

D2B - Toxic

This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations and the SDS contains all of the information required by the Controlled Products Regulations.

Product Identifier: Big D Non-Para Block, Mint Fresh

SDS No.: 0481

Date of Preparation: April 21, 2015

Domestic Substances List (DSL) / Non-Domestic Substances List (NDSL)

All ingredients are listed on the DSL or are not required to be listed.

CEPA - National Pollutant Release Inventory (NPRI)

Part 1A. (Poly(oxy-1,2-ethanediyl)-, alpha-(4-nonylphenyl)-omega-hydroxy-, branched)

USA

Toxic Substances Control Act (TSCA) Section 8(b)

All ingredients are on the TSCA Inventory or are exempt from TSCA Inventory requirements under 40 CFR 720.

Additional USA Regulatory Lists

Massachusetts Right To Know: DiPhenyl Ether (CAS 101-84-8)

New Jersey Right To Know: DiPhenyl Ether (CAS 101-84-8) Benzyl Acetate (CAS 140-11-4)

Pennsylvania Right To Know: DiPhenyl Ether (CAS 101-84-8) Methyl Salicylate (CAS 119-36-8).

SECTION 16. OTHER INFORMATION

NFPA Rating	Health - 1	Flammability - 0	Instability - 0
SDS Prepared By	Wayne Hegstrom		
Phone No.	405 682 2541		
Date of Preparation	April 21, 2015		
Revision Indicators	Not applicable.		