

SAFETY DATA SHEET

Issuing Date No data available

Revision Date 02-Feb-2015

Revision Number 1



The supplier identified below generated this SDS using the UL SDS template. UL did not test, certify, or approve the substance described in this SDS, and all information in this SDS was provided by the supplier or was reproduced from publically available regulatory data sources. UL makes no representations or warranties regarding the completeness or accuracy of the information in this SDS and disclaims all liability in connection with the use of this information or the substance described in this SDS. The layout, appearance and format of this SDS is ©2014 UL LLC. All rights reserved.

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Name (PL 3625) Unitab Round Pink Spice

Other means of identification

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Toilet/Urinal Care Product - Non-aerosol

Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier Name W.W Grainger
Supplier Address 100 Grainger Parkway
Lake Forest
IL
60045-
5201
US
Supplier Phone Number Phone: 800-592-1900
Emergency telephone number Chemtrec: 800-424-9300

2. HAZARDS IDENTIFICATION


Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin irritation	Category 1
Eye irritation	Category 1

GHS Label elements, including precautionary statements



Signal word	Warning	Emergency Overview
Hazard Statements May cause skin irritation May cause eye irritation		
		
Appearance Pink	Physical State Solid	Odor Spice

Precautionary Statements - Prevention

Wash face, hands and any exposed skin thoroughly after handling
 Wear protective gloves/protective clothing/eye protection/face protection
 Avoid breathing dust/fume/gas/mist/vapors/spray
 Remove the contaminated clothing and wash.

Precautionary Statements - Response

Specific treatment (see supplemental first aid instructions on this label)

Eyes

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 If irritation persists consult a doctor/physician.

Skin

IF ON SKIN: No adverse reaction expected. Wash with soap and water
 Take off contaminated clothing and wash before reuse
 If skin irritation or rash occurs: Get medical advice/attention

Ingestion

IF SWALLOWED: Rinse mouth. DO NOT induce vomiting

Precautionary Statements - Storage

Store locked up
 Store in a well-ventilated place. Keep container tightly closed

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Not applicable

Unknown Toxicity

25.8391% of the mixture consists of ingredient(s) of unknown toxicity

Other information

Toxic to aquatic life

Repeated or prolonged skin contact may cause allergic reactions with susceptible persons

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%	Trade Secret
Ethylene oxide-Nonylphenol polymer	9016-45-9	40 - 70	*
Maize starch	9005-25-8	10 - 30	*
Phosphoric acid	7664-38-2	3 - 7	*
Subtilisins (proteolytic enzymes)	9014-01-1	1 - 5	*
Didecyldimethylammonium chloride	7173-51-5	1 - 5	*
Ethanol	64-17-5	0.1 - 1	*

*The exact percentage (concentration) of composition has been withheld as a trade secret

4. FIRST AID MEASURES**First aid measures****General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Keep eye wide open while rinsing. Remove contact lenses, if present and if irritation persists consult a doctor/physician.

Skin Contact

Wash off immediately with soap and plenty of water for at least 15 minutes. May cause an allergic skin reaction. In the case of skin irritation or allergic reactions see a physician.

Inhalation

Remove to fresh air. Get medical attention immediately if symptoms occur.

Ingestion

Rinse mouth immediately and drink plenty of water. Never give anything by mouth to an unconscious person. Do NOT induce vomiting. Call a physician.

Self-protection of the first aider Avoid contact with skin, eyes or clothing. Use personal protective equipment as required. Wear personal protective clothing (see section 8).

Most important symptoms and effects, both acute and delayed

Most Important Symptoms and Effects Burning sensation. Itching. Rashes. Hives.

Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically. May cause sensitization of susceptible persons.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

CAUTION: Use of water spray when fighting fire may be inefficient.

Specific Hazards Arising from the Chemical

The product causes burns of eyes, skin and mucous membranes. Thermal decomposition can lead to release of irritating gases and vapors. Product is or contains a sensitizer. May cause sensitization by inhalation and skin contact. In the event of fire and/or explosion do not breathe fumes.

Uniform Fire Code

Sensitizer: Solid
Irritant: Solid

Hazardous Combustion Products

Carbon oxides.

Explosion Data

Sensitivity to Mechanical Impact No.

Sensitivity to Static Discharge No.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Wear self contained breathing apparatus for fire fighting if necessary.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal Precautions Avoid contact with skin, eyes or clothing. Ensure adequate ventilation. Use personal protective equipment as required.

Other Information Refer to protective measures listed in Sections 7 and 8.

Environmental Precautions

Environmental Precautions Refer to protective measures listed in Sections 7 and 8. Prevent further leakage or spillage if safe to do so.

Methods and material for containment and cleaning up

Methods for Containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers. Use personal protective equipment as required. Cover powder spill with plastic sheet or tarp to minimize spreading and keep powder dry. Avoid generation of dust. Clean contaminated surface thoroughly. Soak up with inert absorbent material. Dam up. Sweep up and shovel into suitable containers for disposal. After cleaning, flush away traces with water.

7. HANDLING AND STORAGE

Precautions for safe handling

Handling Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Do not eat, drink or smoke when using this product.

Conditions for safe storage, including any incompatibilities

Storage Keep containers tightly closed in a dry, cool and well-ventilated place. Store locked up. Keep out of the reach of children.

Incompatible Products None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH



Maize starch 9005-25-8	TWA: 10 mg/m ³	TWA: 15 mg/m ³ total dust TWA: 5 mg/m ³ respirable fraction (vacated) TWA: 15 mg/m ³ total dust (vacated) TWA: 5 mg/m ³ respirable fraction	TWA: 10 mg/m ³ total dust TWA: 5 mg/m ³ respirable dust
Phosphoric acid 7664-38-2	STEL: 3 mg/m ³ TWA: 1 mg/m ³	TWA: 1 mg/m ³ (vacated) TWA: 1 mg/m ³ (vacated) STEL: 3 mg/m ³	IDLH: 1000 mg/m ³ TWA: 1 mg/m ³ STEL: 3 mg/m ³
Subtilisins (proteolytic enzymes) 9014-01-1	Ceiling: 0.00006 mg/m ³ as crystalline active enzyme	(vacated) STEL: 0.00006 mg/m ³ 60 min	STEL: 0.00006 mg/m ³ 60 min Subtilisins
Ethanol 64-17-5	STEL: 1000 ppm	TWA: 1000 ppm TWA: 1900 mg/m ³ (vacated) TWA: 1000 ppm (vacated) TWA: 1900 mg/m ³	IDLH: 3300 ppm 10% LEL TWA: 1000 ppm TWA: 1900 mg/m ³

ACGIH TLV: American Conference of Governmental Industrial Hygienists - Threshold Limit Value OSHA PEL: Occupational Safety and Health Administration - Permissible Exposure Limits Immediately Dangerous to Life or Health NIOSH IDLH

Other Exposure Guidelines Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992) See section 15 for national exposure control parameters

Appropriate engineering controls

Engineering Measures Showers
Eyewash stations
Ventilation systems

Individual protection measures, such as personal protective equipment

Eye/Face Protection Tight sealing safety goggles. Wear safety glasses with side shields (or goggles).

Skin and Body Protection No special protective equipment required. Protective gloves.

Respiratory Protection No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice. Take off contaminated clothing and wash before reuse. Avoid contact with skin, eyes or clothing. Wear suitable gloves and eye/face protection. Do not eat, drink or smoke when using this product.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical and Chemical Properties

Physical State	Solid	Odor	Spice
Appearance	Pink	Odor Threshold	No information available
Color	No information available		

<u>Property</u>	<u>Values</u>	<u>Remarks</u>	<u>Method</u>
pH	No data available	None known	
Melting / freezing point	No data available	None known	
Boiling point / boiling range	No data available	None known	
Flash Point	No data available	None known	
Evaporation Rate	No data available	None known	
Flammability (solid, gas)	No data available	None known	
Flammability Limit in Air			
Upper flammability limit	No data available		
Lower flammability limit	No data available		
Vapor pressure	No data available	None known	



Vapor density	No data available	None known
Specific Gravity	No data available	None known
Water Solubility	Soluble in water	None known
Solubility in other solvents	No data available	None known
Partition coefficient: n-octanol/water	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature	No data available	None known
Kinematic viscosity	No data available	None known
Dynamic viscosity	No data available	None known
Explosive properties	No data available	None known
Oxidizing Properties	No data available	

Other Information

Softening Point	No data available
VOC Content (%)	No data available
Particle Size	No data available
Particle Size Distribution	

10. STABILITY AND REACTIVITY

Reactivity

No data available.

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to avoid

None known.

Incompatible materials

None known.

Hazardous Decomposition Products

Carbon oxides.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information Product does not present an acute toxicity hazard based on known or supplied information.

Inhalation

Specific test data for the substance or mixture is not available. No irritation expected.

Eye Contact	Specific test data for the substance or mixture is not available. Not expected to be an irritant based on components. May Cause Eye Irritation. May cause burns.
Skin Contact	Specific test data for the substance or mixture is not available. Not expected to be a skin irritant based on components. Prolonged contact may cause redness and irritation.
Ingestion	Specific test data for the substance or mixture is not available. Ingestion may cause irritation to mucous membranes. Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea

Component Information

Information on toxicological effects

Symptoms	Erythema (skin redness). Burning. May cause blindness. Coughing and/ or wheezing. Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain, or flushing.
-----------------	---

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization	No information available.
Mutagenic Effects	No information available.
Carcinogenicity	The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
Ethanol 64-17-5	A3	Group 1	Known	X

ACGIH (American Conference of Governmental Industrial Hygienists)

A3 - Animal Carcinogen

IARC (International Agency for Research on Cancer)

Group 1 - Carcinogenic to Humans

NTP (National Toxicology Program)

Known - Known Carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive Toxicity	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.

Chronic Toxicity	No known effect based on information supplied. Repeated contact may cause allergic reactions in very susceptible persons. Avoid repeated exposure. Ethanol has been shown to be a reproductive toxin only when consumed as an alcoholic beverage. Ethanol has been shown to be carcinogenic in long-term studies only when consumed as alcoholic beverage.
Target Organ Effects	Eyes.Skin.
Aspiration Hazard	No information available.

Numerical measures of toxicity Product Information

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral)

5,072.00 mg/kg

12. ECOLOGICAL INFORMATION**Ecotoxicity**

Toxic to aquatic organisms.

Chemical Name	Toxicity to Algae	Toxicity to Fish	Toxicity to Microorganisms	Daphnia Magna (Water Flea)
Phosphoric acid 7664-38-2		96h LC50: 3 - 3.5 mg/L (Gambusia affinis)		12h EC50: = 4.6 mg/L
Ethanol 64-17-5		96h LC50: > 100 mg/L (Pimephales promelas) 96h LC50: 13400 - 15100 mg/L (Pimephales promelas) 96h LC50: 12.0 - 16.0 mL/L (Oncorhynchus mykiss)	EC50 = 34634 mg/L 30 min EC50 = 35470 mg/L 5 min	48h LC50: 9268 - 14221 mg/L 48h EC50: = 2 mg/L 24h EC50: = 10800 mg/L

Persistence and Degradability

No information available.

Bioaccumulation

Chemical Name	Log Pow
Ethanol 64-17-5	-0.32

Other adverse effects

No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal methods

This material, as supplied, is not a hazardous waste according to Federal regulations (40 CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local regulations for additional requirements.

Contaminated Packaging

Dispose of contents/containers in accordance with local regulations.

California Hazardous Waste Codes 331

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical Name	California Hazardous Waste
Phosphoric acid 7664-38-2	Corrosive
Ethanol 64-17-5	Toxic Ignitable

14. TRANSPORT INFORMATION

DOT
Proper Shipping Name NOT REGULATED
Hazard Class NON REGULATED
 N/A

TDG Not regulated

MEX Not regulated

ICAO Not regulated

IATA
Proper Shipping Name Not regulated
Hazard Class NON REGULATED
 N/A

IMDG/IMO
Hazard Class Not regulated
 N/A

RID Not regulated

ADR Not regulated

ADN Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies
DSL All components are listed either on the DSL or NDSL.

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory



DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute Health Hazard	Yes
Chronic Health Hazard	Yes
Fire Hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

Chemical Name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Phosphoric acid 7664-38-2	5000 lb			X

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical Name	Hazardous Substances RQs	Extremely Hazardous Substances RQs	RQ
Phosphoric acid 7664-38-2	5000 lb		RQ 5000 lb final RQ RQ 2270 kg final RQ

US State Regulations**California Proposition 65**

This product contains the following Proposition 65 chemicals. Ethyl alcohol is only considered a Proposition 65 developmental hazard when it is ingested as an alcoholic beverage.

Chemical Name	California Proposition 65
Ethanol - 64-17-5	Carcinogen Developmental

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania	Rhode Island	Illinois
Maize starch 9005-25-8		X	X		
Phosphoric acid 7664-38-2	X	X	X	X	
Ethanol 64-17-5		X			

International Regulations**Mexico****National occupational exposure limits**

Component	Carcinogen Status	Exposure Limits
Phosphoric acid 7664-38-2 (3 - 7)		Mexico: TWA 1 mg/m ³ Mexico: STEL 3 mg/m ³
Ethanol 64-17-5 (0.1 - 1)		Mexico: TWA 1000 ppm Mexico: TWA 1900 mg/m ³



Mexico - Occupational Exposure Limits - Carcinogens

Canada

WHMIS Hazard Class

D2A - Very toxic materials

16. OTHER INFORMATION

NFPA	Health Hazards 1	Flammability 0	Instability 0	Physical and Chemical Hazards - Personal Protection X
HMIS	Health Hazards 1	Flammability 0	Physical Hazard 0	

Revision Date 02-Feb-2015
Revision Note No information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet