

# SAFETY DATA SHEET

Issuing Date No data available

Revision Date 02-Feb-2015

Revision Number 1



The supplier identified below generated this SDS using the UL SDS template. UL did not test, certify, or approve the substance described in this SDS, and all information in this SDS was provided by the supplier or was reproduced from publically available regulatory data sources. UL makes no representations or warranties regarding the completeness or accuracy of the information in this SDS and disclaims all liability in connection with the use of this information or the substance described in this SDS. The layout, appearance and format of this SDS is © 2014 UL LLC. All rights reserved.

## 1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

### Product identifier

**Product Name** Stainless Steel Water based (9330)

### Other means of identification

**Synonyms** None

### Recommended use of the chemical and restrictions on use

**Recommended Use** Metal polish

**Uses advised against** No information available

### Details of the supplier of the safety data sheet

**Supplier Name** VENUS LABORATORIES dba Earth Friendly Products  
**Supplier Address** 111 S ROHLWING ROAD

ADDISON

IL

60101

US

**Supplier Phone Number** Phone:1-800-424-9300

Fax:630-595-1900

Contact Phone8005921900

**Supplier Email** bwolford@ecos.com

**Emergency telephone number**

## 2. HAZARDS IDENTIFICATION

### Classification


This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Serious eye damage/eye irritation	Category 1
Skin sensitization	Category 1

### GHS Label elements, including precautionary statements

### Emergency Overview



<b>Signal word</b>	<b>Danger</b>	
<b>Hazard Statements</b> Causes serious eye damage May cause an allergic skin reaction		
		
<b>Appearance</b> White	<b>Physical State</b> Emulsion Liquid	<b>Odor</b> No information available

**Precautionary Statements - Prevention**

Wear protective gloves/protective clothing/eye protection/face protection  
 Avoid breathing dust/fume/gas/mist/vapors/spray  
 Contaminated work clothing should not be allowed out of the workplace

**Precautionary Statements - Response**

Specific treatment (see supplemental first aid instructions on this label)

**Eyes**

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
 Immediately call a POISON CENTER or doctor/physician

**Skin**

IF ON SKIN: Wash with plenty of soap and water  
 If skin irritation or rash occurs: Get medical advice/attention  
 Wash contaminated clothing before reuse

**Precautionary Statements - Storage**

None

**Precautionary Statements - Disposal**

Dispose of contents/container to an approved waste disposal plant

**Hazards not otherwise classified (HNOC)**

Not applicable

**Unknown Toxicity**

25.93% of the mixture consists of ingredient(s) of unknown toxicity

**Other information**

Very toxic to aquatic life

**Interactions with Other Chemicals**

No information available.

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%	Trade Secret
Alcohols, C12-14, ethoxylated	68439-50-9	10 - 30	*
Methylisothiazolinone	2682-20-4	< 0.1	*

\*The exact percentage (concentration) of composition has been withheld as a trade secret

### 4. FIRST AID MEASURES

#### First aid measures

#### General Advice

Immediate medical attention is required. Show this safety data sheet to the doctor in attendance.

#### Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Keep eye wide open while rinsing. Do not rub affected area. Seek immediate medical attention/advice.

#### Skin Contact

Wash off immediately with soap and plenty of water for at least 15 minutes. Get medical attention if irritation develops and persists.

#### Inhalation

Remove to fresh air. Get medical attention immediately if symptoms occur.

#### Ingestion

Rinse mouth immediately and drink plenty of water. Never give anything by mouth to an unconscious person. Do NOT induce vomiting. Call a physician.

#### Self-protection of the first aider

Avoid contact with skin, eyes or clothing. Use personal protective equipment as required. Wear personal protective clothing (see section 8).

#### Most important symptoms and effects, both acute and delayed

**Most Important Symptoms and Effects** Burning sensation.

#### Indication of any immediate medical attention and special treatment needed

#### Notes to Physician

Treat symptomatically.

## 5. FIRE-FIGHTING MEASURES

### **Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

### **Unsuitable extinguishing media**

CAUTION: Use of water spray when fighting fire may be inefficient.

### **Specific Hazards Arising from the Chemical**

No information available.

#### **Uniform Fire Code**

Sensitizer: Liquid

### **Hazardous Combustion Products**

Carbon oxides.

### **Explosion Data**

**Sensitivity to Mechanical Impact** No.

**Sensitivity to Static Discharge** No.

### **Protective equipment and precautions for firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## 6. ACCIDENTAL RELEASE MEASURES

### **Personal precautions, protective equipment and emergency procedures**

#### **Personal Precautions**

Avoid contact with skin, eyes or clothing. Use personal protective equipment as required.

#### **Other Information**

Refer to protective measures listed in Sections 7 and 8.

### **Environmental Precautions**

#### **Environmental Precautions**

Refer to protective measures listed in Sections 7 and 8. Prevent further leakage or spillage if safe to do so.

### **Methods and material for containment and cleaning up**

#### **Methods for Containment**

Prevent further leakage or spillage if safe to do so.

#### **Methods for cleaning up**

Soak up with inert absorbent material. Pick up and transfer to properly labeled containers.

## 7. HANDLING AND STORAGE

### Precautions for safe handling

**Handling** Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Do not eat, drink or smoke when using this product.

### Conditions for safe storage, including any incompatibilities

**Storage** Keep containers tightly closed in a dry, cool and well-ventilated place. Store locked up. Keep out of the reach of children.

**Incompatible Products** Strong oxidizing agents. Strong acids. Strong bases.

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control parameters

**Exposure Guidelines** This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies

### Appropriate engineering controls

**Engineering Measures** Showers  
Eyewash stations  
Ventilation systems

### Individual protection measures, such as personal protective equipment

**Eye/Face Protection** Tight sealing safety goggles.

**Skin and Body Protection** Wear protective gloves and protective clothing.

**Respiratory Protection** No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Wear suitable gloves and eye/face protection. Do not eat, drink or smoke when using this product. Take off contaminated clothing and wash before reuse.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

### Physical and Chemical Properties

<b>Physical State</b>	Emulsion, Liquid	<b>Odor</b>	No information available
<b>Appearance</b>	White	<b>Odor Threshold</b>	No information available
<b>Color</b>	No information available		

<u>Property</u>	<u>Values</u>	<u>Remarks</u>	<u>Method</u>
<b>pH</b>	5.2	None known	
<b>Melting / freezing point</b>	No data available	None known	
<b>Boiling point / boiling range</b>	No data available	None known	
<b>Flash Point</b>	No data available	None known	
<b>Evaporation Rate</b>	No data available	None known	

<b>Flammability (solid, gas)</b>	No data available	None known
<b>Flammability Limit in Air</b>		
<b>Upper flammability limit</b>	No data available	
<b>Lower flammability limit</b>	No data available	
<b>Vapor pressure</b>	No data available	None known
<b>Vapor density</b>	No data available	None known
<b>Specific Gravity</b>	No data available	None known
<b>Water Solubility</b>	Soluble in water	None known
<b>Solubility in other solvents</b>	No data available	None known
<b>Partition coefficient: n-octanol/water</b>	No data available	None known
<b>Autoignition temperature</b>	No data available	None known
<b>Decomposition temperature</b>	No data available	None known
<b>Kinematic viscosity</b>	No data available	None known
<b>Dynamic viscosity</b>	No data available	None known
<b>Explosive properties</b>	No data available	
<b>Oxidizing Properties</b>	No data available	

**Other Information**

<b>Softening Point</b>	No data available
<b>VOC Content (%)</b>	No data available
<b>Particle Size</b>	No data available
<b>Particle Size Distribution</b>	

## 10. STABILITY AND REACTIVITY

**Reactivity**

No data available.

**Chemical stability**

Stable under recommended storage conditions.

**Possibility of Hazardous Reactions**

None under normal processing.

**Hazardous Polymerization**

Hazardous polymerization does not occur.

**Conditions to avoid**

None known based on information supplied.

**Incompatible materials**

Strong oxidizing agents. Strong acids. Strong bases.

**Hazardous Decomposition Products**

Carbon oxides.

## 11. TOXICOLOGICAL INFORMATION

**Information on likely routes of exposure****Product Information****Inhalation**

Specific test data for the substance or mixture is not available. May cause irritation of respiratory tract.

<b>Eye Contact</b>	Specific test data for the substance or mixture is not available. Severely irritating to eyes. Causes serious eye damage. May cause burns. May cause irreversible damage to eyes.
<b>Skin Contact</b>	Specific test data for the substance or mixture is not available. May cause irritation. Prolonged contact may cause redness and irritation.
<b>Ingestion</b>	Specific test data for the substance or mixture is not available. Ingestion may cause irritation to mucous membranes. Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea.

**Component Information****Information on toxicological effects**

**Symptoms** Erythema (skin redness). May cause blindness. Burning.

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

**Sensitization** May cause sensitization of susceptible persons. May cause sensitization by skin contact.

**Mutagenic Effects** No information available.

**Carcinogenicity** Contains no ingredient listed as a carcinogen.

**Reproductive Toxicity** No information available.

**STOT - single exposure** No information available.

**STOT - repeated exposure** No information available.

**Chronic Toxicity** No known effect based on information supplied.

**Target Organ Effects** Eyes.

**Aspiration Hazard** No information available.

**Numerical measures of toxicity Product Information**

The following values are calculated based on chapter 3.1 of the GHS document

Not applicable

## 12. ECOLOGICAL INFORMATION

**Ecotoxicity**

Very toxic to aquatic life.

**Persistence and Degradability**

No information available.

**Bioaccumulation**

No information available

**Other adverse effects**

No information available.

### 13. DISPOSAL CONSIDERATIONS

#### Waste treatment methods

**Disposal methods** This material, as supplied, is not a hazardous waste according to Federal regulations (40 CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local regulations for additional requirements.

**Contaminated Packaging** Dispose of contents/containers in accordance with local regulations.

**California Hazardous Waste Codes** 561

### 14. TRANSPORT INFORMATION

**DOT**  
**Proper Shipping Name** NOT REGULATED  
**Hazard Class** NON REGULATED  
 N/A

**TDG** Not regulated

**MEX** Not regulated

**ICAO** Not regulated

**IATA**  
**Proper Shipping Name** Not regulated  
**Hazard Class** NON REGULATED  
 N/A

**IMDG/IMO**  
**Hazard Class** Not regulated  
 N/A

**RID** Not regulated

**ADR** Not regulated

**ADN** Not regulated

### 15. REGULATORY INFORMATION

#### International Inventories

**TSCA** Complies  
**DSL** All components are listed either on the DSL or NDSL.

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory  
**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

#### US Federal Regulations





**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

**SARA 311/312 Hazard Categories**

<b>Acute Health Hazard</b>	Yes
<b>Chronic Health Hazard</b>	No
<b>Fire Hazard</b>	No
<b>Sudden release of pressure hazard</b>	No
<b>Reactive Hazard</b>	No

**CWA (Clean Water Act)**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

**CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

**US State Regulations**

**California Proposition 65**

This product does not contain any Proposition 65 chemicals.

**U.S. State Right-to-Know Regulations**

Chemical Name	New Jersey	Massachusetts	Pennsylvania	Rhode Island	Illinois
2-phenoxyethanol 122-99-6			X	X	X

**International Regulations**

**Canada**

**WHMIS Hazard Class**

D2B - Toxic materials



**16. OTHER INFORMATION**

<b>NFPA</b>	<b>Health Hazards</b> 1	<b>Flammability</b> 0	<b>Instability</b> 0	<b>Physical and Chemical Hazards - Personal Protection</b> X
<b>HMIS</b>	<b>Health Hazards</b> 3	<b>Flammability</b> 0	<b>Physical Hazard</b> 0	

**Prepared By** Product Stewardship  
23 British American Blvd.  
Latham, NY 12110  
1-800-572-6501

**Revision Date** 02-Feb-2015

**Revision Note** No information available



**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**