


Gantry Cranes

Model HA90 - Aluminum Gantry Fixed Height & Adjustable Span



The all aluminum gantry is perfect for applications where the crane weight is critical.

PRODUCT FEATURES:

- Lightweight aluminum.
- Balanced design allows for easy rolling, even under load.
- Conforms to AISC, OSHA and CMAA specifications.
- Bolt together construction.
- Easy set up and maintenance.
- 4 poly-coated swivel casters.
- For our optional gantry crane features, please see page H.15.


SPECIFICATIONS

			1 Ton Capacity*			2 Ton Capacity*		
			Nominal Span (ft.)			Nominal Span (ft.)		
			6	9	11	6	8	10
Height Under Beam	7'-6"	Model Number	HA90-1-7/6	HA90-1-7/9	HA90-1-7/11	HA90-2-7/6	HA90-2-7/8	HA90-2-7/10
		Inside Span (A)	6'-10"	9'	11'	6'-4"	8'-6"	10'-6"
		Overall Length (B)	8'-4"	10'-6"	12'-6"	8'-4"	10'-6"	12'-6"
		Weight (lbs.)	212	238	251	351	408	429
		Support Width (C)	4'			4'		
	9'-2"	Model Number	HA90-1-9/6	HA90-1-9/9	HA90-1-9/11	HA90-2-9/6	HA90-2-9/8	HA90-2-9/10
		Inside Span (A)	6'-10"	9'	11'	6'-4"	8'-6"	10'-6"
		Overall Length (B)	8'-4"	10'-6"	12'-6"	8'-4"	10'-6"	12'-6"
		Weight (lbs.)	234	260	273	371	428	449
	Support Width (C)	5'			5'			
10'-10"	Model Number	HA90-1-10/6	HA90-1-10/9	HA90-1-10/11	HA90-2-10/6	HA90-2-10/8	HA90-2-10/10	
	Inside Span (A)	6'-10"	9'	11'	6'-4"	8'-6"	10'-6"	
	Overall Length (B)	8'-4"	10'-6"	12'-6"	8'-4"	10'-6"	12'-6"	
	Weight (lbs.)	258	284	297	401	458	479	
	Support Width (C)	6'			6'			
	Beam Height (in.)	6	8		8	10		
	Flange Width (in.)	3.33	4		4	4.66		
	Caster Diameter (in.)	6			8			

* Total weight of hoist and trolley not to exceed 20% of rated capacity.

Gantry Cranes

Model KA90 - Aluminum Gantry Adjustable Height & Span



The all aluminum gantry is perfect for applications where the crane weight is critical.

PRODUCT FEATURES:

- Lightweight aluminum.
- Balanced design allows for easy rolling, even under load.
- Conforms to AISC, OSHA and CMAA specifications.
- Bolt together construction.
- Easy set up and maintenance.
- 4 poly-coated swivel casters.
- Height and span adjustability.
- Height adjustable down from maximum in 6" increments.
- For our optional gantry crane features, please see page H.15.

GANTRY
CRANES

SPECIFICATIONS

		1 Ton Capacity*			2 Ton Capacity*				
		Nominal Span (ft.)			Nominal Span (ft.)				
		6	8	10	6	8	10		
Height Under Beam	7'-6"	Model Number	KA90-1-7/6	KA90-1-7/8	KA90-1-7/10	KA90-2-7/6	KA90-2-7/8	KA90-2-7/10	
		Inside Span (A)	6'-7"	8'-9"	10'-9"	6'	8'-2"	10'-6"	
		Overall Length (B)	8'-4"	10'-6"	12'-6"	8'-4"	10'-6"	12'-6"	
	Total Weight (lbs.)	350	375	390	460	500	525		
	Minimum Height	5'-6"			5'-6"				
	Support Width (C)	4'			4'				
	9'-2"	Model Number	KA90-1-9/6	KA90-1-9/8	KA90-1-9/10	KA90-2-9/6	KA90-2-9/8	KA90-2-9/10	
		Inside Span (A)	6'-7"	8'-9"	10'-9"	6'	8'-2"	10'-6"	
		Overall Length (B)	8'-4"	10'-6"	12'-6"	8'-4"	10'-6"	12'-6"	
	Weight (lbs.)	360	385	400	485	525	550		
	Minimum Height	6'-2"			6'-2"				
	Support Width (C)	5'			5'				
	10'-10"	Model Number	KA90-1-10/6	KA90-1-10/8	KA90-1-10/10	KA90-2-10/6	KA90-2-10/8	KA90-2-10/10	
		Inside Span (A)	6'-7"	8'-9"	10'-9"	6'	8'-2"	10'-6"	
		Overall Length (B)	8'-4"	10'-6"	12'-6"	8'-4"	10'-6"	12'-6"	
	Weight (lbs.)	385	410	425	520	560	585		
Minimum Height	7'-10"			7'-10"					
Support Width (C)	6'			6'					
12'-6"	Model Number	KA90-1-12/6	KA90-1-12/8	KA90-1-12/10	KA90-2-12/6	KA90-2-12/8	KA90-2-12/10		
	Inside Span (A)	6'-7"	8'-9"	10'-9"	6'	8'-2"	10'-6"		
	Overall Length (B)	8'-4"	10'-6"	12'-6"	8'-4"	10'-6"	12'-6"		
Weight (lbs.)	415	440	455	530	570	595			
Minimum Height	9'-6"			9'-6"					
Support Width (C)	6'-6"			6'-6"					
Beam Height (in.)		6		8		8		10	
Flange Width (in.)		3.44		4		4		4.66	
Caster Diameter (in.)		6		6		8		8	

* Total weight of hoist and trolley not to exceed 20% of rated capacity.