



Safety Data Sheet

Issue date 11-Mar-2014

Version 1

1. Identification of the Substance/Preparation and of the Company/Undertaking

Product Identifier

Product name CHAMPION SPRAYON MANGO AIR FRESHENER
Chemical name 7-7983-1

Other means of identification

Product code FG 438-5323-2
Synonyms Air deodorizer

Recommended use of the chemical and restrictions on use

Recommended Use Room Deodorizer.
Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier Address	Manufacturer Address
Chase Products Co. 2727 Gardner Road Broadview, IL 60155 708-273-1121	Chase Products Co. 2727 Gardner Road Broadview, IL 60155 708-273-1121

Emergency Telephone Number

Company Phone Number 708-865-1000
24 Hour Emergency Phone Number 1-800-255-3924

2. Hazards Identification

Classification

FLAMMABLE AEROSOLS	Not classified
--------------------	----------------

Label Elements

EMERGENCY OVERVIEW

The product contains no substances which at their given concentration, are considered to be hazardous to health

appearance liquid

Physical State Aerosol

Odor Perfumed.

Hazards not otherwise classified (HNOC)

OTHER INFORMATION

No information available

3. Composition/information on Ingredients

Common Name Air Freshener.
Synonyms Air deodorizer.

FG 438-5323-2 CHAMPION SPRAYON MANGO AIR FRESHENER

Chemical Family MIXTURES.
Formula 7-7983-1
Chemical nature Aqueous perfumed solution.

Chemical name	CAS No	weight-%	Trade secret
N-Butane	106-97-8	10-15	*
Propane	74-98-6	1-5	*

Chemical Additions Hazardous components according to OSHA, are listed when present at 1% or greater. Carcinoges are listed when present at 0.1% or greater.

* The exact percentage (concentration) of composition has been withheld as a trade secret.

4. First aid measures

FIRST AID MEASURES

Eye Contact Flush from eyes with plenty of water. If irritation develops, consult a physician.

Skin contact Wash skin with soap and water.

inhalation If overcome by vapor, move person to fresh air. Restore respiration if necessary. Get medical attention if injury develops.

INGESTION Ingestion from an aerosol product is unlikely to occur.

Most important symptoms and effects, both acute and delayed

Symptoms Acute, Deliberate inhalation of concentrated vapor or mist may cause headaches. Prolonged and repeated contact with the eyes may cause mild irritation.

Indication of any immediate medical attention and special treatment needed

Note to physicians None needed.

5. Fire-fighting measures

Suitable extinguishing media

Dry chemical, CO2 or water spray.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

This product is under pressure. Water spray may be used to cool cans in the vicinity of fire or excessive heat to prevent the explosion of the cans.

Hazardous combustion products Thermal decomposition may release carbon monoxide and carbon dioxide.

Explosion data

Sensitivity to Mechanical Impact Contents under pressure, keep away from heat and open flame.

Sensitivity to Static Discharge Keep away from heat, sparks, flame, and other sources of ignition (i.e., pilot lights, electric motors and static electricity).

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions Use with adequate general or local exhaust ventilation.

For emergency responders Remove all sources of ignition.

Environmental Precautions

Environmental Precautions See Section 12 for additional Ecological Information.

Methods and material for containment and cleaning up

Methods for Containment Provide adequate ventilation to area being treated. Soak up spills with chemically inert, absorbent material.

Methods for cleaning up Clean contaminated surface thoroughly.

7. Handling and Storage

Precautions for safe handling

Advice on safe handling Do not deliberately inhale vapor or spray mist. Avoid getting spray into eyes.

Conditions for safe storage, including any incompatibilities

Storage Conditions Store in a cool, dry place away from heat and open flame. Keep out of reach of children. AEROSOL STORAGE LEVEL I (NFPA-30B) .

Incompatible Materials Avoid heat, open flame and contact with strong oxidizers.

8. Exposure Controls/Personal Protection

Control parameters

Exposure guidelines See occupational exposure limits listed below.

Chemical name	ACGIH TLV	OSHA PEL	NIOSH IDLH
N-Butane 106-97-8	STEL: 1000 ppm	(vacated) TWA: 800 ppm (vacated) TWA: 1900 mg/m ³	TWA: 800 ppm TWA: 1900 mg/m ³
Propane 74-98-6	TWA: 1000 ppm	TWA: 1000 ppm TWA: 1800 mg/m ³ (vacated) TWA: 1000 ppm (vacated) TWA: 1800 mg/m ³	IDLH: 2100 ppm TWA: 1000 ppm TWA: 1800 mg/m ³

Appropriate engineering controls

Engineering controls Use with adequate general or local exhaust ventilation.

Individual protection measures, such as personal protective equipment

Eye/face Protection Conventional eyeglasses to guard against splashing.

Skin and Body Protection Household type gloves, if desired.

Respiratory protection None required if used in a well-ventilated area .

General hygiene considerations None needed.

9. Physical and Chemical Properties

Information on basic physical and chemical properties

Physical State	Aerosol	Odor	Perfumed.
appearance	liquid		
color	white		

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	0.99 to 1.00	
Melting point/freezing point	Not applicable	
Boiling point/boiling range	Water 212 °F/100 °C	
Flash Point	Not Available. This is an aerosol product for which Flame Projection is 0 inches. Temperatures above 120 F may cause cans to burst.	
Evaporation Rate	Faster than butyl acetate	
flammability (solid, gas)		
Flammability Limits in Air		
Upper flammability limits	Not available	
Lower Flammability Limit	Not available	
vapor pressure		
Specific gravity	0.99 -1.00 (concentrate)	
Water solubility		Soluble in water

OTHER INFORMATION

VOC content (%)	19.5%
density	8.33 lb/gal
Bulk Density	

10. Stability and Reactivity

<u>Reactivity</u>	Not applicable
Not applicable	Not applicable

Chemical stability
Stable.

Possibility of hazardous reactions
Temperatures above 120 F may cause cans to burst with force.

hazardous polymerization Hazardous polymerization does not occur.

Conditions to Avoid
Temperatures above 120 F.

Incompatible Materials
Avoid heat, open flame and contact with strong oxidizers.

Hazardous decomposition products
Thermal decomposition may yield gases like carbon monoxide and carbon dioxide.

11. Toxicological Information

Information on likely routes of exposure

Product Information	This product has not been tested as whole. See below for information on ingredients.		
inhalation	no data available.		
Eye Contact	no data available.		
Skin contact	no data available.		
INGESTION	no data available.		

Chemical name	Oral LD50	dermal LD50	Inhalation LC50

FG 438-5323-2 CHAMPION SPRAYON MANGO AIR FRESHENER

N-Butane 106-97-8	-	-	= 658 g/m ³ (Rat) 4 h
Propane 74-98-6	-	-	= 658 mg/L (Rat) 4 h

Information on toxicological effects

Symptoms Deliberate inhalation of concentrated vapor or mist may cause headache, dizziness and nausea.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation None expected.
Serious eye damage/eye irritation May cause eye irritation with susceptible persons.
corrosivity Not applicable.
sensitization No a skin sensitizer.
Germ Cell Mutagenicity No information available.
carcinogenicity Not known chronic effects based on available data. None of the ingredients present in excess of 0.1% are listed as carcinogenic by NTP, IARC or OSHA.

Reproductive Toxicity No information available.
STOT - single exposure No information available.
STOT - repeated exposure No information available.
Aspiration Hazard Deliberate inhalation of concentrated vapor or mist may cause headache, dizziness and nausea.

Numerical measures of toxicity - Product Information

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (inhalation-gas) 2293333 mg/l
ATEmix (inhalation-vapor) 4526.3 mg/l

12. Ecological Information

This product does not contain marine pollutants.

ecotoxicity

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Chemical name	Partition coefficient
N-Butane 106-97-8	2.89
Propane 74-98-6	2.3

Other adverse effects

Ozone No information available
 This product does not contain CFCs or other ozone depleting substances. Federal regulations prohibit the use CFC propellants in aerosols.

13. Disposal Considerations

Waste treatment methods

Disposal of wastes Dispose of in accordance with federal, state and local regulations.

Contaminated packaging

Pressurized container: Do not pierce or burn, even after use. Do not puncture or incinerate container. If empty: Place in trash or offer for recycling if available. If partly filled: Call your local solid waste agency for disposal instructions.

14. Transport Information

DOT	Limited quantity (LQ) Air Freshener/Deodorizer
UN/ID no	UN1950
Proper Shipping Name	Limited quantity (LQ)
Hazard Class	2.1
Marine pollutant	This product does not contain marine pollutants.

15. Regulatory information

International Inventories

TSCA All ingredients of this product are listed or are excluded from listing under the U.S. Toxic Substances Control Act (TSCA) Chemical Substance Inventory.

DSL All ingredients are listed or are excluded from listing on the DSL.

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute Health Hazard	yes
Chronic Health Hazard	No
Fire Hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations

Chemical name	New Jersey	Massachusetts	Pennsylvania
N-Butane 106-97-8	X	X	X
Propane 74-98-6	X	X	X

U.S. EPA Label information

EPA Pesticide registration number Not applicable

16. Other information

<u>NFPA</u>	Health Hazards 1	flammability 1	Instability 1	Physical and chemical properties Not applicable PERSONAL PROTECTION A - Eyes protection
<u>HMIS</u>	Health Hazards 1	flammability 2	Physical Hazards 1	

Prepared by Regulatory Department

Issue date 11-Mar-2014

Revision note

No information available

Disclaimer

The information provided in this Material Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet