SAFETY DATA SHEET

Issuing Date No data available

Revision Date 03-Nov-2014

Revision Number 2



The supplier identified below generated this SDS using the UL SDS template. UL did not test, certify, or approve the substance described in this SDS, and all information in this SDS was provided by the supplier or was reproduced from publically available regulatory data sources. UL makes no representations or warranties regarding the completeness or accuracy of the information in this SDS and disclaims all liability in connection with the use of this information or the substance described in this SDS. The layout, appearance and format of this SDS is © 2014 UL LLC. All rights reserved.

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Name Parsley Plus (9746)

Other means of identification

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended UseGeneral Purpose Cleaner - Non-aerosol

Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier NameVENUS LABORATORIESSupplier Address111 S ROHLWING ROAD

ADDISO N IL 60101 US

Supplier Phone Number Phone:800-592-1900 Chemtrec: 800-424-9300

2. HAZARDS IDENTIFICATION

Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Serious eye damage/eye irritation Category 1

GHS Label elements, including precautionary statements

Emergency Overview

Signal word Warning



Hazard Statements

May cause eye irritation May cause skin irritation



Appearance Water white

Physical State Liquid

Odor Parsley

Precautionary Statements - Prevention

Wash face, hands and any exposed skin thoroughly after handling

Wear protective gloves/protective clothing/eye protection/face protection Avoid breathing dust/fume/gas/mist/vapors/spray Remove the contaminated clothing and wash.

Precautionary Statements - Response

Eves

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing If irritation persists consult a doctor/physician.

Precautionary Statements - Storage

None

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Not applicable

Unknown Toxicity

3.25% of the mixture consists of ingredient(s) of unknown toxicity

Other information

No information available

Interactions with Other Chemicals

No information available.

3. COMPOSITION/INFORMATION ON INGREDIENTS

.

Chemical Name	CAS No.	Weight-%	Trade Secret
Coco-glucoside	68515-73-1	1 - 5	*
Ethyl alcohol	64-17-5	0.1 - 1	*

^{*}The exact percentage (concentration) of composition has been withheld as a trade secret

4. FIRST AID MEASURES



First aid measures

General Advice Show this safety data sheet to the doctor in attendance. Immediate medical

attention is required.

Eye Contact Rinse immediately with plenty of water, also under the eyelids, for at least 15

minutes. Keep eye wide open while rinsing. Remove contact lenses, if present and

If irritation persists consult a doctor/physician.

Skin Contact Wash off immediately with soap and plenty of water for at least 15 minutes. May

cause an allergic skin reaction. In the case of skin irritation or allergic reactions

see a physician.

Inhalation Remove to fresh air. Get medical attention immediately if symptoms occur.

Ingestion Rinse mouth immediately and drink plenty of water. Never give anything by mouth

to an unconscious person. Do NOT induce vomiting. Call a physician.

Self-protection of the first aider Avoid contact with skin, eyes or clothing. Use personal protective equipment as required. Wear personal protective clothing (see section 8).

Burning sensation. Itching. Rashes. Hives.

Most important symptoms and effects, both acute and delayed

Most Important Symptoms and Effects

Indication of any immediate medical attention and special treatment needed

Notes to Physician May cause sensitization of susceptible persons. Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

CAUTION: Use of water spray when fighting fire may be inefficient.

Specific Hazards Arising from the Chemical

No information available.

Hazardous Combustion Products

Carbon oxides.

Explosion Data

Sensitivity to Mechanical Impact No.

Sensitivity to Static Discharge No.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.



6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal Precautions Avoid contact with skin, eyes or clothing. Use personal protective equipment as required.

Other Information Refer to protective measures listed in Sections 7 and 8.

Environmental Precautions

Environmental Precautions Refer to protective measures listed in Sections 7 and 8.

Methods and material for containment and cleaning up

Methods for Containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Handling Handle in accordance with good industrial hygiene and safety practice. Avoid contact with

skin, eyes or clothing. Do not eat, drink or smoke when using this product.

Conditions for safe storage, including any incompatibilities

Storage Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible ProductsNone known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Ethyl alcohol	STEL: 1000 ppm	TWA: 1000 ppm	IDLH: 3300 ppm 10% LEL
64-17-5		TWA: 1900 mg/m ³	TWA: 1000 ppm
		(vacated) TWA: 1000 ppm	TWA: 1900 mg/m ³
		(vacated) TWA: 1900 mg/m ³	-

ACGIH TLV: American Conference of Governmental Industrial Hygienists - Threshold Limit Value OSHA PEL: Occupational Safety and Health Administration - Permissible Exposure Limits NIOSH IDLH Immediately Dangerous to Life or Health

Other Exposure Guidelines Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962

(11th Cir., 1992)

Appropriate engineering controls



Engineering Measures Showers

Eyewash stations Ventilation systems

Individual protection measures, such as personal protective equipment

Eye/Face ProtectionNone required for consumer use. If splashes are likely to occur:. Wear safety glasses with

side shields (or goggles).

Skin and Body Protection Wear protective gloves and protective clothing.

Respiratory Protection No protective equipment is needed under normal use conditions. If exposure limits are

exceeded or irritation is experienced, ventilation and evacuation may be required.

Handle in accordance with good industrial hygiene and safety practice. Avoid contact with

skin, eyes or clothing. Wear suitable gloves and eye/face protection. Do not eat, drink or

None known

smoke when using this product.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical and Chemical Properties

Physical StateLiquidAppearanceWater whiteOdorHerbaceous

Color No information available Odor Threshold No information available

PropertValuesRemarks/ Methody pH5None known

Melting / freezing pointNo data availableNone knownBoiling point / boiling range85°CNone knownFlash Point94° C / 201° FNone knownEvaporation RateNo data availableNone knownFlammability (solid, gas)No data availableNone known

Flammability Limit in Air

Upper flammability limit
Lower flammability limit
Vapor pressure

No data available
No data available

None known Vapor density No data available None known 1.01 - 1.02**Specific Gravity** None known Soluble in water None known **Water Solubility** None known Solubility in other solvents No data available Partition coefficient: n-octanol/waterNo data available None known **Autoignition temperature** No data available None known **Decomposition temperature** No data available None known Kinematic viscosity No data available None known

Dynamic viscosity
No data available
Explosive properties
No data available
Oxidizing Properties
No data available

Other Information

Softening Point

VOC Content (%)

Particle Size

No data available

No data available

No data available

Particle Size Distribution



10. STABILITY AND REACTIVITY

Reactivity

No data available.

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to avoid

None known based on information supplied.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

Carbon oxides.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation Specific test data for the substance or mixture is not available. No irritation expected.

Eye Contact Specific test data for the substance or mixture is not available. Expected to be an irritant

based on components. May Cause Eye Irritation. May cause burns.

Skin Contact Specific test data for the substance or mixture is not available. Not expected to be a

skin irritant based on components. Prolonged contact may cause redness and irritation.

Ingestion Specific test data for the substance or mixture is not available. Ingestion may cause

irritation to mucous membranes. Ingestion may cause gastrointestinal irritation, nausea,

vomiting and diarrhea.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Ethyl alcohol	-	-	= 124.7 mg/L (Rat)4 h
64-17-5			

Information on toxicological effects

Symptoms May cause redness and tearing of the eyes.



Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No information available.

Mutagenic Effects No information available.

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
Ethyl alcohol 64-17-	A3	Group 1	Known	X
5		•		

ACGIH (American Conference of Governmental Industrial Hygienists)

A3 - Animal Carcinogen

IARC (International Agency for Research on Cancer)

Group 1 - Carcinogenic to Humans
NTP (National Toxicology Program)

Known - Known Carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive Toxicity

No information available.

STOT - single exposure

No information available.

STOT - repeated exposure

No information available.

Chronic Toxicity No known effect based on information supplied. Contains a known or suspected

carcinogen. Ethanol has been shown to be carcinogenic in long-term studies only when consumed as alcoholic beverage. Contains a known or suspected reproductive toxin. Ethanol has been shown to be a reproductive toxin only when consumed as an alcoholic

beverage.

Target Organ Effects Eyes.

Aspiration Hazard No information available.

Numerical measures of toxicity Product Information

The following values are calculated based on chapter 3.1 of the GHS document

Not applicable



12. ECOLOGICAL INFORMATION

Ecotoxicity

The environmental impact of this product has not been fully investigated.

Chemical Name	Toxicity to Algae	Toxicity to Fish	Toxicity to Microorganisms	Daphnia Magna (Water Flea)
Ethyl alcohol		96h LC50: > 100 mg/L	EC50 = 34634 mg/L 30 min	48h LC50: 9268 - 14221
64-17-5		(Pimephales promelas) 96h	EC50 = 35470 mg/L 5 min	mg/L 48h EC50: = 2 mg/L
		LC50: 13400 - 15100 mg/L	_	24h EC50: = 10800 mg/L
		(Pimephales promelas) 96h		_
		LC50: 12.0 - 16.0 mL/L		
		(Oncorhynchus mykiss)		

Persistence and Degradability

No information available.

Bioaccumulation

Chemical Name	Log Pow
Ethyl alcohol 64-17-	-0.32
5	

Other adverse effects

No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal methodsThis material, as supplied, is not a hazardous waste according to Federal regulations (40)

CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local

regulations for additional requirements.

Contaminated Packaging Dispose of contents/containers in accordance with local regulations.

California Hazardous Waste Codes 561

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical Name	California Hazardous Waste
Ethyl alcohol 64-17-	Toxic
5	Ignitable

14. TRANSPORT INFORMATION

DOTNOT REGULATEDProper Shipping NameNON REGULATED

Hazard Class N/A

TDG Not regulated



ICAO Not regulated

Not regulated IATA **NON REGULATED**

Proper Shipping Name

Hazard Class N/A

IMDG/IMO Not regulated

Hazard Class N/A

RID Not regulated **ADR** Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies

DSL All components are listed either on the DSL or NDSL.

Not regulated

Not regulated

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

MEX

ADN

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute Health Hazard Yes **Chronic Health Hazard** No Fire Hazard No Sudden release of pressure hazard No **Reactive Hazard** No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.



U.S. State Right-to-Know Regulations

Canada WHMIS Hazard Class D2B - Toxic materials



16. OTHER INFORMATION

NFPA Health Hazards 1 Flammability 1 Instability 0 Physical and Chemical Hazards - HMIS Health Hazards 1 Flammability 1 Physical Hazard 0 Personal Protection

Revision Date 03-Nov-2014

Revision Note No information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet

